





- 1 .000050 MIN THK NICKEL UNDERPLATE OVER ENTIRE CONTACT.
- 2 .000150 MIN BRIGHT TIN/LEAD OVER ENTIRE CONTACT.
- 3 .000100 MIN THK BRIGHT TIN/LEAD IN ZONE 1.
- 4 GOLD FLASH IN LOCALIZED GOLD PLATE AREA.
- 5 .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 6 .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 7. TO BE APPLIED PER AMP APPLICATION SPEC 114-16015.
- 8. RECOMMENDED HOLE SIZE IS .031-.035 DIA.
- 9 FOR SOLDERABILITY SEE AMP PRODUCT SPEC 108-9024.
- 10 .000150 MIN TIN-LEAD IN ZONE 2.
- 11 AREA TO BE UNPLATED (-9 ONLY).
- 12 GOLD FLASH IN ZONE 1. .000150 MIN TIN IN ZONE 3.
- 13 GOLD FLASH IN ZONE 1.
- 14 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL IN THIS AREA.

	161314	1-88997-4
	151314	1-88997-3
	191214	1-88997-2
OBSOLETE	1011	88997-9
	1336	88997-5
	1335	88997-4
SUPERSEDED BY 88997-5	1334	88997-3
	1229	88997-2
	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER CHK S. BOLASH APVD M. WALMSLEY	10MAR04 10MAR04 10MAR04		TE Connectivity						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		0 PLC ± -		CONTACT, SOLDER TAB, FFC, .100							
		1 PLC ± -									
		2 PLC ± -									
		3 PLC ± .005									
		4 PLC ± -									
ANGLES ± -		PRODUCT SPEC 108-9024		SIZE A2		CAGE CODE 00779		DRAWING NO C=88997		RESTRICTED TO —	
APPLICATION SPEC 114-16015											
WEIGHT —											
MATERIAL PH. BRONZE .010 THK		FINISH SEE TABLE		CUSTOMER DRAWING							
				SCALE 10:1		SHEET 1 of 1		REV Y			