









Copyright FCI.



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



SHELL		PART NUMBER						
		A±0.38	B±0.12	C±0.10	D±0.25	G±0.25	Plating:0.76µ AU	Plating:Flash AU
09		30.81	24.99	16.96	16.79	5.90	D09P23B6UA00**	D09P23B4UA00**
15		39.14	33.32	25.18	25.12	5.90	D15P23B6UA00**	D15P23B4UA00**
25		53.03	47.04	39.12	38.84	5.70	D25P23B6UA00**	D25P23B4UA00**
37		69.32	63.50	55.68	55.30	5.70	D37P23B6UA00**	D37P23B4UA00**

REQUIREMENTS

Technical characteristics:
Shell:steel tin/Zinc Cr3 plated
Insulators:self-extinguishing black polyester,ULclass94V0
Contacts size 20,brass,gold on mating end,bright tin on termination end over nickel on entire contact
Cycles :500 for protection 6
 :200 for protection 4

Metal plate for electrical continuity:brass,tin/Zinc Cr3 plated

Electrical characteristics:

max.current rating:5A
Test voltage:1000V
Rated voltage:300V
Contact resistance:≤15mΩ
Shell resistance:≤5mΩ
Insulation resistance:≥5000MΩ

Climatic characteristics:

Operating temperature range:-55°C +125°C

Dimensions:

in accordance with MIL-C-24308

LF FOR LEAD FREE

FOR ROHS DETAILS REFER DWG.NO:C01-8646-0000

rev	ecn no	dr	date
B	105-0124	JS	2005/07/27
C	106-0074	SK	2006/06/08
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection size A3	mm Scale 1:1
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	JOHN SLEEBA	2000/11/21	ANGULAR 0.XX' ±1°	0.X	±0.1	
Eng	GEORGE VJ	2000/11/21		0.XX	±0.1	
Chr	GEORGE VJ	2005/07/27		0.XXX	±0.1	
Appr	KVSD	2005/07/27	Product family		D-SUB	Spec ref -
FCI			title MALE CONNECT.DELTA D WITH METAL PLATE.			Rev. C
			catalog no DELTA-D			dwg no C01-8646-0737
						sheet 1 of 1

REV F - 2006-04-17