

CGA3E3X7R1H154K080AB

TDK Item Description : CGA3E3X7R1H154KT****




Equivalent C1608X7R1H154K for Automotive

Application & Main Feature


Automotive Grade (General (Up to 50V))

Series

CGA3(1608) [EIA CC0603]



DC Bias Characteristic



Dimensions

L 1.60mm +/-0.1mm
W 0.80mm +/-0.1mm
T 0.80mm +/-0.1mm
B 0.20mm Min.
G 0.30mm Min.

Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

Rated Voltage

1H (50Vdc)

Capacitance

150nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor

5% Max.


Insulation Resistance

3.33Gohm Min.


AEC-Q200

Yes


|Z|, ESR vs. Freq. Characteristics



Temperature Characteristic



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristic

