


## Features

- **Low Insertion Loss** : 0.50 dB @ 2.7 GHz  
0.60 dB @ 5.8 GHz
- **Isolation**: 29 dB @ 2.7 GHz  
22 dB @ 5.8 GHz
- **Low DC Power Consumption**
- **Miniature QFN12L (3x3 mm) Plastic Lead (Pb) Free Package, RoHS Compliant**
- **PHEMT process**

## QFN12L (3 x 3 mm)



## Description

The HWS447 is a GaAs PHEMT MMIC SPDT switch operating at DC-6 GHz in a low cost miniature QFN12L (3 x 3 mm) plastic lead (Pb) free package. The HWS447 features low insertion loss and high isolation with very low DC power consumption. This switch can be used in WiMAX or IEEE 802.11a/b/g WLAN PC card and access point applications as transmit/receive switch, antenna diversity switch, or band-selection switch.


## Electrical Specifications at 25°C with 0, +3V Control Voltages

| Parameter                          | Test Conditions   | Min. | Typ.     | Max. | Unit       |
|------------------------------------|-------------------|------|----------|------|------------|
| Insertion Loss                     | 0.10-6.00 GHz     |      | 0.60     |      | dB         |
|                                    | 2.30-2.70 GHz     |      | 0.50     | 0.80 | dB         |
|                                    | 3.30-3.90 GHz     |      | 0.50     | 0.80 | dB         |
|                                    | 5.15-5.88 GHz     |      | 0.60     | 0.90 | dB         |
| Isolation (RFC Port to Off Port)   | 0.10-6.00 GHz     |      | 22       |      | dB         |
|                                    | 2.30-2.70 GHz     | 25   | 29       |      | dB         |
|                                    | 3.30-3.90 GHz     | 23   | 27       |      | dB         |
|                                    | 5.15-5.88 GHz     | 18   | 22       |      | dB         |
| Isolation (RF1 Port to RF2 Port)   | 0.10-6.00 GHz     |      | 18       |      | dB         |
|                                    | 2.30-2.70 GHz     |      | 24       |      | dB         |
|                                    | 3.30-3.90 GHz     |      | 21       |      | dB         |
|                                    | 5.15-5.88 GHz     |      | 18       |      | dB         |
| Return Loss (On Port)              | 0.10-6.00 GHz     |      | 20       |      | dB         |
| Return Loss (Off Port)             | 0.10-6.00 GHz     |      | 12       |      | dB         |
| Input Power for One dB Compression | 2.00-6.00 GHz     |      |          |      |            |
|                                    | @+3V<br>@+5V      |      | 36<br>38 |      | dBm<br>dBm |
| Control Current                    | No RF Power Input |      | 3        | 10   | uA         |


Note: All measurements made in a 50 ohm system with 0/+3.0V control voltages, unless otherwise specified.

## Typical Performance Data with 8pF Capacitors @ +25 °C


### Insertion Loss vs Frequency



### Isolation vs Frequency




### Return Loss vs Frequency



## Absolute Maximum Ratings

| Parameter             | Absolute Maximum  |
|-----------------------|-------------------|
| RF Input Power        | +36 dBm @ +3V     |
| Control Voltage       | +6V               |
| Operating Temperature | -40 °C to +85 °C  |
| Storage Temperature   | -65 °C to +150 °C |

## Pin Out (Top View)



Note:

1. DC blocking capacitors  $C_B=8\text{pF}$  are required on all RF ports.
2. Exposed pad in the bottom must be connected to ground by via holes.

## Logic Table for Switch On-Path

| VC1 | VC2 | RFC-RF1 | RFC-RF2 |
|-----|-----|---------|---------|
| 1   | 0   | On      | Off     |
| 0   | 1   | Off     | On      |

'1' = +2.7V to +5V

'0' = 0V to +0.2V