

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

30968-1100

Status:

Active

Overview:

H-DAC 64™ Dual-Row High Density Automotive Connectors

Description:

2.54mm Pitch, 0.64mm Width HDAC 64™ High Density Automotive Crimp Housing, Dual Row, 10 Circuits, Polarization Option #1, Gray

Documents:

3D Model

Drawing (PDF)

Product Specification PS-30968-0001 (PDF)

Product Specification PS-34646-001 (PDF)

Application Specification AS-30700-000 (PDF)

RoHS Certificate of Compliance (PDF)


General	
Product Family	Crimp Housings
Series	30968
Application	Power, Wire-to-Wire
Comments	Polarization Option #1
Overview	H-DAC 64™ Dual-Row High Density Automotive Connectors
Product Name	H-DAC 64™
UPC	800754879736

Physical	
Circuits (maximum)	10
Circuits Detail	10
Color - Resin	Gray
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	5.130/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical	
Current - Maximum per Contact	7A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-30700-000
Product Specification	PS-30968-0001, PS-34646-001
Sales Drawing	SD-30968-120



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

30968Series

Mates With

30700 , 31389 H-DAC 64™ High Density Automotive Connectors

Use With

34230 Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

30968-1100