



D

C



B

A



DETAIL A
SCALE 20:1

- 1 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2 WIRE RANGE: 0.5-2mm² [20-14 AWG]. INSULATION RANGE: 1.52-3.30 [.060-.130] DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5 SUPERSEDED BY 1-770250-0.



5	GOLD	4	0.30 [.012]	BRASS	1-770250-0
	GOLD	1	0.30 [.012]	BRASS	-770250-2-
	PRE-TIN		0.30 [.012]	BRASS	770250-1
	FINISH		MATERIAL	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 21MAY03	 TE Connectivity					
		CHK C.JONES 21MAY03						
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C.JONES 21MAY03	NAME				
	0 PLC ± -		PRODUCT SPEC	PIN, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II -				
	1 PLC ± -		-					
	2 PLC ± -		APPLICATION SPEC					
	3 PLC ± -		-					
	4 PLC ± -		-					
ANGLES ± -		FINISH	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
MATERIAL			WEIGHT -	A2	00779	C-770250		-
SEE TABLE	SEE TABLE		CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV F