



Helping Customers Innovate, Improve & Grow



OX-220

Features

- Reflow Process Compatible
- Surface Mount package
- AT-CUT and SC_CUT Crystal Options
- Low Profile Compact Package (8.3mm)

Applications

- Base stations
- Test equipment
- Synthesizers
- Military communication equipment
- Digital Switching

Performance Specifications


Frequency Stabilities ¹ (AT-Cut Crystal-10 to 160 MHz -)						
Parameter	Min	Typical	Max	Units	Condition	
vs. operating temperature range (referenced to +25°C)	-100		+100	ppb	-20 to +70°C	Options ⁵
	-200		+200	ppb	-20 to +70°C	
	-250		+250	ppb	-40 to +85°C	
Initial tolerance	-0.5		+0.5	ppm	at time of shipment, nominal EFC	
vs. supply voltage change	-10		+10	ppb	V _s ±5% static	
vs. load change	-10		+10	ppb	Load ±5% static	
vs. aging / day	-5		+5	ppb	after 30 days of operation	
vs. aging / year	-300		+300	ppb	≤ 60 MHz after 30 days of operation	
vs. aging / year	-500		+500	ppb	≥ 60 MHz after 30 days of operation	
Warm-up time			5	minutes	to ±100ppb of final frequency (1 hour reading) @ +25°C	
Frequency Stabilities ¹ (SC-Cut Crystal-Option - 10 to 100 MHz)						
vs. operating temperature range (referenced to +25°C)	-5		+ 5	ppb	0 to 50 °C	
	-10		+10	ppb	-5 to +70°C	
	-10		+10	ppb	-20 to +70°C	
	-20		+20	ppb	-40 to +85°C	
Initial tolerance	-0.2		+0.2	ppm	at time of shipment, nominal EFC	
vs. supply voltage change	-5		+5	ppb	V _s ±5% static	
vs. load change	-5		+5	ppb	Load ±5% static	
vs. aging / day	-1		+1	ppb	after 30 days of operation	
vs. aging / year	-100		+100	ppb	after 30 days of operation	
vs. aging / year (following years)	-80		+80	ppb	after 30 days of operation	
vs. aging / year (5MHz; OX- 221)	-15		+15	ppb	after 30 days of operation	
Warm-up time			5	minutes	to ±100ppb of final frequency (1 hour reading) @ +25°C	

Performance Specifications


Supply Voltage (Vs)					
Parameter	Min	Typical	Max	Units	Condition
Supply voltage (standard)	3.135	3.3	3.465	VDC	
	4.75	5.0	5.25	VDC	
Power consumption			3.1	Watts	during warm-up
			1.5	Watts	steady state @ +25°C
RF Output					
Signal [standard]	HCMOS				
Load		15		pF	
Signal Level (Vol)			0.4	VDC	with Vs=3.3V and 15pF Load
Signal Level (Vol)			0.5		with Vs=5.0V & 12V and 15pF Load
Signal Level (Voh)	2.4			VDC	with Vs=3.3V and 15pF Load
Signal Level (Voh)	3.5				with Vs=5.0V & 12V and 15pF Load
Duty Cycle	45		55	%	@ (Voh-Vol)/2
Signal	Sine Wave				
Load		50		Ω	
Output Power @3,3V	2	5	8	dBm	50 Ω load
Putput Power @ 5.0V	5	8	11	dBm	50 Ω load
Harmonics			-30	dBm	50 Ω load
Frequency Tuning (EFC)					
Tuning Range	Fixed OCXO; No adjust				Option ⁵
Tuning Range	±3.0		±8	ppm	
	±0.8		±2.4	ppm	
Linearity	10%				
Tuning Slope	Positive				
Control Voltage Range	0.0	1.4	2.8	VDC	with Vs=3.3V
	0.0	2.0	4.0		with Vs=5.0V
Reference Voltage Output (Vref)					
Reference Voltage	2.75	2.8	2.85	VDC	with Vs = 3.3 VDC
	3.92	4.0	4.08	VDC	with Vs = 5.0 VDC
Additional Parameters					
Phase Noise ³		-80	-70	dBc/Hz	1 Hz
		-110	-105	dBc/Hz	10 Hz
		-138	-130	dBc/Hz	100 Hz
		-148	-140	dBc/Hz	1 kHz
		-152	-145	dBc/Hz	10 kHz
					@ 30.72MHz with SC Cut
Phase Noise ³		-80	-70	dBc/Hz	1 Hz
		-110	-105	dBc/Hz	10 Hz
		-135	-130	dBc/Hz	100 Hz
		-145	-140	dBc/Hz	1 kHz
		-152	-145	dBc/Hz	10 kHz
					@ 20MHz with SC Cut
Weight			10	g	
Processing & Packing	Handling & Processing Note				

Absolute Maximum Ratings					
supply voltage (Vs)			5.5	V	with Vs=3.3 & 5.0 VDC
Output Load			50	pF	
Operable Temperature Range	-55		+85	°C	
Storage Temperature Range	-55		+85	°C	

Outline Drawing / Enclosure



OX-220	
Height "H"	cover material
7.8	metal
12.1	plastic
15.0	metal
11.3	metal
8.5	plastic
7.1	metal




Padvorschlag
land pattern
recommendation

Pin Connections	
1	Electronic Frequency Control Input (EFC)
2	Reference Voltage output
3	Supply Voltage Input (Vs)
4	RF Output
5	Oven Alarm
6	N.C or Option (must remain un connected)
7	Ground (Case)

Dimensions in mm

Standard Shipping Method (OX-220 / OX -221)



Maßangaben in mm:

A, B und K Maße vom Bauelement abhängig.
Fertigungstoleranzen entsprechen der DIN IEC 286-3

Dimension in mm:


A, B und K are dependent upon component dimensions,
production tolerance complying DIN IEC 286-3

All dimensions in millimetres unless otherwise stated.

Enclosure Type	Tape Width W (mm)	Quantity per meter	Quantity per reel	Dimension P
OX-2200 (7.8mm)	44	37.5	280	32
OX-2201 (12.1mm)	44	37.5	175	28
OX-2202 (15mm)	44	37.5	120	28
OX-2206 (8.5mm)	44	37.5	250	28
OX-2207 (7.1mm)	44	37.5	230	32

Recommended Reflow Profile


Solderprofile:



Profile Feature	Pb-Free Assembly/ Sn-Pb Assembly	Profile Feature	Pb-Free Assembly/ Sn-Pb Assembly
Average ramp-up rate (T_L to T_p)	3°C/second max.	Time 25°C to Peak Temperature	8 minutes max.
Preheat -Temperature Min $T_{s \text{ min}}$ -Temperature Min $T_{s \text{ max}}$ -Time (min to max) t_s	150°C 200°C 60-180 seconds	Time maintained above -Temperature (T_L) -Time (t_L)	217°C 60-150 seconds
$T_{s \text{ max}}$ to T_L -Ramp-up Rate	3°C/second max		
Time maintained above -Temperature (T_L) -Time (t_L)	217°C 60-150 seconds	Time within 5°C of actual Peak Temperature (T_p)	20-40 seconds
Peak Temperature (T_p)	max 260°C	Ramp-down Rate	6°C/ second max

Note: All temperatures refer to topside of the package, measured on the package body surface.

Ordering Information



Notes:

1. Contact factory for improved stabilities or additional product options. Not all options and codes are available at all frequencies.
2. Unless other stated all values are valid after warm-up time and refer to typical conditions for supply voltage, frequency control voltage, load, temperature (25°C).
3. Phase noise degrades with increasing output frequency.
4. Subject to technical modification.
5. Contact factory for availability.

For Additional Information, Please Contact

USA:

Vectron International
267 Lowell Road
Hudson, NH 03051
Tel: 1.888.328.7661
Fax: 1.888.329.8328

Europe:

Vectron International
Landstrasse, D-74924
Neckarbischofsheim, Germany
Tel: +49 (0) 7268.801.100
Fax: +49 (0) 7268.801.282

Asia:

Vectron International
1589 Century Avenue, the 19th Floor
Chamtime International Financial Center
Shanghai, China
Tel: 86.21.6081.2888
Fax: 86.21.6163.3598

Disclaimer

Vectron International reserves the right to make changes to the product(s) and or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Rev:31 mar 2011