

BDX33

Darlington Transistor


High Voltage Switching



Features:

- Collector-Emitter Sustaining Voltage - $V_{CEO(sus)} = 100\text{ V}$ (Minimum)
- Monolithic construction with built-in base-emitter shunt resistor

TO-220



- Pin**
1. Base
 2. Collector
 3. Emitter
 4. Collector (Case)

Dimensions	Minimum	Maximum
A	14.68	15.31
B	9.78	10.42
C	5.01	6.52
D	13.06	14.62
E	3.57	4.07
F	2.42	3.66
G	1.12	1.36
H	0.72	0.96
I	4.22	4.98
J	1.14	1.38
K	2.2	2.97
L	0.33	0.55
M	2.48	2.98
O	3.7	3.9

Dimensions : Millimetres

NPN
BDX33C

10 Amperes
Complementary Silicon
Power Transistors
80 - 100 Volts
70 Watts

Maximum Ratings


Characteristic	Symbol	BDX33C	Unit
Collector - emitter voltage	V_{CEO}	100	V
Collector - base voltage	V_{CBO}		
Emitter - base voltage	V_{EBO}	5	A
Collector current - continuous - peak	I_C	10	
	I_{CM}	15	
Base current	I_B	0.25	
Total power dissipation at $T_C = 25^\circ\text{C}$ derate above 25°C	P_D	70 0.56	W W/ $^\circ\text{C}$
Operating and storage junction temperature range	T_J, T_{STG}	-65 to +150	$^\circ\text{C}$

Thermal Characteristics

Parameters	Symbol	Maximum	Unit
Thermal resistance junction to case	$R_{\theta jc}$	1.78	$^\circ\text{C/W}$

Darlington Transistor

Figure - 1 Power Derating




Electrical Characteristics ($T_C = 25^\circ\text{C}$ Unless Otherwise Noted)

Parameters	Symbol	Minimum	Maximum	Unit
OFF Characteristics				
Collector - emitter sustaining voltage (1) ($I_C = 100\text{ mA}$, $I_B = 0$)	$V_{CEO(SUS)}$	100	-	V
Collector cut off current ($V_{CE} = 50\text{ V}$, $I_B = 0$)	I_{CES}	-	0.5	mA
Collector - base cut off current ($V_{CB} = \text{Rated } V_{CB}$, $I_E = 0$)	I_{CBO}	-	200	μA
Emitter - base cut off current ($V_{EB} = 5\text{ V}$, $I_C = 0$)	I_{EBO}	-	10	mA
ON Characteristics (1)				
DC current gain ($I_C = 3\text{ A}$, $V_{CE} = 3\text{ V}$)	h_{FE}	750	-	-
Collector - emitter saturation voltage ($I_C = 3\text{ A}$, $I_B = 6\text{ mA}$)	$V_{CE(sat)}$	-	2.5	V
Base - emitter on voltage ($I_C = 3\text{ A}$, $V_{CE} = 3\text{ V}$)	$V_{BE(on)}$	-	2.5	

(1) Pulse Test : Pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$

Figure - 2 Safe Operating Area



There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown safe operating area curves indicate I_C - V_{CE} limits of the transistor that must be observed for reliable operation i.e., the transistor must not be subjected to greater dissipation than the curves indicate

The data of Figure - 2 is based on $T_{J(PK)} = 150^\circ\text{C}$; T_C is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(PK)} < 150^\circ\text{C}$. At high case temperatures, thermal limitation will reduce the power that can be handled to values less than the limitations imposed by second breakdown.

Part Number Table

Description	Type	Part Number
Darlington Transistor	NPN	BDX33C

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.