



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		E1	REVISED PER ECO-15-016302	14NOV2015	NK	DR



- 1


TIN PLATING OVER ALL.
- 2

WIRE RANGE: 0.3 - 1 MM² (22-17 AWG)
- 3

GOLD OVER NICKEL UNDERPLATE ALL OVER.



SECTION A-A




SECTION B-B

0.13	.005	1.486	.0585	2.79	.110	7.62	.300
0.00203	.000080	1.47	.058	2.67	.105	6.55	.258
0.00127	.000050	1.359	.0535	2.41	.095	6.40	.252
0.00038	.000015	0.25	.010	2.29	.090	3.94	.155
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

OBSOLETE	3	0.25 BE CU	640259-2
	1	0.25 BE CU	640259-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 6-10-97		 TE Connectivity	
DIMENSIONS: mm		CHK R. SWING 6-10-97			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. BEDDICK 6-17-97		NAME RECEPTACLE, .058 DIAMETER, 22-17 AWG, P.C. CONTACT —
	0 PLC ± —		PRODUCT SPEC 108-1025		
	1 PLC ± —		APPLICATION SPEC 114-1008		
	2 PLC ± 0.13		SIZE		
3 PLC ± —		4 PLC ± —		CAGE CODE	
ANGLES ± —		FINISH		DRAWING NO	
MATERIAL SEE TABLE		SEE TABLE		RESTRICTED TO —	
		WEIGHT —		A2 00779 C=640259	
CUSTOMER DRAWING				SCALE 10:1	
				SHEET 1 of 1	
				REV E1	