





FCI

FCI P/N	"L"
(NOTE 1)	
54177-YXXX	XXX



COMPONENTS		
ITEM	QTY	DESCRIPTION
1	2	FC CONNECTOR, 3mm, MM-127
2	"L"	CABLE, 650/1.6mm ZIP
3	1	MTRJ CONNECTOR, MM
4	1	90° MTRJ BOOT, BLACK
5	A/R	ID LABEL
6	2"	SHRINK TUBE, WHITE
7	2"	SHRINK TUBE, YELLOW

SPECIFICATIONS		
	MTRJ	FC
INSERTION LOSS	0.5dB MAX	0.5dB MAX
RETURN LOSS	20dB MIN	N/A
FIBER PROTRUSION	100nm MAX	50nm MAX
APEX OFFSET	N/A	45um MAX
FIBER UNDERCUT	SEE TELECORDIA GR-326	

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 Electronics FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	NOMINALS ONLY				projection 	title		
A	V12300	JKK	10/01/01		UNLESS NOTED					CA, MJ90-FC DPX		
B	V12322	JKK	10/16/01							MM-1.6mm ZIP, TYPE NRA		
C	V12373	JKK	1/3/02	angles						product family FIBER OPTICS		code
D	V20480	JRW	4/1/02	dr	J. KILE	10/01/01	MM			size	dwg no	
				enrg	S. CLARK	10/01/01						
				chr	S. CLARK	10/01/01	scale		A4	54177	sheet	
				appd	S. CLARK	10/01/01	1:1				1 of 1	
sheet index	revision sheet											

- NOTES:
- FCI PART NUMBER CONSISTS OF THE DWG NO, A DASH, AND A SUFFIX YXXX WHERE Y IS THE UNIT OF LENGTH (Y=M IS METERS, Y=F IS FEET) AND WHERE XXX IS THE LENGTH OF "L"
(EX. 54177-M004 IS 4 METERS IN LENGTH)
 - LENGTH IS MEASURED IN A LINEAR STATE FROM CONNECTOR TIP TO CONNECTOR TIP.

1 | 2

3 |

4

ACAD

PDM: Rev:D

STATUS:Released

Printed: Aug 14, 2008