



Home: Crimp Housings >

Part Number: 42140-2204**BOTTOM ENTRY FEMALE HSG ASSY**

Image not available

Status:	OBsolete
Replacement:	Contact Molex
Series:	42140
Category:	Crimp Housings

Go to [Part Detail](#) ▾ [CHECK DISTRIBUTOR INVENTORY](#) [Add to My Parts](#) [Email this page](#)

Series image - Reference only

Product Environmental Compliance[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active

EU RoHS Certificate of Compliance (PDF)

[Multiple Part Product Compliance Statements](#)
EU RoHS, REACH SVHC, & Low-Halogen [Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail****COLLAPSE ALL****▼ General**

Status	Obsolete
Category	Crimp Housings
Series	42140
Application	Signal
Product Name	N/A
UPC	756054254721

▼ Physical

Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	0.500/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +105°C

▼ Electrical

(Please review the Product Specification for specific details.)	
Current - Maximum per Contact	2.0A

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. Click here to visit the UL Database	
CSA	LR19980
UL	E29179

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017