


Rated inductance 0.5 to 3.9 μ H

Rated current 10 to 25 A

Construction

- Ferrite core
- Magnetically shielded
- Winding: enamel copper flat wire
- Self-leaded construction under body termination



Features

- Very high rated current
- Extremely low DC resistance
- Very low profile and smallest possible footprint
- Suitable for pick and place processes

Applications

- Energy storage chokes for
 - DC/DC converters
 - VRM modules
 - POL converters

Terminals

- Pure tin (Pb-free)

Marking

EPCOS. ordering code, inductance,
date of manufacture (coded)


Delivery mode and packing unit

Blister tape 24 mm, reel 330 mm dia.


4.95 mm height = 750 pcs./reel

5.95 mm height = 550 pcs./reel

Dimensional drawing



Recommended PCB layout




General technical data and measuring conditions

Rated inductance L_R	Measured with Wayne-Kerr 3260A/3265B, measuring voltage 100 mV
Inductance tolerance	$\pm 10\%$
Saturation current I_{sat}	Current that will result in approx. 20% drop in inductance value. Temperature response needs to be verified in specific applications. Test results on request.
DC resistance	Measured at 20 °C ambient temperature
Solderability	235 °C, 5 s, wetting >90%
Operating temperature	-40 ... +130 °C
Weight	2.2 g (height = 4.95 mm), 2.6 g (height = 5.95 mm)

Characteristics and ordering codes

L_R	I_{sat}	R_{max}	Height h	Ordering code
μH	A	m Ω	mm	
0.50	30	1.1	4.95	B82559A0501A013
0.95	25	1.4	5.95	B82559A0951A013
1.1	20	2.2	4.95	B82559A0112A013
1.4	22	1.8	5.95	B82559A0142A013
2.2	15	4.2	4.95	B82559A0222A013
2.4	16.5	3.2	5.95	B82559A0242A013
3.0	13	5.1	4.95	B82559A0302A013
3.9	12	6.0	5.95	B82559A0392A013

Published by EPCOS AG
Corporate Communications, P.O. Box 80 17 09, 81617 Munich, GERMANY
☎ ++49 89 636 09, FAX (089) 636-2 26 89

© EPCOS AG 2004. Reproduction, publication and dissemination of this brochure and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.