

BCC connectors and cables
... for faster and simpler connectivity



more added value





With over 50 years of sensors experience, Balluff is a worldwide leading sensor specialist with our own line of connectivity products for every area of factory automation. With headquarters in Germany and 54 representatives and subsidiaries, Balluff is expertly represented on every continent in the world.

Balluff stands for comprehensive systems from a single source, continuous innovation, the most modern technology, highest quality and greatest reliability. And even more: for distinctive customer orientation, custom tailored solutions, fast worldwide service and outstanding applications assistance. In short: for reliable, expert partnership.

Whether electronic and mechanical sensors, rotary and linear transducers, identification systems or optimized connectivity solutions for high-performance automation, Balluff masters not only the entire technological variety with all the operating principles, but also offers innovative technology and the most modern electronics – tested down to the last detail in the company's own accredited testing laboratory and manufactured according to DIN ISO 9001 (EN 29001). Balluff technology can be used anywhere in the world, since it meets even regional quality standards. And Balluff technology is available internationally. So there is always a Balluff expert near you.

Balluff products increase throughput, quality and productivity day in and day out. They create the prerequisites for meeting the demands of the global market when it comes to greater performance and cost reduction. Including in the most demanding areas. No matter how stringent your requirements may be, Balluff provides solutions at the latest state of the art.

Fully exploit the potential of high quality. And profit from easy, quick setup with connectors and cables: the best possible connection for high efficiency.



more added value

- High protection rating: IP 67 guaranteed
- High shock and vibration ratings
- Easy, quick connection



Faster, simpler connection
Clearly visible markings on the grip for ease of orientation. The special BCC tool allows you to screw on the connector or set the tightening torque on the hex.

Highly visible LEDs
The LEDs are clearly visible from various directions, even under difficult lighting conditions.



Principles 4

M8 connectors	3-pin	male	8
	4-pin	male	10
	3-pin	female	9
	4-pin	female	11
Cables M8 ↔ M8	3-pin	female/male	12
	4-pin	female/male	14
Cables M8 ↔ M12	3-pin	female/male	16
	4-pin	female/male	18
M12 connectors	3-pin	male	20
	4-pin	male	26
	3-pin	female	22
	4-pin	female	28
Cables M12 ↔ M8	3-pin	female/male	32
	4-pin	female/male	36
Cables M12 ↔ M12	3-pin	female/male	38
	4-pin	female/male	40

	Materials	Use and characteristics
Metals	CuZn Brass	Standard housing material with surface protection.
	Stainless steel	Excellent corrosion resistance and strength. <u>Quality 1.4034, 1.4104</u> : Standard material. <u>Quality 1.4305, 1.4301</u> : Standard material for foods industry. <u>Quality 1.4401, 1.4404, 1.4571</u> : For foods industry with higher requirements for chemical resistance at elevated temperatures.
Plastics	PUR Polyurethane	Elastic, abrasion-resistant, impact-resistant. Good resistance to oils, greases, solvents (used for gaskets and cable jackets).
	PUR Cable material	Drag chain compatible, flame resistance per IEC 332-2, halogen-free per IEC 60754-1, cable construction per UL-AWM Style 21198.
	PVC Polyvinylchloride	Good mechanical strength and chemical resistance (cable).
	FPK (Viton)	Seal material with high thermal and chemical resistance
Other	TPE Thermoplastic elastomers	A thermoplastic mixture that combines the best properties of PVC and rubber insulation. Resistant to oils, chemicals, acids, solvents and weld splatter.
Insulation class	II 	EN 60947-5-2/IEC 60947-5-2
Enclosure rating	IP 60...67	EN 60529/IEC 60529
	IP 68 per BWN Pr. 20	Balluff Factory Standard (BWN): Continuous temperature 48 h at 60 °C, 8 temperature cycles per EN 60068-2-14/IEC 60068-2-14 between the reference temperatures according to data sheet, 1 h in water, insulation test, 24 h in water, insulation test, 8 temperature cycles per EN 60068-2-14/IEC 60068-2-14 between the reference temperatures according to data sheet, 7 days in water, insulation test.
	IP 68 per BWN Pr. 27	Balluff Factory Standard (BWN): Testing products for use in the foods industry.
	IP 69K	DIN 40050 Part 9 Protection against ingress of water at high pressure and steam cleaning.

Quality Management System
in accordance with
DIN EN ISO 9001:2000

Balluff Companies	
Balluff GmbH	Germany
Balluff Elektronika Kft	Hungary
Nihon Balluff Com. Ltd.	Japan
Balluff U.K. Ltd.	Great Britain
Balluff Automation s.r.l.	Italy
Balluff Inc.	USA
Gebhard Balluff Vetriebsgmbh	Austria
Balluff CZ	Czech Republic
Hy-Tech AG	Switzerland
Balluff Sensortechnik AG	Switzerland
Balluff Controles Elétricos Ltda.	Brazil

Environmental
Management System
per DIN EN ISO 14001:2005

Balluff Companies	
Balluff GmbH	Germany
Balluff Elektronika Kft	Hungary

Testing Laboratory

The Balluff testing laboratory works in accordance with ISO/IEC 17025 and is accredited by the DATech for Testing of Electromagnetic Compatibility (EMC).

Balluff products
meet the EU Directives

Products requiring marking are subjected to a conformity evaluation process according to the EU Directive and the product is marked with the CE Marking. Balluff products fall under the following EU Directives:

2004/108/EC	EMC Directive
2006/95/EC	Low-Voltage Directive applies to AC and AC/DC sensors
94/9/EC	ATEX Directive applies to products having the Ex marking

Approvals

... are granted by national and international institutions. Their symbols affirm that our products meet the specifications of these institutions.
"US Safety System" and "Canadian Standards Association" under the auspices of Underwriters Laboratories Inc. (cUL).

CCC Marking by the Chinese CQC.

Balluff is a member of
ALPHA

ALPHA, an association for testing and certification of low-voltage devices, promotes the individual responsibility of the manufacturer of such devices by means of uniform test procedures according to current standards and thereby supports the attainment of high product quality. ALPHA also grants nationally recognized product certificates when certain prerequisites are met. Through ALPHA's membership in LOVAG (Low Voltage Agreement Group), its certificates are also recognized in other European countries.




Connectors and Cables

Cable Types, Tightening Torque, Wire Colors

Cable types	PUR cable, PUR jacketed		
	No. of conductors × cross-section (mm²)	Outside diameter typ. (mm)	
	3×0.34	4.3...5.1	
	3×0.50	4.5...4.7	
	4×0.34	4.7...5.5	
	PVC cable, PVC jacketed		
	No. of conductors × cross-section (mm²)	Outside diameter typ. (mm)	
	3×0.34	4.9...5.0	
	3×0.50	4.7...5.0	
	4×0.34	4.8...5.0	
Least bending radius		tensioned	untensioned
	PUR	10×D	5×D
	PVC	15×D	8×D
	PUR shielded	10×D	5×D
	PVC shielded	15×D	8×D
Bending cycles and drag chain compatibility for PUR materials	> 10×D	> 2 mil.	
	Vertical travel permitted	at 5 m/sec² 2 m	
	Horizontal travel permitted	at 5 m/sec² 5 m	
Tightening torques	Permissible tightening torque for connectors		
	M8	0.4 Nm	
	M12	0.6 Nm	
	7/8"	1.5 Nm	
Wire colors	BN	brown	
	BK	black	
	BU	blue	
	WH	white	



Connectors and Cables

Dimensions



M8-male straight and right-angle,
3-pin, no LED




M8



Operating voltage max. AC U _B	60 V AC	60 V AC
Operating voltage max. DC U _B	60 V DC	60 V DC
Cable	Molded-on	Molded-on
No. of wires × cross-section	3×0.34mm ²	3×0.34mm ²
Enclosure rating per IEC 60529	IP 67	IP 67
Ambient temperature T _a	PUR	-25 °C...+80 °C
	PUR shielded	-25 °C...+80 °C
	PVC	-5 °C...+80 °C
	PVC shielded	-5 °C...+80 °C
Version	Normally open	Normally open
LED	LED	LED




Cable material	Color	Length	Ordering code	
			Part number	
PUR	black	2 m	BCC02M2	BCC02M5
			BCC M313-0000-20-001-PX0334-020	BCC M323-0000-20-001-PX0334-020
PUR	black	5 m	BCC02M3	BCC02M6
			BCC M313-0000-20-001-PX0334-050	BCC M323-0000-20-001-PX0334-050
PUR	black	10 m	BCC02M4	BCC02M7
			BCC M313-0000-20-001-PX0334-100	BCC M323-0000-20-001-PX0334-100
PUR shielded	black	2 m		
PUR shielded	black	5 m		
PUR shielded	black	10 m		
PVC	gray	2 m	BCC02NL	BCC02NP
PVC	gray	5 m	BCC02NM	BCC02NR
PVC	gray	10 m	BCC02NN	BCC02NT
PVC shielded	gray	2 m		
PVC shielded	gray	5 m		
PVC shielded	gray	10 m		

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Please visit www.balluff.com for more details





M8-female straight and right-angle,
3-pin, with and without LED



1) LED green = Power
2) LED yellow = Switching output

60 V AC	60 V AC	
60 V DC	60 V DC	30 V DC
Molded-on	Molded-on	Molded-on
3x0.34mm ²	3x0.34mm ²	3x0.34mm ²
IP 67	IP 67	IP 67
-25 °C...+80 °C	-25 °C...+80 °C	-25 °C...+80 °C
-25 °C...+80 °C	-25 °C...+80 °C	
-5 °C...+80 °C	-5 °C...+80 °C	-5 °C...+80 °C
-5 °C...+80 °C	-5 °C...+80 °C	
Normally open 	Normally open 	PNP-Normally open 
		green/yellow

Ordering code		
Part number		
BCC02M8	BCC02ML	BCC02MH
BCC M313-0000-10-001-PX0334-020	BCC M323-0000-10-001-PX0334-020	BCC M323-0000-10-004-PX0334-020
BCC02M9	BCC02MM	BCC02MJ
BCC M313-0000-10-001-PX0334-050	BCC M323-0000-10-001-PX0334-050	BCC M323-0000-10-004-PX0334-050
BCC02MA	BCC02MN	BCC02MK
BCC M313-0000-10-001-PX0334-100	BCC M323-0000-10-001-PX0334-100	BCC M323-0000-10-004-PX0334-100
BCC02MC	BCC02MP	
BCC M313-0000-10-036-PS0334-020	BCC M323-0000-10-036-PS0334-020	
BCC02ME	BCC02MR	
BCC M313-0000-10-036-PS0334-050	BCC M323-0000-10-036-PS0334-050	
BCC02MF	BCC02MT	
BCC M313-0000-10-036-PS0334-100	BCC M323-0000-10-036-PS0334-100	
BCC02NU	BCC02P5	BCC02P2
BCC M313-0000-10-001-VX8334-020	BCC M323-0000-10-001-VX8334-020	BCC M323-0000-10-004-VX8334-020
BCC02NW	BCC02P6	BCC02P3
BCC M313-0000-10-001-VX8334-050	BCC M323-0000-10-001-VX8334-050	BCC M323-0000-10-004-VX8334-050
BCC02NY	BCC02P7	BCC02P4
BCC M313-0000-10-001-VX8334-100	BCC M323-0000-10-001-VX8334-100	BCC M323-0000-10-004-VX8334-100
BCC02NZ	BCC02P8	
BCC M313-0000-10-036-VS8334-020	BCC M323-0000-10-036-VS8334-020	
BCC02P0	BCC02P9	
BCC M313-0000-10-036-VS8334-050	BCC M323-0000-10-036-VS8334-050	
BCC02P1	BCC02PA	
BCC M313-0000-10-036-VS8334-100	BCC M323-0000-10-036-VS8334-100	



■ www.balluff.com

BALLUFF | 9

18





M8

Connectors

M8-male straight and right-angle, 4-pin, no LED





Connector diagram and wiring



Operating voltage max. AC U _B	30 V AC	30 V AC
Operating voltage max. DC U _B	30 V DC	30 V DC
Cable	Molded-on	Molded-on
No. of wires × cross-section	4×0.34mm ²	4×0.34mm ²
Enclosure rating per IEC 60529	IP 67	IP 67
Ambient temperature T _a	PUR -25 °C...+80 °C	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C	PVC -5 °C...+80 °C
	PVC shielded	
Version	Complementary (NO/NC) /- / -/	Complementary (NO/NC) /- / -/
LED		




Cable material	Color	Length	Ordering code
PUR	black	2 m	BCC02MU BCC M314-0000-20-003-PX0434-020
PUR	black	5 m	BCC02MW BCC M314-0000-20-003-PX0434-050
PUR	black	10 m	BCC02MY BCC M314-0000-20-003-PX0434-100
PUR shielded	black	2 m	
PUR shielded	black	5 m	
PUR shielded	black	10 m	
PVC	gray	2 m	BCC02PC BCC M314-0000-20-003-VX8434-020
PVC	gray	5 m	BCC02PE BCC M314-0000-20-003-VX8434-050
PVC	gray	10 m	BCC02PF BCC M314-0000-20-003-VX8434-100
PVC shielded	gray	2 m	
PVC shielded	gray	5 m	
PVC shielded	gray	10 m	

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.






Connectors

M8-female straight and right-angle, 4-pin, with and without LED




Operating voltage max. AC U _B	30 V AC	30 V AC	30 V DC
Operating voltage max. DC U _B	30 V DC	30 V DC	30 V DC
Cable	Molded-on	Molded-on	Molded-on
No. of wires × cross-section	4×0.34mm ²	4×0.34mm ²	4×0.34mm ²
Enclosure rating per IEC 60529	IP 67	IP 67	IP 67
Ambient temperature T _a	-25 °C...+80 °C	-25 °C...+80 °C	-25 °C...+80 °C
	-25 °C...+80 °C	-25 °C...+80 °C	-5 °C...+80 °C
	-5 °C...+80 °C	-5 °C...+80 °C	
	-5 °C...+80 °C		
Version	Complementary (NO/NC) /- / -/	Complementary (NO/NC) /- / -/	PNP-complementary (NO/NC) /- / -/
LED			green/yellow


Ordering code	Ordering code	Ordering code
BCC02N2 BCC M314-0000-10-003-PX0434-020	BCC02NC BCC M324-0000-10-003-PX0434-020	BCC02N8 BCC M324-0000-10-008-PX0434-020
BCC02N3 BCC M314-0000-10-003-PX0434-050	BCC02NE BCC M324-0000-10-003-PX0434-050	BCC02N9 BCC M324-0000-10-008-PX0434-050
BCC02N4 BCC M314-0000-10-003-PX0434-100	BCC02NF BCC M324-0000-10-003-PX0434-100	BCC02NA BCC M324-0000-10-008-PX0434-100
BCC02N5 BCC M314-0000-10-014-PS0434-020	BCC02NH BCC M324-0000-10-014-PS0434-020	
BCC02N6 BCC M314-0000-10-014-PS0434-050	BCC02NJ BCC M324-0000-10-014-PS0434-050	
BCC02N7 BCC M314-0000-10-014-PS0434-100	BCC02NK BCC M324-0000-10-014-PS0434-100	
BCC02PL BCC M314-0000-10-003-VX8434-020	BCC02PZ BCC M324-0000-10-003-VX8434-020	BCC02PU BCC M324-0000-10-008-VX8434-020
BCC02PM BCC M314-0000-10-003-VX8434-050	BCC02R0 BCC M324-0000-10-003-VX8434-050	BCC02PW BCC M324-0000-10-008-VX8434-050
BCC02PN BCC M314-0000-10-003-VX8434-100	BCC02R1 BCC M324-0000-10-003-VX8434-100	BCC02PY BCC M324-0000-10-008-VX8434-100
BCC02PP BCC M314-0000-10-014-VS8434-020	BCC02R2 BCC M324-0000-10-014-VS8434-020	
BCC02PR BCC M314-0000-10-014-VS8434-050	BCC02R3 BCC M324-0000-10-014-VS8434-050	
BCC02PT BCC M314-0000-10-014-VS8434-100	BCC02R4 BCC M324-0000-10-014-VS8434-100	




M8-female straight ↔ M8-male straight
or right-angle, 4-pin, no LED




Operating voltage max. AC U _B	30 V AC
Operating voltage max. DC U _B	30 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 67
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded PVC -5 °C...+80 °C
	PVC shielded
Version	Complementary (NO/NC)  / 
LED	




30 V AC
30 V DC
Molded-on
4x0.34mm²
IP 67
-25 °C...+80 °C
-5 °C...+80 °C
Complementary (NO/NC)  / 



30 V AC
30 V DC
Molded-on
4x0.34mm²
IP 67
-25 °C...+80 °C
-5 °C...+80 °C
Complementary (NO/NC)  / 



30 V AC
30 V DC
Molded-on
4x0.34mm²
IP 67
-25 °C...+80 °C
-5 °C...+80 °C
Complementary (NO/NC)  / 








30 V DC
Molded-on
4×0.34mm²
IP 67
-25 °C...+80 °C
-5 °C...+80 °C
PNP-complementary (NO/NC) $\swarrow$ / $\searrow$
green/yellow

M8 ↔ M8

M8-female right-angle ↔ M8-male straight
or right-angle, 4-pin, with and without LED

Cable material	Color	Length	Ordering code			Ordering code		
			Part number			Part number		
PUR	black	0.3 m	BCC02TF	BCC02TP		BCC02UH	BCC02U7	BCC02U0
			BCC M314-M314-30-304-PX0434-003	BCC M314-M324-30-304-PX0434-003		BCC M324-M324-30-304-PX0434-003	BCC M324-M314-30-304-PX0434-003	BCC M324-M314-30-606-PX0434-003
PUR	black	0.6 m	BCC02TH	BCC02TR		BCC02UJ	BCC02U8	BCC02U1
			BCC M314-M314-30-304-PX0434-006	BCC M314-M324-30-304-PX0434-006		BCC M324-M324-30-304-PX0434-006	BCC M324-M314-30-304-PX0434-006	BCC M324-M314-30-606-PX0434-006
PUR	black	1 m	BCC02TJ	BCC02TT		BCC02UK	BCC02U9	BCC02U2
			BCC M314-M314-30-304-PX0434-010	BCC M314-M324-30-304-PX0434-010		BCC M324-M324-30-304-PX0434-010	BCC M324-M314-30-304-PX0434-010	BCC M324-M314-30-606-PX0434-010
PUR	black	1.5 m	BCC02TK	BCC02TU		BCC02UL	BCC02UA	BCC02U3
			BCC M314-M314-30-304-PX0434-015	BCC M314-M324-30-304-PX0434-015		BCC M324-M324-30-304-PX0434-015	BCC M324-M314-30-304-PX0434-015	BCC M324-M314-30-606-PX0434-015
PUR	black	2 m	BCC02TL	BCC02TW		BCC02UM	BCC02UC	BCC02U4
			BCC M314-M314-30-304-PX0434-020	BCC M314-M324-30-304-PX0434-020		BCC M324-M324-30-304-PX0434-020	BCC M324-M314-30-304-PX0434-020	BCC M324-M314-30-606-PX0434-020
PUR	black	3 m	BCC02TM	BCC02TY		BCC02UN	BCC02UE	BCC02U5
			BCC M314-M314-30-304-PX0434-030	BCC M314-M324-30-304-PX0434-030		BCC M324-M324-30-304-PX0434-030	BCC M324-M314-30-304-PX0434-030	BCC M324-M314-30-606-PX0434-030
PUR	black	5 m	BCC02TN	BCC02TZ		BCC02UP	BCC02UF	BCC02U6
			BCC M314-M314-30-304-PX0434-050	BCC M314-M324-30-304-PX0434-050		BCC M324-M324-30-304-PX0434-050	BCC M324-M314-30-304-PX0434-050	BCC M324-M314-30-606-PX0434-050
PVC	gray	0.3 m	BCC02Y2	BCC02Y9		BCC02Z3	BCC02YU	BCC02YK
			BCC M314-M314-30-304-VX8434-003	BCC M314-M324-30-304-VX8434-003		BCC M324-M324-30-304-VX8434-003	BCC M324-M314-30-304-VX8434-003	BCC M324-M314-30-606-VX8434-003
PVC	gray	0.6 m	BCC02Y3	BCC02YA		BCC02Z4	BCC02YW	BCC02YL
			BCC M314-M314-30-304-VX8434-006	BCC M314-M324-30-304-VX8434-006		BCC M324-M324-30-304-VX8434-006	BCC M324-M314-30-304-VX8434-006	BCC M324-M314-30-606-VX8434-006
PVC	gray	1 m	BCC02Y4	BCC02YC		BCC02Z5	BCC02YY	BCC02YM
			BCC M314-M314-30-304-VX8434-010	BCC M314-M324-30-304-VX8434-010		BCC M324-M324-30-304-VX8434-010	BCC M324-M314-30-304-VX8434-010	BCC M324-M314-30-606-VX8434-010
PVC	gray	1.5 m	BCC02Y5	BCC02YE		BCC02Z6	BCC02YZ	BCC02YN
			BCC M314-M314-30-304-VX8434-015	BCC M314-M324-30-304-VX8434-015		BCC M324-M324-30-304-VX8434-015	BCC M324-M314-30-304-VX8434-015	BCC M324-M314-30-606-VX8434-015
PVC	gray	2 m	BCC02Y6	BCC02YF		BCC02Z7	BCC02Z0	BCC02YP
			BCC M314-M314-30-304-VX8434-020	BCC M314-M324-30-304-VX8434-020		BCC M324-M324-30-304-VX8434-020	BCC M324-M314-30-304-VX8434-020	BCC M324-M314-30-606-VX8434-020
PVC	gray	3 m	BCC02Y7	BCC02YH		BCC02Z8	BCC02Z1	BCC02YR
			BCC M314-M314-30-304-VX8434-030	BCC M314-M324-30-304-VX8434-030		BCC M324-M324-30-304-VX8434-030	BCC M324-M314-30-304-VX8434-030	BCC M324-M314-30-606-VX8434-030
PVC	gray	5 m	BCC02Y8	BCC02YJ		BCC02Z9	BCC02Z2	BCC02YT
			BCC M314-M314-30-304-VX8434-050	BCC M314-M324-30-304-VX8434-050		BCC M324-M324-30-304-VX8434-050	BCC M324-M314-30-304-VX8434-050	BCC M324-M314-30-606-VX8434-050

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.








Connection cable

M8-female straight ↔ M12-male straight
or right-angle, 4-pin, no LED

M8 ↔ M12


Connection cable

M8-female right-angle ↔ M12-male straight
or right-angle, 4-pin, with and without LED

						
Connector diagram and wiring						
Operating voltage max. AC U _B		30 V AC	30 V AC	30 V AC	30 V AC	30 V DC
Operating voltage max. DC U _B		30 V DC	30 V DC	30 V DC	30 V DC	30 V DC
Cable		Molded-on	Molded-on	Molded-on	Molded-on	Molded-on
No. of wires × cross-section		4×0.34mm ²	4×0.34mm ²	4×0.34mm ²	4×0.34mm ²	4×0.34mm ²
Enclosure rating per IEC 60529		IP 67	IP 67	IP 67	IP 67	IP 67
Ambient temperature T _a	PUR	−25 °C...+80 °C	−25 °C...+80 °C	−25 °C...+80 °C	−25 °C...+80 °C	−25 °C...+80 °C
	PUR shielded					
	PVC	−5 °C...+80 °C	−5 °C...+80 °C	−5 °C...+80 °C	−5 °C...+80 °C	−5 °C...+80 °C
	PVC shielded					
Version		Complementary (NO/NC)  / 	Complementary (NO/NC)  / 	Complementary (NO/NC)  / 	Complementary (NO/NC)  / 	PNP-complementary (NO/NC)  / 
LED						green/yellow

Cable material	Color	Length	Ordering code			Ordering code			
			Part number			Part number			
PUR	black	0.3 m	BCC03JP BCC M314-M414-3E-304-PX0434-003	BCC03K0 BCC M314-M424-3E-304-PX0434-003		BCC03KH BCC M324-M424-3E-304-PX0434-003	BCC03K7 BCC M324-M414-3E-304-PX0434-003	BCC03KR BCC M324-M414-3E-606-PX0434-003	
PUR	black	0.6 m	BCC03JR BCC M314-M414-3E-304-PX0434-006	BCC03K1 BCC M314-M424-3E-304-PX0434-006		BCC03KJ BCC M324-M424-3E-304-PX0434-006	BCC03K8 BCC M324-M414-3E-304-PX0434-006	BCC03KT BCC M324-M414-3E-606-PX0434-006	
PUR	black	1 m	BCC03JT BCC M314-M414-3E-304-PX0434-010	BCC03K2 BCC M314-M424-3E-304-PX0434-010		BCC03KK BCC M324-M424-3E-304-PX0434-010	BCC03K9 BCC M324-M414-3E-304-PX0434-010	BCC03KU BCC M324-M414-3E-606-PX0434-010	
PUR	black	1.5 m	BCC03JU BCC M314-M414-3E-304-PX0434-015	BCC03K3 BCC M314-M424-3E-304-PX0434-015		BCC03KL BCC M324-M424-3E-304-PX0434-015	BCC03KA BCC M324-M414-3E-304-PX0434-015	BCC03KW BCC M324-M414-3E-606-PX0434-015	
PUR	black	2 m	BCC03JW BCC M314-M414-3E-304-PX0434-020	BCC03K4 BCC M314-M424-3E-304-PX0434-020		BCC03KM BCC M324-M424-3E-304-PX0434-020	BCC03KC BCC M324-M414-3E-304-PX0434-020	BCC03KY BCC M324-M414-3E-606-PX0434-020	
PUR	black	3 m	BCC03JY BCC M314-M414-3E-304-PX0434-030	BCC03K5 BCC M314-M424-3E-304-PX0434-030		BCC03KN BCC M324-M424-3E-304-PX0434-030	BCC03KE BCC M324-M414-3E-304-PX0434-030	BCC03KZ BCC M324-M414-3E-606-PX0434-030	
PUR	black	5 m	BCC03JZ BCC M314-M414-3E-304-PX0434-050	BCC03K6 BCC M314-M424-3E-304-PX0434-050		BCC03KP BCC M324-M424-3E-304-PX0434-050	BCC03KF BCC M324-M414-3E-304-PX0434-050	BCC03L0 BCC M324-M414-3E-606-PX0434-050	
PVC	gray	0.3 m	BCC03L1 BCC M314-M414-3E-304-VX8434-003	BCC03L8 BCC M314-M424-3E-304-VX8434-003		BCC03LT BCC M324-M424-3E-304-VX8434-003	BCC03LJ BCC M324-M414-3E-304-VX8434-003	BCC03M2 BCC M324-M414-3E-606-VX8434-003	
PVC	gray	0.6 m	BCC03L2 BCC M314-M414-3E-304-VX8434-006	BCC03L9 BCC M314-M424-3E-304-VX8434-006		BCC03LU BCC M324-M424-3E-304-VX8434-006	BCC03LK BCC M324-M414-3E-304-VX8434-006	BCC03M3 BCC M324-M414-3E-606-VX8434-006	
PVC	gray	1 m	BCC03L3 BCC M314-M414-3E-304-VX8434-010	BCC03LA BCC M314-M424-3E-304-VX8434-010		BCC03LW BCC M324-M424-3E-304-VX8434-010	BCC03LL BCC M324-M414-3E-304-VX8434-010	BCC03M4 BCC M324-M414-3E-606-VX8434-010	
PVC	gray	1.5 m	BCC03L4 BCC M314-M414-3E-304-VX8434-015	BCC03LC BCC M314-M424-3E-304-VX8434-015		BCC03LY BCC M324-M424-3E-304-VX8434-015	BCC03LM BCC M324-M414-3E-304-VX8434-015	BCC03M5 BCC M324-M414-3E-606-VX8434-015	
PVC	gray	2 m	BCC03L5 BCC M314-M414-3E-304-VX8434-020	BCC03LE BCC M314-M424-3E-304-VX8434-020		BCC03LZ BCC M324-M424-3E-304-VX8434-020	BCC03LN BCC M324-M414-3E-304-VX8434-020	BCC03M6 BCC M324-M414-3E-606-VX8434-020	
PVC	gray	3 m	BCC03L6 BCC M314-M414-3E-304-VX8434-030	BCC03LF BCC M314-M424-3E-304-VX8434-030		BCC03M0 BCC M324-M424-3E-304-VX8434-030	BCC03LP BCC M324-M414-3E-304-VX8434-030	BCC03M7 BCC M324-M414-3E-606-VX8434-030	
PVC	gray	5 m	BCC03L7 BCC M314-M414-3E-304-VX8434-050	BCC03LH BCC M314-M424-3E-304-VX8434-050		BCC03M1 BCC M324-M424-3E-304-VX8434-050	BCC03LR BCC M324-M414-3E-304-VX8434-050	BCC03M8 BCC M324-M414-3E-606-VX8434-050	

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Please visit www.balluff.com for more details

M8 ↔ M12





M12

Connectors

M12-male straight,
3-pin, no LED





Connector diagram and wiring



Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally open
LED	


Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally open
LED	

Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally closed
LED	



Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally open
LED	











Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally closed
LED	



Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	PNP-Normally open
LED	green/yellow

Cable material	Color	Length	Ordering code
PUR	black	2 m	BCC022A
PUR	black	5 m	BCC022C
PUR	black	10 m	BCC022E
PUR shielded	black	2 m	BCC022K
PUR shielded	black	5 m	BCC022L
PUR shielded	black	10 m	BCC022M
PVC	gray	2 m	BCC0334
PVC	gray	5 m	BCC0335
PVC	gray	10 m	BCC0336
PVC shielded	gray	2 m	BCC033A
PVC shielded	gray	5 m	BCC033C
PVC shielded	gray	10 m	BCC033E

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Connectors



M12-male right-angle,
3-pin, with and without LED

Connectors

M12-female straight, 3-pin, no LED



Connector diagram and wiring







Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally open
LED	

Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally open
LED	

Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Normally closed
LED	



Cable material	Color	Length	Ordering code
			Part number
PUR	black	2 m	BCC030K
			BCC M415-0000-1A-001-PX0334-020
PUR	black	5 m	BCC030L
			BCC M415-0000-1A-001-PX0334-050
PUR	black	10 m	BCC030M
			BCC M415-0000-1A-001-PX0334-100
PUR shielded	black	2 m	BCC030T
			BCC M415-0000-1A-036-PS0334-020
PUR shielded	black	5 m	BCC030U
			BCC M415-0000-1A-036-PS0334-050
PUR shielded	black	10 m	BCC030W
			BCC M415-0000-1A-036-PS0334-100
PVC	gray	2 m	BCC034A
			BCC M415-0000-1A-001-VX8334-020
PVC	gray	5 m	BCC034C
			BCC M415-0000-1A-001-VX8334-050
PVC	gray	10 m	BCC034E
			BCC M415-0000-1A-001-VX8334-100
PVC shielded	gray	2 m	BCC034K
			BCC M415-0000-1A-036-VS8334-020
PVC shielded	gray	5 m	BCC034L
			BCC M415-0000-1A-036-VS8334-050
PVC shielded	gray	10 m	BCC034M
			BCC M415-0000-1A-036-VS8334-100

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Connectors





M12-female straight, 3-pin, with LED



Operating voltage max. AC U _B	30 V DC
Operating voltage max. DC U _B	30 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	-25 °C...+80 °C
	-5 °C...+80 °C
Version	PNP-Normally open
LED	green/yellow

Operating voltage max. AC U _B	30 V DC
Operating voltage max. DC U _B	30 V DC
Cable	Molded-on
No. of wires × cross-section	3×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	-25 °C...+80 °C
	-5 °C...+80 °C
Version	PNP Normally closed
LED	green/yellow

Ordering code	Ordering code
Part number	Part number
BCC030A	BCC030F
BCC M415-0000-1A-004-PX0334-020	BCC M415-0000-1A-005-PX0334-020
BCC030C	BCC030H
BCC M415-0000-1A-004-PX0334-050	BCC M415-0000-1A-005-PX0334-050
BCC030E	BCC030J
BCC M415-0000-1A-004-PX0334-100	BCC M415-0000-1A-005-PX0334-100
BCC0344	BCC0347
BCC M415-0000-1A-004-VX8334-020	BCC M415-0000-1A-005-VX8334-020
BCC0345	BCC0348
BCC M415-0000-1A-004-VX8334-050	BCC M415-0000-1A-005-VX8334-050
BCC0346	BCC0349
BCC M415-0000-1A-004-VX8334-100	BCC M415-0000-1A-005-VX8334-100





Connectors

M12-female right-angle,
3-pin, no LED



Connector diagram and wiring





Operating voltage max. AC U_B
Operating voltage max. DC U_B
Cable
No. of wires $\times$ cross-section
Enclosure rating per IEC 60529
Ambient temperature T_a
PUR
PUR shielded
PVC
PVC shielded
Version
LED

250 V AC
250 V DC
Molded-on
3 $\times$ 0.34mm²
IP 68
-25 °C...+80 °C
-25 °C...+80 °C
-5 °C...+80 °C
-5 °C...+80 °C
Normally open

250 V AC
250 V DC
Molded-on
3 $\times$ 0.34mm²
IP 68
-25 °C...+80 °C
-25 °C...+80 °C
-5 °C...+80 °C
-5 °C...+80 °C
Normally closed


Cable material	Color	Length	Ordering code
PUR	black	2 m	BCC0317 BCC M425-0000-1A-001-PX0334-020
PUR	black	5 m	BCC0318 BCC M425-0000-1A-001-PX0334-050
PUR	black	10 m	BCC0319 BCC M425-0000-1A-001-PX0334-100
PUR shielded	black	2 m	BCC031F BCC M425-0000-1A-036-PS0334-020
PUR shielded	black	5 m	BCC031H BCC M425-0000-1A-036-PS0334-050
PUR shielded	black	10 m	BCC031J BCC M425-0000-1A-036-PS0334-100
PVC	gray	2 m	BCC0351 BCC M425-0000-1A-001-VX8334-020
PVC	gray	5 m	BCC0352 BCC M425-0000-1A-001-VX8334-050
PVC	gray	10 m	BCC0353 BCC M425-0000-1A-001-VX8334-100
PVC shielded	gray	2 m	BCC0357 BCC M425-0000-1A-036-VS8334-020
PVC shielded	gray	5 m	BCC0358 BCC M425-0000-1A-036-VS8334-050
PVC shielded	gray	10 m	BCC0359 BCC M425-0000-1A-036-VS8334-100

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Connectors



M12-female right-angle,
3-pin, with LED



30 V DC
Molded-on
3 $\times$ 0.34mm²
IP 68
-25 °C...+80 °C
-5 °C...+80 °C
PNP-Normally open
green/yellow

30 V DC
Molded-on
3 $\times$ 0.34mm²
IP 68
-25 °C...+80 °C
-5 °C...+80 °C
PNP Normally closed
green/yellow

Ordering code	Ordering code
BCC031A BCC M425-0000-1A-002-PX0334-020	BCC0311 BCC M425-0000-1A-004-PX0334-020
BCC031C BCC M425-0000-1A-002-PX0334-050	BCC0312 BCC M425-0000-1A-004-PX0334-050
BCC031E BCC M425-0000-1A-002-PX0334-100	BCC0313 BCC M425-0000-1A-004-PX0334-100
BCC031K BCC M425-0000-1A-037-PS0334-020	
BCC031L BCC M425-0000-1A-037-PS0334-050	
BCC031M BCC M425-0000-1A-037-PS0334-100	
BCC0354 BCC M425-0000-1A-002-VX8334-020	BCC034T BCC M425-0000-1A-004-VX8334-020
BCC0355 BCC M425-0000-1A-002-VX8334-050	BCC034U BCC M425-0000-1A-004-VX8334-050
BCC0356 BCC M425-0000-1A-002-VX8334-100	BCC034W BCC M425-0000-1A-004-VX8334-100
BCC035A BCC M425-0000-1A-037-VS8334-020	BCC034Y BCC M425-0000-1A-005-VX8334-020
BCC035C BCC M425-0000-1A-037-VS8334-050	BCC034Z BCC M425-0000-1A-005-VX8334-050
BCC035E BCC M425-0000-1A-037-VS8334-100	BCC0350 BCC M425-0000-1A-005-VX8334-100






Connectors

M12-male straight or right-angle,
4-pin, no LED



Connector diagram and wiring



Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	

Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	







Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	

Operating voltage max. AC U _B	30 V DC
Operating voltage max. DC U _B	30 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	-25 °C...+80 °C
	-5 °C...+80 °C
Version	PNP-complementary (NO/NC) /- / -/
LED	green/yellow

Cable material	Color	Length	Ordering code
			Part number
PUR	black	2 m	BCC031N
			BCC M414-0000-2A-003-PX0434-020
PUR	black	5 m	BCC031P
			BCC M414-0000-2A-003-PX0434-050
PUR	black	10 m	BCC031R
			BCC M414-0000-2A-003-PX0434-100
PUR shielded	black	2 m	BCC031T
			BCC M414-0000-2A-014-PS0434-020
PUR shielded	black	5 m	BCC031U
			BCC M414-0000-2A-014-PS0434-050
PUR shielded	black	10 m	BCC031W
			BCC M414-0000-2A-014-PS0434-100
PVC	gray	2 m	BCC035F
			BCC M414-0000-2A-003-VX8434-020
PVC	gray	5 m	BCC035H
			BCC M414-0000-2A-003-VX8434-050
PVC	gray	10 m	BCC035J
			BCC M414-0000-2A-003-VX8434-100
PVC shielded	gray	2 m	BCC035K
			BCC M414-0000-2A-014-VS8434-020
PVC shielded	gray	5 m	BCC035L
			BCC M414-0000-2A-014-VS8434-050
PVC shielded	gray	10 m	BCC035M
			BCC M414-0000-2A-014-VS8434-100

Ordering code
Part number
BCC0321
BCC M424-0000-2A-003-PX0434-020
BCC0322
BCC M424-0000-2A-003-PX0434-050
BCC0323
BCC M424-0000-2A-003-PX0434-100
BCC0324
BCC M424-0000-2A-014-PS0434-020
BCC0325
BCC M424-0000-2A-014-PS0434-050
BCC0326
BCC M424-0000-2A-014-PS0434-100
BCC035T
BCC M424-0000-2A-003-VX8434-020
BCC035U
BCC M424-0000-2A-003-VX8434-050
BCC035W
BCC M424-0000-2A-003-VX8434-100
BCC035Y
BCC M424-0000-2A-014-VS8434-020
BCC035Z
BCC M424-0000-2A-014-VS8434-050
BCC0360
BCC M424-0000-2A-014-VS8434-100

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Connectors

M12-male right-angle,
4-pin, with LED






Connectors

M12-female straight, 4-pin, with and without LED


Connectors

M12-female straight, 4-pin, with LED

Connector diagram and wiring				
Operating voltage max. AC U _B	250 V AC	30 V DC		30 V DC
Operating voltage max. DC U _B	250 V DC	Molded-on		Molded-on
Cable	Molded-on	4x0.34mm ²		4x0.34mm ²
No. of wires × cross-section	4x0.34mm ²	IP 68		IP 68
Enclosure rating per IEC 60529	IP 68	–25 °C...+80 °C		–25 °C...+80 °C
Ambient temperature T _a	PUR	–25 °C...+80 °C		–25 °C...+80 °C
	PUR shielded	–5 °C...+80 °C		–5 °C...+80 °C
	PVC	–5 °C...+80 °C		–5 °C...+80 °C
	PVC shielded	–5 °C...+80 °C		–5 °C...+80 °C
Version	Complementary (NO/NC)  / 	PNP-complementary (NO/NC)  / 		PNP-complementary (NO/NC)  / 
LED		green/yellow		green/yellow/white

Cable material	Color	Length	Ordering code		Ordering code
			Part number		Part number
PUR	black	2 m	BCC032F	BCC0327	BCC032A
			BCC M415-0000-1A-003-PX0434-020	BCC M415-0000-1A-008-PX0434-020	BCC M415-0000-1A-010-PX0434-020
PUR	black	5 m	BCC032H	BCC0328	BCC032C
			BCC M415-0000-1A-003-PX0434-050	BCC M415-0000-1A-008-PX0434-050	BCC M415-0000-1A-010-PX0434-050
PUR	black	10 m	BCC032J	BCC0329	BCC032E
			BCC M415-0000-1A-003-PX0434-100	BCC M415-0000-1A-008-PX0434-100	BCC M415-0000-1A-010-PX0434-100
PUR shielded	black	2 m	BCC032K		
			BCC M415-0000-1A-014-PS0434-020		
PUR shielded	black	5 m	BCC032L		
			BCC M415-0000-1A-014-PS0434-050		
PUR shielded	black	10 m	BCC032M		
			BCC M415-0000-1A-014-PS0434-100		
PVC	gray	2 m	BCC0367	BCC0361	BCC0364
			BCC M415-0000-1A-003-VX8434-020	BCC M415-0000-1A-008-VX8434-020	BCC M415-0000-1A-010-VX8434-020
PVC	gray	5 m	BCC0368	BCC0362	BCC0365
			BCC M415-0000-1A-003-VX8434-050	BCC M415-0000-1A-008-VX8434-050	BCC M415-0000-1A-010-VX8434-050
PVC	gray	10 m	BCC0369	BCC0363	BCC0366
			BCC M415-0000-1A-003-VX8434-100	BCC M415-0000-1A-008-VX8434-100	BCC M415-0000-1A-010-VX8434-100
PVC shielded	gray	2 m	BCC036A		
			BCC M415-0000-1A-014-VS8434-020		
PVC shielded	gray	5 m	BCC036C		
			BCC M415-0000-1A-014-VS8434-050		
PVC shielded	gray	10 m	BCC036E		
			BCC M415-0000-1A-014-VS8434-100		

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.






Connectors

M12-female right-angle,
4-pin, with and without LED



Connector diagram and wiring



Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -25 °C...+80 °C
	PVC -5 °C...+80 °C
	PVC shielded -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	

250 V AC
250 V DC
Molded-on
4×0.34mm ²
IP 68
-25 °C...+80 °C
-25 °C...+80 °C
-5 °C...+80 °C
-5 °C...+80 °C

30 V DC
Molded-on
4×0.34mm ²
IP 68
-25 °C...+80 °C
-5 °C...+80 °C




30 V DC
Molded-on
4×0.34mm ²
IP 68
-25 °C...+80 °C
-5 °C...+80 °C

PNP-complementary (NO/NC) /- / -/ green/yellow

PNP-complementary (NO/NC) /- / -/ green/yellow/white

Cable material	Color	Length	Ordering code	Ordering code	Ordering code
			Part number		Part number
PUR	black	2 m	BCC032Y	BCC032N	BCC032T
			BCC M425-0000-1A-003-PX0434-020	BCC M425-0000-1A-008-PX0434-020	BCC M425-0000-1A-010-PX0434-020
PUR	black	5 m	BCC032Z	BCC032P	BCC032U
			BCC M425-0000-1A-003-PX0434-050	BCC M425-0000-1A-008-PX0434-050	BCC M425-0000-1A-010-PX0434-050
PUR	black	10 m	BCC0330	BCC032R	BCC032W
			BCC M425-0000-1A-003-PX0434-100	BCC M425-0000-1A-008-PX0434-100	BCC M425-0000-1A-010-PX0434-100
PUR shielded	black	2 m	BCC0331		
			BCC M425-0000-1A-014-PS0434-020		
PUR shielded	black	5 m	BCC0332		
			BCC M425-0000-1A-014-PS0434-050		
PUR shielded	black	10 m	BCC0333		
			BCC M425-0000-1A-014-PS0434-100		
PVC	gray	2 m	BCC036N	BCC036F	BCC036K
			BCC M425-0000-1A-003-VX8434-020	BCC M425-0000-1A-008-VX8434-020	BCC M425-0000-1A-010-VX8434-020
PVC	gray	5 m	BCC036P	BCC036H	BCC036L
			BCC M425-0000-1A-003-VX8434-050	BCC M425-0000-1A-008-VX8434-050	BCC M425-0000-1A-010-VX8434-050
PVC	gray	10 m	BCC036R	BCC036J	BCC036M
			BCC M425-0000-1A-003-VX8434-100	BCC M425-0000-1A-008-VX8434-100	BCC M425-0000-1A-010-VX8434-100
PVC shielded	gray	2 m	BCC036T		
			BCC M425-0000-1A-014-VS8434-020		
PVC shielded	gray	5 m	BCC036U		
			BCC M425-0000-1A-014-VS8434-050		
PVC shielded	gray	10 m	BCC036W		
			BCC M425-0000-1A-014-VS8434-100		

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Connection cable

M12-female straight ↔ M8-male straight, 3-pin, or right-angle, no LED

M12 ↔ M8





Connection cable

M12-female right-angle ↔ M8-male right-angle, 3-pin, with and without LED

Connector diagram and wiring					
Operating voltage max. AC U _B	60 V AC	60 V AC	60 V AC	60 V AC	60 V AC
Operating voltage max. DC U _B	60 V DC	60 V DC	60 V DC	60 V DC	30 V DC
Cable	Molded-on	Molded-on	Molded-on	Molded-on	Molded-on
No. of wires × cross-section	3×0.34mm ²	3×0.34mm ²	3×0.34mm ²	3×0.34mm ²	3×0.34mm ²
Enclosure rating per IEC 60529	IP 67	IP 67	IP 67	IP 67	IP 67
Ambient temperature T _a	PUR -25 °C...+80 °C	PUR -25 °C...+80 °C	PUR -25 °C...+80 °C	PUR -25 °C...+80 °C	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C	PUR shielded -5 °C...+80 °C	PUR shielded -5 °C...+80 °C	PUR shielded -5 °C...+80 °C	PUR shielded -5 °C...+80 °C
	PVC shielded	PVC shielded	PVC shielded	PVC shielded	PVC shielded
Version	Normally open	Normally open	Normally open	Normally open	PNP-Normally open
LED	—	—	—	—	green/yellow

Cable material	Color	Length	Ordering code	Part number
PUR	black	0.3 m	BCC03M9	BCC M415-M313-3F-300-PX0334-003
PUR	black	0.6 m	BCC03MA	BCC M415-M313-3F-300-PX0334-006
PUR	black	1 m	BCC03MC	BCC M415-M313-3F-300-PX0334-010
PUR	black	1.5 m	BCC03ME	BCC M415-M313-3F-300-PX0334-015
PUR	black	2 m	BCC03MF	BCC M415-M313-3F-300-PX0334-020
PUR	black	3 m	BCC03MH	BCC M415-M313-3F-300-PX0334-030
PUR	black	5 m	BCC03MJ	BCC M415-M313-3F-300-PX0334-050
PVC	gray	0.3 m	BCC03NW	BCC M415-M313-3F-300-VX8334-003
PVC	gray	0.6 m	BCC03NY	BCC M415-M313-3F-300-VX8334-006
PVC	gray	1 m	BCC03NZ	BCC M415-M313-3F-300-VX8334-010
PVC	gray	1.5 m	BCC03P0	BCC M415-M313-3F-300-VX8334-015
PVC	gray	2 m	BCC03P1	BCC M415-M313-3F-300-VX8334-020
PVC	gray	3 m	BCC03P2	BCC M415-M313-3F-300-VX8334-030
PVC	gray	5 m	BCC03P3	BCC M415-M313-3F-300-VX8334-050
PUR	black	0.3 m	BCC03MK	BCC M415-M323-3F-300-PX0334-003
PUR	black	0.6 m	BCC03ML	BCC M415-M323-3F-300-PX0334-006
PUR	black	1 m	BCC03MM	BCC M415-M323-3F-300-PX0334-010
PUR	black	1.5 m	BCC03MN	BCC M415-M323-3F-300-PX0334-015
PUR	black	2 m	BCC03MP	BCC M415-M323-3F-300-PX0334-020
PUR	black	3 m	BCC03MR	BCC M415-M323-3F-300-PX0334-030
PUR	black	5 m	BCC03MT	BCC M415-M323-3F-300-PX0334-050
PVC	gray	0.3 m	BCC03P4	BCC M415-M323-3F-300-VX8334-003
PVC	gray	0.6 m	BCC03P5	BCC M415-M323-3F-300-VX8334-006
PVC	gray	1 m	BCC03P6	BCC M415-M323-3F-300-VX8334-010
PVC	gray	1.5 m	BCC03P7	BCC M415-M323-3F-300-VX8334-015
PVC	gray	2 m	BCC03P8	BCC M415-M323-3F-300-VX8334-020
PVC	gray	3 m	BCC03P9	BCC M415-M323-3F-300-VX8334-030
PVC	gray	5 m	BCC03PA	BCC M415-M323-3F-300-VX8334-050
PUR	black	0.3 m	BCC03N3	BCC M425-M323-3F-300-PX0334-003
PUR	black	0.6 m	BCC03N4	BCC M425-M323-3F-300-PX0334-006
PUR	black	1 m	BCC03N5	BCC M425-M323-3F-300-PX0334-010
PUR	black	1.5 m	BCC03N6	BCC M425-M323-3F-300-PX0334-015
PUR	black	2 m	BCC03N7	BCC M425-M323-3F-300-PX0334-020
PUR	black	3 m	BCC03N8	BCC M425-M323-3F-300-PX0334-030
PUR	black	5 m	BCC03N9	BCC M425-M323-3F-300-PX0334-050
PVC	gray	0.3 m	BCC03PM	BCC M425-M323-3F-300-VX8334-003
PVC	gray	0.6 m	BCC03PN	BCC M425-M323-3F-300-VX8334-006
PVC	gray	1 m	BCC03PP	BCC M425-M323-3F-300-VX8334-010
PVC	gray	1.5 m	BCC03PR	BCC M425-M323-3F-300-VX8334-015
PVC	gray	2 m	BCC03PT	BCC M425-M323-3F-300-VX8334-020
PVC	gray	3 m	BCC03PU	BCC M425-M323-3F-300-VX8334-030
PVC	gray	5 m	BCC03PW	BCC M425-M323-3F-300-VX8334-050
PUR	black	0.3 m	BCC03NL	BCC M425-M323-3F-602-PX0334-003
PUR	black	0.6 m	BCC03NM	BCC M425-M323-3F-602-PX0334-006
PUR	black	1 m	BCC03NN	BCC M425-M323-3F-602-PX0334-010
PUR	black	1.5 m	BCC03NP	BCC M425-M323-3F-602-PX0334-015
PUR	black	2 m	BCC03NR	BCC M425-M323-3F-602-PX0334-020
PUR	black	3 m	BCC03NT	BCC M425-M323-3F-602-PX0334-030
PUR	black	5 m	BCC03NU	BCC M425-M323-3F-602-PX0334-050
PVC	gray	0.3 m	BCC03R5	BCC M425-M323-3F-602-VX8334-003
PVC	gray	0.6 m	BCC03R6	BCC M425-M323-3F-602-VX8334-006
PVC	gray	1 m	BCC03R7	BCC M425-M323-3F-602-VX8334-010
PVC	gray	1.5 m	BCC03R8	BCC M425-M323-3F-602-VX8334-015
PVC	gray	2 m	BCC03R9	BCC M425-M323-3F-602-VX8334-020
PVC	gray	3 m	BCC03RA	BCC M425-M323-3F-602-VX8334-030
PVC	gray	5 m	BCC03RC	BCC M425-M323-3F-602-VX8334-050

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Connection cable

M12-female right-angle ↔ M8-male straight, 3-pin, with and without LED

M12 ↔ M8


Connection cable



Connector diagram and wiring			
Operating voltage max. AC U _B	60 V AC	30 V DC	
Operating voltage max. DC U _B	60 V DC		
Cable	Molded-on	Molded-on	
No. of wires × cross-section	3×0.34mm ²	3×0.34mm ²	
Enclosure rating per IEC 60529	IP 67	IP 67	
Ambient temperature T _a	PUR -25 °C...+80 °C PUR shielded PVC -5 °C...+80 °C PVC shielded	-25 °C...+80 °C -5 °C...+80 °C	
Version	Normally open	PNP-Normally open	
LED		green/yellow	

Cable material	Color	Length	Ordering code	
PUR	black	0.3 m	BCC03MU	BCC03NA
PUR	black	0.6 m	BCC03MW	BCC03NC
PUR	black	1 m	BCC03MY	BCC03NE
PUR	black	1.5 m	BCC03MZ	BCC03NF
PUR	black	2 m	BCC03N0	BCC03NH
PUR	black	3 m	BCC03N1	BCC03NJ
PUR	black	5 m	BCC03N2	BCC03NK
PVC	gray	0.3 m	BCC03PC	BCC03PY
PVC	gray	0.6 m	BCC03PE	BCC03PZ
PVC	gray	1 m	BCC03PF	BCC03R0
PVC	gray	1.5 m	BCC03PH	BCC03R1
PVC	gray	2 m	BCC03PJ	BCC03R2
PVC	gray	3 m	BCC03PK	BCC03R3
PVC	gray	5 m	BCC03PL	BCC03R4

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



M12 ↔ M8



Connection cable
M12-female straight ↔ M12-male straight
or right-angle, 3-pin, no LED


M12 ↔ M12

Connection cable
M12-female right-angle ↔ M12-male straight
or right-angle, 3-pin, with and without LED

Connector diagram and wiring							
Operating voltage max. AC U _B	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC	250 V AC	30 V DC
Operating voltage max. DC U _B	250 V DC	250 V DC	250 V DC	250 V DC	250 V DC	250 V DC	Molded-on
Cable	Molded-on	Molded-on	Molded-on	Molded-on	Molded-on	Molded-on	3x0.34mm ²
No. of wires × cross-section	3x0.34mm ²	3x0.34mm ²	3x0.34mm ²	3x0.34mm ²	3x0.34mm ²	3x0.34mm ²	IP 68
Enclosure rating per IEC 60529	IP 68	IP 68	IP 68	IP 68	IP 68	IP 68	-25 °C...+80 °C
Ambient temperature T _a	PUR	PUR	PUR	PUR	PUR	PUR	-5 °C...+80 °C
	PUR shielded	PUR shielded	PUR shielded	PUR shielded	PUR shielded	PUR shielded	PNP-Normally open ✓-
	PVC	PVC	PVC	PVC	PVC	PVC	green/yellow
	PVC shielded	PVC shielded	PVC shielded	PVC shielded	PVC shielded	PVC shielded	
Version	Normally open ✓-	Normally open ✓-	Normally open ✓-	Normally open ✓-	Normally open ✓-	Normally open ✓-	
LED							

Cable material	Color	Length	Ordering code	Part number
PUR	black	0.3 m	BCC036Y	BCC0375
PUR	black	0.6 m	BCC036Z	BCC0376
PUR	black	1 m	BCC0370	BCC0377
PUR	black	1.5 m	BCC0371	BCC0378
PUR	black	2 m	BCC0372	BCC0379
PUR	black	3 m	BCC0373	BCC037A
PUR	black	5 m	BCC0374	BCC037C
PVC	gray	0.3 m	BCC0386	BCC038F
PVC	gray	0.6 m	BCC0387	BCC038H
PVC	gray	1 m	BCC0388	BCC038J
PVC	gray	1.5 m	BCC0389	BCC038K
PVC	gray	2 m	BCC038A	BCC038L
PVC	gray	3 m	BCC038C	BCC038M
PVC	gray	5 m	BCC038E	BCC038N
			BCC M415-M413-3A-300-PX0334-003	BCC M415-M423-3A-300-PX0334-003
			BCC M415-M413-3A-300-PX0334-006	BCC M415-M423-3A-300-PX0334-006
			BCC M415-M413-3A-300-PX0334-010	BCC M415-M423-3A-300-PX0334-010
			BCC M415-M413-3A-300-PX0334-015	BCC M415-M423-3A-300-PX0334-015
			BCC M415-M413-3A-300-PX0334-020	BCC M415-M423-3A-300-PX0334-020
			BCC M415-M413-3A-300-PX0334-030	BCC M415-M423-3A-300-PX0334-030
			BCC M415-M413-3A-300-PX0334-050	BCC M415-M423-3A-300-PX0334-050
			BCC M415-M413-3A-300-VX8334-003	BCC M415-M423-3A-300-VX8334-003
			BCC M415-M413-3A-300-VX8334-006	BCC M415-M423-3A-300-VX8334-006
			BCC M415-M413-3A-300-VX8334-010	BCC M415-M423-3A-300-VX8334-010
			BCC M415-M413-3A-300-VX8334-015	BCC M415-M423-3A-300-VX8334-015
			BCC M415-M413-3A-300-VX8334-020	BCC M415-M423-3A-300-VX8334-020
			BCC M415-M413-3A-300-VX8334-030	BCC M415-M423-3A-300-VX8334-030
			BCC M415-M413-3A-300-VX8334-050	BCC M415-M423-3A-300-VX8334-050
			BCC M425-M423-3A-300-PX0334-003	BCC M425-M413-3A-300-PX0334-003
			BCC M425-M423-3A-300-PX0334-006	BCC M425-M413-3A-300-PX0334-006
			BCC M425-M423-3A-300-PX0334-010	BCC M425-M413-3A-300-PX0334-010
			BCC M425-M423-3A-300-PX0334-015	BCC M425-M413-3A-300-PX0334-015
			BCC M425-M423-3A-300-PX0334-020	BCC M425-M413-3A-300-PX0334-020
			BCC M425-M423-3A-300-PX0334-030	BCC M425-M413-3A-300-PX0334-030
			BCC M425-M423-3A-300-PX0334-050	BCC M425-M413-3A-300-PX0334-050
			BCC M425-M423-3A-300-VX8334-003	BCC M425-M413-3A-300-VX8334-003
			BCC M425-M423-3A-300-VX8334-006	BCC M425-M413-3A-300-VX8334-006
			BCC M425-M423-3A-300-VX8334-010	BCC M425-M413-3A-300-VX8334-010
			BCC M425-M423-3A-300-VX8334-015	BCC M425-M413-3A-300-VX8334-015
			BCC M425-M423-3A-300-VX8334-020	BCC M425-M413-3A-300-VX8334-020
			BCC M425-M423-3A-300-VX8334-030	BCC M425-M413-3A-300-VX8334-030
			BCC M425-M423-3A-300-VX8334-050	BCC M425-M413-3A-300-VX8334-050

Other cable materials, colors and lengths on request. Connectors without LED are suitable for PNP and NPN switching functions. NPN versions on request.



Connection cable

M12-female straight ↔ M12-male straight, 4-pin, with and without LED




M12 ↔ M12

Connection cable

M12-female straight ↔ M12-male right-angle, 4-pin, no LED



Connector diagram and wiring



Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C
	PVC -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	

Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C
	PVC -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	




Operating voltage max. AC U _B	30 V DC
Operating voltage max. DC U _B	30 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C
	PVC -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	green/yellow

Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C
	PVC -5 °C...+80 °C
Version	Complementary (NO/NC) /- / -/
LED	

Cable material	Color	Length	Ordering code
PUR	black	0.3 m	BCC039H
PUR	black	0.6 m	BCC039J
PUR	black	1 m	BCC039K
PUR	black	1.5 m	BCC039L
PUR	black	2 m	BCC039M
PUR	black	3 m	BCC039N
PUR	black	5 m	BCC039P
PVC	gray	0.3 m	BCC03C9
PVC	gray	0.6 m	BCC03CA
PVC	gray	1 m	BCC03CC
PVC	gray	1.5 m	BCC03CE
PVC	gray	2 m	BCC03CF
PVC	gray	3 m	BCC03CH
PVC	gray	5 m	BCC03CJ

BCC03A1	BCC039R
BCC03A2	BCC039T
BCC03A3	BCC039U
BCC03A4	BCC039W
BCC03A5	BCC039Y
BCC03A6	BCC039Z
BCC03A7	BCC03A0
BCC03CU	BCC03CK
BCC03CW	BCC03CL
BCC03CY	BCC03CM
BCC03CZ	BCC03CN
BCC03E0	BCC03CP
BCC03E1	BCC03CR
BCC03E2	BCC03CT

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.







Connection cable

M12-female right-angle ↔ M12-male straight or right-angle, 4-pin, no LED



Connector diagram and wiring



Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C
	PVC -5 °C...+80 °C
Version	Complementary (NO/NC) / - / /
LED	

Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C
	PVC -5 °C...+80 °C
Version	Complementary (NO/NC) / - / /
LED	







Operating voltage max. AC U _B	250 V AC
Operating voltage max. DC U _B	250 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	PUR -25 °C...+80 °C
	PUR shielded -5 °C...+80 °C
	PVC -5 °C...+80 °C
Version	Complementary (NO/NC) / - / /
LED	

Cable material	Color	Length	Ordering code
PUR	black	0.3 m	BCC03AJ
PUR	black	0.6 m	BCC03AK
PUR	black	1 m	BCC03AL
PUR	black	1.5 m	BCC03AM
PUR	black	2 m	BCC03AN
PUR	black	3 m	BCC03AP
PUR	black	5 m	BCC03AR
PVC	gray	0.3 m	BCC03EA
PVC	gray	0.6 m	BCC03EC
PVC	gray	1 m	BCC03EE
PVC	gray	1.5 m	BCC03EF
PVC	gray	2 m	BCC03EH
PVC	gray	3 m	BCC03EJ
PVC	gray	5 m	BCC03EK

Part number	Ordering code
BCC M425-M424-3A-304-PX0434-003	BCC03A8
BCC M425-M424-3A-304-PX0434-006	BCC03A9
BCC M425-M424-3A-304-PX0434-010	BCC03AA
BCC M425-M424-3A-304-PX0434-015	BCC03AC
BCC M425-M424-3A-304-PX0434-020	BCC03AE
BCC M425-M424-3A-304-PX0434-030	BCC03AF
BCC M425-M424-3A-304-PX0434-050	BCC03AH
BCC M425-M424-3A-304-VX8434-003	BCC03E3
BCC M425-M424-3A-304-VX8434-006	BCC03E4
BCC M425-M424-3A-304-VX8434-010	BCC03E5
BCC M425-M424-3A-304-VX8434-015	BCC03E6
BCC M425-M424-3A-304-VX8434-020	BCC03E7
BCC M425-M424-3A-304-VX8434-030	BCC03E8
BCC M425-M424-3A-304-VX8434-050	BCC03E9

Part number	Ordering code
BCC M425-M414-3A-304-PX0434-003	BCC03AT
BCC M425-M414-3A-304-PX0434-006	BCC03AU
BCC M425-M414-3A-304-PX0434-010	BCC03AW
BCC M425-M414-3A-304-PX0434-015	BCC03AY
BCC M425-M414-3A-304-PX0434-020	BCC03AZ
BCC M425-M414-3A-304-PX0434-030	BCC03C0
BCC M425-M414-3A-304-PX0434-050	BCC03C1
BCC M425-M414-3A-304-VX8434-003	BCC03EL
BCC M425-M414-3A-304-VX8434-006	BCC03EM
BCC M425-M414-3A-304-VX8434-010	BCC03EN
BCC M425-M414-3A-304-VX8434-015	BCC03EP
BCC M425-M414-3A-304-VX8434-020	BCC03ER
BCC M425-M414-3A-304-VX8434-030	BCC03ET
BCC M425-M414-3A-304-VX8434-050	BCC03EU

Other cable materials, colors and lengths on request.
Connectors without LED are suitable for PNP and NPN switching functions.
NPN versions on request.



Operating voltage max. AC U _B	30 V DC
Operating voltage max. DC U _B	30 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	-25 °C...+80 °C
	-5 °C...+80 °C
Version	PNP-complementary (NO/NC) / - / /
LED	green/yellow

Operating voltage max. AC U _B	30 V DC
Operating voltage max. DC U _B	30 V DC
Cable	Molded-on
No. of wires × cross-section	4×0.34mm ²
Enclosure rating per IEC 60529	IP 68
Ambient temperature T _a	-25 °C...+80 °C
	-5 °C...+80 °C
Version	PNP-complementary (NO/NC) / - / /
LED	green/yellow/white

Part number	Ordering code
BCC M425-M414-3A-606-PX0434-003	BCC03C2
BCC M425-M414-3A-606-PX0434-006	BCC03C3
BCC M425-M414-3A-606-PX0434-010	BCC03C4
BCC M425-M414-3A-606-PX0434-015	BCC03C5
BCC M425-M414-3A-606-PX0434-020	BCC03C6
BCC M425-M414-3A-606-PX0434-030	BCC03C7
BCC M425-M414-3A-606-PX0434-050	BCC03C8
BCC M425-M414-3A-606-VX8434-003	BCC03EW
BCC M425-M414-3A-606-VX8434-006	BCC03Y4
BCC M425-M414-3A-606-VX8434-010	BCC03EZ
BCC M425-M414-3A-606-VX8434-015	BCC03F0
BCC M425-M414-3A-606-VX8434-020	BCC03F1
BCC M425-M414-3A-606-VX8434-030	BCC03F2
BCC M425-M414-3A-606-VX8434-050	BCC03F3

Part number	Ordering code
BCC M425-M414-3A-650-PX0434-003	BCC03C2
BCC M425-M414-3A-650-PX0434-006	BCC03C3
BCC M425-M414-3A-650-PX0434-010	BCC03C4
BCC M425-M414-3A-650-PX0434-015	BCC03C5
BCC M425-M414-3A-650-PX0434-020	BCC03C6
BCC M425-M414-3A-650-PX0434-030	BCC03C7
BCC M425-M414-3A-650-PX0434-050	BCC03C8
BCC M425-M414-3A-650-VX8434-003	BCC03EW
BCC M425-M414-3A-650-VX8434-006	BCC03Y4
BCC M425-M414-3A-650-VX8434-010	BCC03EZ
BCC M425-M414-3A-650-VX8434-015	BCC03F0
BCC M425-M414-3A-650-VX8434-020	BCC03F1
BCC M425-M414-3A-650-VX8434-030	BCC03F2
BCC M425-M414-3A-650-VX8434-050	BCC03F3

M12 ↔ M12




BALLUFF


sensors worldwide




Object Detection



Linear Position Sensing



Industrial Identification



Industrial Networking and Connectivity



Mechanical Accessories

Balluff GmbH
Schurwaldstrasse 9
73765 Neuhausen a.d.F.
Germany
Phone +49 7158 173-0
Fax +49 7158 5010
balluff@balluff.de



 **www.balluff.com**