







- | | |
|---|--|
| 1 | THESE SURFACES WILL NOT BE PLATED |
| 2 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING |
| 3 | .000100-.000200 TIN LEAD OVER .000030 NICKEL. |
| 4 | .000100-.000200 TIN OVER .000030 NICKEL. |
| 5 | PRELIMINARY PART |
| 6 | ROHS 2002/95/EC COMPLIANT. |
| 7 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |



KEYWAY LOCATIONS (REF-SEE TABLE)
(MATING LENGTH OF POST ON NEAR SIDE)
SCALE: 2:1

OBSOLETE △	△	NONE	0	.111	—	—	1	△ 7-87160-6
	△	A,C,E,H,K,M,Q,S,U,W,Y	11	3.855	3.744	24	25	△ 7-87160-5
	△	A,C,E,G,J,L,N,Q,S,U,W,Y	12	3.699	3.588	23	24	△ 7-87160-4
	△	A,D,G,K,N,R,U,X	8	3.543	3.432	22	23	△ 7-87160-3
	△	A,C,E,G,J,L,N,Q,S,U,W	11	3.387	3.276	21	22	△ 7-87160-2
	△	A,D,G,K,N,R,U	7	3.231	3.120	20	21	△ 7-87160-1
OBSOLETE	△	A,C,E,G,J,L,N,Q,S,U	10	3.075	2.964	19	20	△ 7-87160-0
OBSOLETE △	△	B,D,F,J,L,N,Q,S	8	2.919	2.808	18	19	△ 6-87160-9
	△	A,D,F,J,M,P,S	7	2.763	2.652	17	18	△ 6-87160-8
	△	A,D,G,K,N,R	6	2.607	2.496	16	17	△ 6-87160-7
	△	A,C,E,G,J,L,N,Q	8	2.451	2.340	15	16	△ 6-87160-6
△ OBSOLETE	△	A,D,G,K,N	5	2.295	2.184	14	15	△ 6-87160-5
	△	A,C,E,G,J,L,N	7	2.139	2.028	13	14	△ 6-87160-4
	△	A,C,E,G,J,L	6	1.827	1.716	11	12	△ 6-87160-3
	△	A,D,G,K	4	1.671	1.560	10	11	△ 6-87160-2
	△	A,C,E,G,J	5	1.515	1.404	9	10	△ 6-87160-1
	△	A,D,G	3	1.359	1.248	8	9	△ 6-87160-0
	△	A,C,E,G	4	1.203	1.092	7	8	△ 5-87160-9
	△	A,C,E	3	1.047	.936	6	7	△ 5-87160-8
	△	A,C,E	3	.891	.780	5	6	△ 5-87160-7
	△	A,C	2	.579	.468	3	4	△ 5-87160-6
	△	A	1	.423	.312	2	3	△ 5-87160-5
	△	A	1	.267	.156	1	2	△ 5-87160-4
	△	A,D,J,M	4	1.983	1.872	12	13	△ 5-87160-2
	△	A,D	2	.735	.624	4	5	△ 5-87160-1
OBSOLETE	△	A	1	.267	.156	1	2	△ 3-87160-7
OBSOLETE	△	NONE	0	5.415	5.304	34	35	3-87160-6
OBSOLETE	△	NONE	0	5.259	5.148	33	34	3-87160-5
OBSOLETE	△	NONE	0	5.103	4.992	32	33	3-87160-4
OBSOLETE	△	NONE	0	4.947	4.836	31	32	3-87160-3
OBSOLETE	△	NONE	0	4.791	4.680	30	31	3-87160-2
OBSOLETE	△	NONE	0	4.635	4.524	29	30	3-87160-1
OBSOLETE	△	NONE	0	4.479	4.368	28	29	3-87160-0
OBSOLETE	△	NONE	0	4.323	4.212	27	28	2-87160-9
OBSOLETE	△	NONE	0	4.167	4.056	26	27	2-87160-8
OBSOLETE	△	NONE	0	4.011	3.900	25	26	2-87160-7
OBSOLETE △	△	NONE	0	.111	—	—	1	—2-87160-6
	△	A,C,E,H,K,M,Q,S,U,W,Y	11	3.855	3.744	24	25	—2-87160-5
	△	A,C,E,G,J,L,N,Q,S,U,W,Y	12	3.699	3.588	23	24	—2-87160-4
	△	A,D,G,K,N,R,U,X	8	3.543	3.432	22	23	—2-87160-3
	△	A,C,E,G,J,L,N,Q,S,U,W	11	3.387	3.276	21	22	—2-87160-2
	△	A,D,G,K,N,R,U	7	3.231	3.120	20	21	—2-87160-1
OBSOLETE △	△	A,C,E,G,J,L,N,Q,S,U	10	3.075	2.964	19	20	2-87160-0
	△	B,D,F,J,L,N,Q,S	8	2.919	2.808	18	19	—1-87160-9
	△	A,D,F,J,M,P,S	7	2.763	2.652	17	18	—1-87160-8
	△	A,D,G,K,N,R	6	2.607	2.496	16	17	—1-87160-7
	△	A,C,E,G,J,L,N,Q	8	2.451	2.340	15	16	—1-87160-6
△ OBSOLETE	△	A,D,G,K,N	5	2.295	2.184	14	15	1-87160-5
	△	A,C,E,G,J,L,N	7	2.139	2.028	13	14	1-87160-4
	△	A,C,E,G,J,L	6	1.827	1.716	11	12	1-87160-3
	△	A,D,G,K	4	1.671	1.560	10	11	—1-87160-2
	△	A,C,E,G,J	5	1.515	1.404	9	10	1-87160-1
	△	A,D,G	3	1.359	1.248	8	9	1-87160-0
	△	A,C,E,G	4	1.203	1.092	7	8	87160-9
	△	A,C,E	3	1.047	.936	6	7	87160-8
	△	A,C,E	3	.891	.780	5	6	87160-7
	△	A,C	2	.579	.468	3	4	87160-6
	△	A	1	.423	.312	2	3	87160-5
	△	A	1	.267	.156	1	2	87160-4
	OBSOLETE	△						87160-3
	△	A,D,J,M	4	1.983	1.872	12	13	87160-2
△	A,D	2	.735	.624	4	5	87160-1	
FINISH	KEYWAY LOCATIONS	NO OF KEYWAY	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	

[illegible]