







DIMENSION		Poles	Tolerance
Dim L	$N \times 7.62$	4p-8p	± 0.15
Dim A	$(N-1) \times 7.62$	9p-12p	± 0.25
		13p-16p	± 0.35

N=Number of poles



N=Number of poles



P.C.B LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
—			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Terminal housing: Thermoplastic (UL 94V-0)
- Clamp: Brass, Ni plated
- Wire guard solder pin: Brass, Tin plated
- Terminal screw: Steel Zinc plating" - "slot type

Electrical

- Voltage rating: 300VAC
- Current rating: 20A
- Solid wire (AWG): 12-30
- Stranded wire (AWG): 12-30
- Torque (Lb-In): 3.5
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to $+115^{\circ}\text{C}$
- Soldering temperature: $250^{\circ}\text{C} \pm 10^{\circ}\text{C}/5 \text{ Sec}$

RoHS Compliant

PART NUMBER:

OSTVJXX6153

No. of Poles
02 2 Poles
03 3 Poles
... ..
16 16 Poles

COLOR
0: Black
5: Green (Standard)
6: Blue
8: Grey

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

OST ON-SHORE TECHNOLOGY, INC.

TITLE	OSTVJ-7.62 SERIES (4P-16P) 90° wire inlet Solid block						
PART NO.	OSTVJXX6153			DWG NO.	OSTVJXX6153.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Kind 2008.12.15	Kind 2008.12.15				



Tolerance	
X.	± 0.50
X.X	± 0.30
X.XX	± 0.10
X°	$\pm 1^{\circ}$

SHEET: 01/01

REV: B