

MEC1-130-02-L-D-EM2

MEC1-120-02-L-D-RA1-SL

MEC1-120-02-F-D-EM2

(1,00 mm) .0394"

MEC1-RA, MEC1-EM SERIES

RIGHT ANGLE/EDGE MOUNT SOCKETS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MEC1-RA

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating: Au or Sn over

50µ" (1,27 µm) Ni

Current Rating:

1.6 A per pin

(2 adjacent pins powered)

Operating Temp Range:

-55°C to +125°C

Insertion Depth:

(5,84 mm) .230" to

(8,13 mm) .320"

RoHS Compliant: Yes

Processing:

Lead-Free Solderable: Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (05-40)

(0,15 mm) .006" max (50-70)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



MEC1 - 1 POSITIONS PER ROW - CARD SLOT - PLATING OPTION - D - RA1 - NP - SL

Mates with:

(1,60 mm)

.062" card

05, 08, 20, 30,
40, 50, 60, 70

-02

= (1,60 mm)

.062" thick card

-F

= Gold flash on contact,

Matte Tin on tail

-L

= 10µ" (0,25 µm)

Gold on contact,

Matte Tin on tail


POSITIONS PER ROW	POLARIZED POSITIONS
05	3, 4
08	5, 6
20	15, 16
30	21, 22
40	31, 32
50	41, 42
60	31, 32, 63 & 64
70	53, 54, 115 & 116

Note: While optimized for 50Ω applications, this connector with alternative signal/ground patterns may also perform well in certain 75Ω applications. Contact Samtec for further information.

-NP
= No Polarization
(8 positions only)
Leave Blank for polarization

ALSO AVAILABLE
(MOQ Required)

- Elevated body height
 - Other platings
- Contact Samtec.



Note: Some sizes, styles and options are non-standard, non-returnable.

APPLICATION

Samtec recommends that pads on the mating board be Gold plated.

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MEC1-EM

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating: Au or Sn over

50µ" (1,27 µm) Ni

Current Rating:

1.8 A per pin

(2 adjacent pins powered)

Operating Temp Range:

-55°C to +125°C

Insertion Depth:

(5,84 mm) .230" to

(8,13 mm) .320"

RoHS Compliant: Yes

Lead-Free Solderable:

Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



MEC1 - 1 POSITIONS PER ROW - 02 - PLATING OPTION - D - EM2 - NP

Mates with:

(1,60 mm)

.062" card

05, 08, 20, 30,
40, 50, 60, 70

-F

= Gold flash on contact,
Matte Tin on tail


-L

= 10µ" (0,25 µm) Gold on contact,
Matte Tin on tail

-NP
= No Polarization
(8 positions only)
Leave Blank for polarization

ALSO AVAILABLE
(MOQ Required)

- Edge mount leads for (0,80 mm) .031" thick board
 - Other platings
- Contact Samtec.



Note: While optimized for 50Ω applications, this connector with alternative signal/ground patterns may also perform well in certain 75Ω applications. Contact Samtec for further information.

POSITIONS PER ROW	POLARIZED POSITIONS
05	3, 4
08	5, 6
20	15, 16
30	21, 22
40	31, 32
50	41, 42
60	31, 32, 63 & 64
70	53, 54, 115 & 116

Note: Some sizes, styles and options are non-standard, non-returnable.

