

INTERCONNECTS

SERIES 350, 450, 801, 803 • .100" GRID (.025" DIA. PINS), LOW PROFILE HEADERS & VERSATILE SOCKETS • SINGLE & DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4





FIG. 5

- Series 350 and 450 single and double row pin headers use MM #0290 pins. See page 215 for details
- Series 801 and 803 single and double row low profile sockets use MM #1303 receptacles. See page 180 for details
- Series 801 and 803 receptacles use Hi-Rel, 6-finger BeCu #16 contact rated at 4.5 amps. Receptacles accept .025" diameter and .025" square pins. See page 256 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 350...001 Single Row .025" Pin / .018" Solder Tail				
	350-XX-1 -00-001000 Specify number of pins 01-64				
FIG. 2	Series 450...001 Double Row .025" Pin / .018" Solder Tail				
	450-XX-2 -00-001000 Specify number of pins 04-64				
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264					
SPECIFY PLATING CODE XX=		10	90	40	
Pin Plating 		10 μ" Au	200 μ" Sn/Pb	200 μ" Sn	

FIG. 3	Series 801...003 Low Profile Socket (short insulator)					
	801-XX-0 -10-003000 Specify number of pins 01-64					
FIG. 4	Series 801...013 Low Profile Socket (long insulator)					
	801-XX-0 -10-013000 Specify number of pins 01-36					
FIG. 5	Series 803...003 Double Row Low Profile Socket					
	803-XX-0 -10-003000 Specify number of pins 04-72					
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264						
SPECIFY PLATING CODE XX=					41	43
Sleeve (Pin) 					200 μ" Sn	200 μ" Sn
Contact (Clip) 					10 μ" Au	30 μ" Au

