



CORE DIMENSIONS:

A	9.96 [.392]	+	0.15 [.006]
B	3.51 [.138]	+	0.13 [.005]
C	20.00 [.787]	+	0.25 [.010]
D	4.54 [.179]	+	0.13 [.005]

**UNCONTROLLED
DOCUMENT**



SEE NOTE 5


CASE DIMENSIONS:

A	13.00 [.512]	+	1.00 [.039]
B	4.90 [.193]	+	1.00 [.039]
C	25.50 [1.004]	+	1.00 [.039]
D	11.70 [.460]	+	1.00 [.039]
E	2.42 [.095]	+	REF.

IMPEDANCE (Z)

Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	100 Ω	240 Ω	400 Ω
Minimum	- Ω	192 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



FREQUENCY (MHz)

AGILENT E4991A Impedance/Material Analyzer
HP 16082A-Test Fixture REF 3399

NOTES:

1. ASSEMBLED PART #: 28A0350-0B2.
2. CASE COLOR: BLACK-0B2.
3. CASE MATERIAL: DUPONT 101L PA66 NYLON OR EQUIVALENT MATERIAL.
4. FLAMMABILITY RATE: UL94 V-2.

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. Laird TECHNOLOGIES®	
J	ADD NOTES 3 AND 4	06/28/12	Jcai	PROJECT/PART NUMBER: 28A0350-0B2	
H	UPDATED APPEARANCE AND DIMENSIONS TO REFLECT ACTUAL CASE PROFILE	10/28/10	JUN		
G	UPDATE CASE DIMENSION TOLERANCES UPDATE COMPANY LOGO	07/18/08	TMB	REV J DRAWN BY: JRK	
F	UPDATE MIN Z SPEC @ 100 MHZ	04/17/07	TMB	DATE: 01/15/03	SCALE: 1.5 : 1
E	UPDATE COMPANY LOGO	04/17/07	TMB	CAD # 28A0350-0B2-J	TOOL # -
REV	DESCRIPTION	DATE	INT	MATERIAL: FERRITE	



REV J
DRAWN BY: JRK