



3M Worldwide : United States : Utilities & Telecommunication

Search This Product
Catalog

[Product Catalog for Global Telecommunications OEM Site](#) > [Products for Equipment Manufacturers](#) . . .
[3M™ .100" x .100" Preassembled Wiremount Socket, 891 Series](#) > [3M™ .100" x .100" Preassembled Wiremount Socket, 14 Contacts, 89114 Series](#) >

[Printer-friendly format](#) **3M™ .100" x .100" Preassembled Wiremount Socket, 14 Contacts, 89114-0103**



.100" x .100" for .050" Pitch Cable, Preassembled, Flat Cable Connector, Center Bump Key, Open Cover, Phos Bronze Contact, 30u" Gold Plating, With Strain Relief

[\[click to enlarge\]](#)

3M Id : 80-6107-0644-4
GTIN(UPC/EAN) : 0 00 54007 54459 3

Additional Information

- Preassembled, terminates faster than two-piece sockets
- "Sword" packaging makes easy loading of manual and semi-automatic assembly equipment
- "Bumps" prevent premature latch locking during shipment
- Optional double-sided adhesive pull tab for easy unplugging
- Double-recessed cover for cable terminating from either side eliminates need for single-recessed cover

[Full Text . . .](#)

Learn More . . .

[Packaging Data](#)

[3M™Pak100Preassem.WM](#)

[Skt...100"x.100"for .050"PitchCbl,TS0449 - Data Sheet \(PDF 345.0 K\)](#)

Please Note:

Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Conductor Accommodation	26 & 28 AWG Stranded
Connector Cover Style	PlasticClip Preassembled OpenEnds DualRecess
Contact Material	Copper Alloy
Contact Termination Area Plating	None
Contact Underplating	100 μ" [2.54 μm] Nickel
Contact Wiping Area Plating	30 μ" [0.76 μm] Gold
Current Rating	1 Ampere
Insulation Color	Gray
Insulation Flammability Rating	UL 94V-0
Insulation Material	Glass Filled Polyester (PBT)
Insulation Resistance	>1 X 109 Ohms @ 500 Vdc
Interface Grid	.100" x .100"
Interface Style	Rectangular Socket

Markings	3M Logo, Part Identification Number and Orientation Triangle
Non-Operating Temperature	-55 to 105 Degree Celsius
Number of Contact Rows	2
Number of Contacts	14
Pitch	.050 Inch
Polarization	Dual Slots & Centerbump
Primary Trademark Name	3M
Separable	Yes
Strain Relief Type	Plastic
Termination Method	Insulation Displacement
Termination Style	Multiple Wires
Withstanding Voltage	1000 Vrms at Sea Level