





LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B2	REVISED PER ECO-09-007277	31MAR2009	HMR	CR




796984-3 AS SHOWN

- △ MATERIAL AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: BLACK.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
3. WIRE SIZE RANGE: 12-30 AWG.
4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677.
5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- △ 6. NOT CUMULATIVE TOLERANCE
- 7 PARTS TO BE MERKED WITH WHITE PERMANENT MARKING. SEE DETAIL C.
- △ 8. PARTS TO BE MARKED WITH WHITE PERMANENT MARKING. SEE DETAIL C.
- △ 9. PRELIMINARY - NOT FOR PRODUCTION.



DETAIL C
SCALE 4:1



RECOMMENDED PC BOARD LAYOUT
ACCEPTS 1.6 - 2.4 mm PC BOARD THICKNESS

DETAIL C	DIMENSIONS (mm)			
	B	A	NO. OF POSN	PART NUMBER
	53.34	50.80	10	2-796984-5
	124.46	121.92	24	2-796984-4
	99.06	96.52	19	1-796984-9
	63.50	60.96	12	1-796984-2
	58.42	55.88	11	1-796984-1
	53.34	50.80	10	1-796984-0
	48.26	45.72	9	796984-9
	43.18	40.64	8	796984-8
	38.10	35.56	7	796984-7
	33.02	30.48	6	796984-6
	27.94	25.40	5	796984-5
	22.86	20.32	4	796984-4
	17.78	15.24	3	796984-3
	12.70	10.16	2	796984-2

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED. IT IS TO BE RETURNED TO TYCO ELECTRONICS CORPORATION WHEN NO LONGER REQUIRED. IT IS TO BE DESTROYED WHEN NO LONGER REQUIRED. IT IS TO BE DESTROYED WHEN NO LONGER REQUIRED. IT IS TO BE DESTROYED WHEN NO LONGER REQUIRED.		DWN S. WELDON 07NOV2001	Tyco Electronics Harrisburg, PA 17105-3608		
DIMENSIONS:		CHK D. BIEVENOUR 07NOV2001	NAME		
mm		APVD D. BIEVENOUR 07NOV2001	PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO RESTRICTED TO A100779C=796984 CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 1 REV B2		
TOLERANCES UNLESS OTHERWISE SPECIFIED:					
9 PLC ±0.1					
1 PLC ±0.1					
2 PLC ±0.1					
3 PLC ±0.1					
4 PLC ±0.1					
ANGLES					
FINISH					
MATERIAL					