



## Product: [3079A](#)

Profibus, 1 Pr #22 Sol BC, PO Ins, OS+TC Brd, PVC Jkt, PLTC Profibus DP

 [Request Sample](#)

### Product Description

Profibus, 1 Pair 22AWG (Solid) Bare Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(65%) Shield, PVC Outer Jacket, PLTC CMG AWM 20201 SUN RES Profibus DP

### Technical Specifications

#### Product Overview

Suitable Applications:	harsh environment, outdoors, where multiple cable runs are required, data transmission applications such as Profibus DP or PA, Instrumentation and computer cable, etc. exposure to temperature extremes, humidity/moisture, dust, and oil.
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	Solid	BC - Bare Copper	0.026 in	1

Conductor Count: 2

##### Insulation

Material
PE - Polyethylene (Foam)

##### Color Chart

Number	Color
1	Red & Green

##### Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Alum / Poly	Beldfoil®	100%
Braid	2	Tinned Copper (TC)		65%

##### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.315 in

#### Electrical Characteristics

##### Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
3.9 Ohm/1000ft	16 Ohm/1000ft

##### Capacitance

Nom.Mutual Capacitance
8.5 pF/ft

##### Inductance

Nominal Inductance
0.282 $\mu$ H/ft

## Impedance

### Nominal Characteristic Impedance

150 Ohm

## High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.2 MHz	0.27 dB/100ft
4 MHz	0.67 dB/100ft
16 MHz	1.37 dB/100ft

## Delay

### Nominal Velocity of Propagation (VP) [%]

78%

## High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
0.2 MHz	1.1 dB/100m
4 MHz	2.65 dB/100m
16 MHz	5.4 dB/100m

## Current

Element	Max. Recommended Current [A]
Per Conductor	2.3 Amps per Conductor

## Voltage

UL Voltage Rating
300 V RMS (NEC Type CMG)
600 V RMS (UL AWM Style 20201)
300 V RMS (NEC Type PLTC)

Electrical Characteristics Notes:	Capacitance Unbalance @ 1 kHz: Less than 1000 pF/km
Other Electrical Characteristic 2:	Input Impedance/Unfitted Impedance 3 - 20 MHZ, 150 +/-15 Ohms

## Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-30°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	52 lbs/1000ft
Max. Pull Tension:	50 lbs
Min Bend Radius/Minor Axis:	3.2 in

## Standards

NEC/(UL) Compliance:	CMG, PLTC
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	UL Style 20201 (600 V 75°C)
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

## Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
IEC Flammability:	IEC 60332-1-2
IEEE Flammability:	1202
UL voltage rating:	300 V RMS (NEC Type CMG)

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
3079A 0601000	Chrome	Reel	1,000 ft	612825140382
3079A 0602000	Chrome	Reel	2,000 ft	612825140399
3079A 0071000	Violet	Reel	1,000 ft	612825140344
3079A 0072000	Violet	Reel	2,000 ft	612825140351
3079A 0075000	Violet	Reel	5,000 ft	612825140375

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Siemens Sinec L2 Cable. For CPE jacketed version order Part No. YR45047. For LS0H (FRNC) jacketed version, order Part No. YR44731.
--------	--

## History

Update and Revision:	Revision Number: 0.323 Revision Date: 06-08-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.