





REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	A2	REVISED PER ECO-17-011927	22AUG2017	RS	KR





SEE DETAIL A


- 1 MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
- 2 RECOMMENDED PANEL THICKNESS 0.76 – 2.29.
- 3 PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
- 4 OPTIONAL FOR KEYING HOUSING IN PANEL.
- 5 CIRCUIT NUMBER 1 LOCATION.
- 6 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- 7 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 8 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
- 9 150° C TEMPERATURE RATING FOR THIS HOUSING IS FOR SHORT TERM DURATION. MAX OPERATING TEMPERATURE REMAINS 125° C.
- 10 PHOSPHOR BRONZE CONTACTS SHOULD ALWAYS BE USED WITH THIS HOUSING.



DETAIL A
OPTIONAL CONSTRUCTIONS




RECOMMENDED PANEL CUT OUT



3-DIMENSIONAL MODEL
NTS

7.62	.300	27.43	1.080
6.35	.250	27.10	1.067
4.45	.175	27.05	1.065
2.79	.110	26.67	1.050
2.54	.100	13.46	.530
2.41	.095	13.41	.528
2.29	.090	12.96	.510
0.76	.030	8.64	.340
0.38	.015	8.13	.320
MM	IN	MM	IN
CONVERSION TABLE			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 15-NOV-2001	TE Connectivity	794707-1	
		CHK S. RIDGILL 15-NOV-2001			
DIMENSIONS: mm		APVD S. RIDGILL 15-NOV-2001	NAME CAP, 4 CIRCUIT, UNIVERSAL MATE-N-LOK™		PART NUMBER
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0.000000		PRODUCT SPEC	SIZE A1		RESTRICTED TO
MATERIAL NYLON, UL 94-2, BLACK		FINISH -	WEIGHT 0.000000		SCALE 4:1
		APPLICATION SPEC	DRAWING NO 794707		SHEET 1 OF 1
		ANGLES ± 0° 30'	CUSTOMER DRAWING		REV A2