


SERIES**0925R
0925****Molded Shielded RF Coils**

Actual Size

**Military Specifications**

MS21426 (LT10K); MS21427 (LT10K)

Physical Parameters

	Inches	Millimeters
Length	0.250 ± 0.010	6.35 ± 0.25
Diameter	0.095 ± 0.010	2.41 ± 0.25
Lead Size		
AWG #24 TCW	0.020 ± 0.0015	0.508 ± 0.038
Lead Length	1.5 ± 0.12	38.10 ± 3.05

Current Rating at 90°C Ambient 15°C Rise**Operating Temperature Range** -55°C to +105°C**Maximum Power Dissipation at 90°C** 0.0585 W**Weight Max.** (Grams) 0.25**Incremental Current** Current level which causes a Max. of 5% change in inductance.**Coupling** 3% Max.

† Self Resonant Frequency (SRF) values are calculated and to be used for reference only.

Marking DELEVAN; inductance with units and tolerance; date code (YYWWL). Note: An R before the date code indicates a RoHS component.

Example: 0925R-472K

<i>Front:</i>	<i>Reverse:</i>
DELEVAN	4.7uH±10%
4.7uH±10%	R 0902A

Packaging Tape & reel: 12" reel, 3500 pieces max.; 14" reel, 6000 pieces max.**Made in the U.S.A.**

RF II										
DASH NUMBER*	MIL DASH #	INDUCTANCE (μH) ±10%		TEST FREQUENCY (MHz)	Q MINIMUM	SRF MINIMUM (MHz)	MAXIMUM (MHz)	DC RESISTANCE MAXIMUM (OHMS)	CURRENT RATING MAXIMUM (mA)	INCREMENTAL CURRENT (mA)
MS21426— SERIES 0925 IRON CORE & SLEEVE (LT10K)										
-101K	1	0.10		54	25.0	490.0†	0.10	670	670	
-121K	2	0.12		52	25.0	430.0†	0.11	635	635	
-151K	3	0.15		50	25.0	415.0†	0.12	610	610	
-181K	4	0.18		49	25.0	375.0†	0.13	585	585	
-221K	5	0.22		47	25.0	330.0†	0.15	545	545	
-271K	6	0.27		46	25.0	300.0†	0.16	530	530	
-331K	7	0.33		44	25.0	260.0†	0.18	495	495	
-391K	8	0.39		42	25.0	230.0	0.19	485	485	
-471K	9	0.47		41	25.0	220.0	0.21	460	460	
-561K	10	0.56		41	25.0	210.0	0.23	440	440	
-681K	11	0.68		39	25.0	180.0	0.24	430	430	
-821K	12	0.82		38	25.0	165.0	0.27	405	405	
-102K	13	1.00		37	25.0	150.0	0.30	385	385	
-122K	14	1.20		40	7.9	130.0	0.73	247	247	
-152K	15	1.50		41	7.9	115.0	0.86	228	228	
-182K	16	1.80		43	7.9	105.0	0.95	217	217	
-222K	17	2.20		45	7.9	95.0	1.10	202	202	
-272K	18	2.70		48	7.9	90.0	1.20	193	193	
-332K	19	3.30		49	7.9	80.0	1.30	185	185	
-392K	20	3.90		50	7.9	75.0	1.50	173	173	
-472K	21	4.70		53	7.9	70.0	2.40	136	136	
-562K	22	5.60		54	7.9	60.0	2.90	124	124	
-682K	23	6.80		55	7.9	55.0	3.20	118	118	
-822K	24	8.20		55	7.9	53.0	3.60	111	111	
-103K	25	10.0		57	7.9	50.0	4.00	106	106	
-123K	26	12.0		36	2.5	35.0	3.00	122	122	
-153K	27	15.0		38	2.5	30.0	3.40	115	115	
-183K	28	18.0		40	2.5	26.0	3.80	108	108	
-223K	29	22.0		40	2.5	24.0	4.90	96	96	
-273K	30	27.0		40	2.5	21.0	5.80	88	88	
-333K	31	33.0		41	2.5	20.0	6.50	83	83	
-393K	32	39.0		42	2.5	19.0	7.90	75	75	
-473K	33	47.0		44	2.5	16.0	9.30	69	69	
-563K	34	56.0		44	2.5	15.0	11.0	64	64	
-683K	35	68.0		45	2.5	13.0	12.0	61	61	
-823K	36	82.0		45	2.5	11.0	13.0	59	59	
-104K	37	100.0		40	2.5	10.5	16.8	51	51	
MS21427— SERIES 0925 FERRITE CORE & SLEEVE (LT10K)										
-124K	1	120.0		31	0.79	13.0	5.80	88	27	
-154K	2	150.0		33	0.79	12.0	7.90	75	24	
-184K	3	180.0		33	0.79	11.0	9.40	69	22	
-224K	4	220.0		35	0.79	10.0	11.0	64	20	
-274K	5	270.0		37	0.79	9.0	12.0	61	18	
-334K	6	330.0		40	0.79	8.0	16.0	53	16	
-394K	7	390.0		38	0.79	7.8	21.0	46	14	
-474K	8	470.0		36	0.79	7.5	24.0	43	13	
-564K	9	560.0		36	0.79	7.0	28.0	40	12	

Parts listed above are QPL/MIL qualified

Optional Tolerances: J = 5% H = 3%

*Complete part # must include series # PLUS the dash #

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Delevan:

[MS21426-13](#) [MS21426-19](#) [MS21426-35](#) [MS21426-18](#)