

Compact limit switch conforming to NFC 63 145

→ Series 83 880 with cable output

- IP 66/67
- Metal case
- cUL approval



Main specifications

Characteristics		Type of output	
Standard		Cable length 1 m	83 880 101
Standard		Cable length 2 m	83 880 102
Standard		Cable length 3 m	83 880 103
Standard		Cable length 6 m	83 880 106
Plunger with 90° roller		Cable length 1 m	-
Plunger with 90° roller		Cable length 2 m	-
Plunger with 90° roller		Cable length 3 m	-
Plunger with 90° roller		Cable length 6 m	-
Mechanical characteristics			
Sequence			
Snap action			
Minimum operating force (N)			10
Minimum operating force (Nm)			-
Minimum total travel force (N)			30
Minimum total travel force (Nm)			-
Min. positive opening travel (N)			28
Min. positive opening travel (Nm)			-
Mechanical life millions of operations			10
Vertical approach speed			1 mm/min → 0.5 m/s
Horizontal approach speed (30° cam)			-
Weight (g)			190

General characteristics

Assigned impulse voltage (Uimp) - V	2500
Assigned insulation voltage (Ui) V	500
Thermal current (Ith) A	10
Low-load switching - Minimum voltage (V)	10
Low-load switching - Minimum current (mA)	100
Assigned working characteristics (EN 60 947.5.1, UL 508)	A300 = AC15 250 V 6 A Q150 = DC13 24 V 8 A
Use category according to IEC 947.5.1	AC15=250 V/6 A DC13=24 V/8 A
Use category according to UL 508	A300 - Q150
Electrical protection	Integral earth wire Short-circuit protection device : IEC/EN 60947.5.1 Fuse 6 AgC
Approvals	UL 508, UL 50

Product adaptations



- Contact type
- Rear output
- Protective scraper seal
- Length of cable/connector/stripping
- Connector output
- Low level contact




Metal roller plunger	Metal plunger with threaded barrel	Roller plunger - metal with threaded barrel	Steel metal roller lever (2 directions of attack)
83 881 101	83 884 101	83 882 101	83 883 101
83 881 102	83 884 102	83 882 102	83 883 102
83 881 103	83 884 103	83 882 103	83 883 103
83 881 106	83 884 106	83 882 106	83 883 106
83 885 101	-	83 886 101	-
83 885 102	-	83 886 102	-
83 885 103	-	83 886 103	-
83 885 106	-	83 886 106	-
10	10	10	-
-	-	-	0.15
30	30	30	-
-	-	-	0.35
28	28	28	-
-	-	-	0.15
10	10	10	10
1 mm/min → 0.5 m/s	-	1 mm/min → 0.5 m/s	1 mm/min → 0.5 m/s
1 mm/min → 0.3 m/s	1 mm/min → 0.3 m/s	1 mm/min → 0.3 m/s	-
200	220	220	230

Principles

Function

Four-terminal double break two-way contact element (form Zb) with positive opening NC contacts. The 2 moving contacts are electrically isolated from one another.


Snap-action contact




- ① Brown
- ② Black
- ③ Blue
- ④ Green-yellow

→ **Product**


- 83 884 1




- 83 883 1




- 83 881 1




- 83 885 1



- 83 882 1



- 83 886 1



- 1 POP marking
- 2 Max.tightening thickness 10.5