



exclusively represented in the USA by:



2013

Terms of Delivery and Payment

Number 1 IN CUSTOMER SERVICE!

Here's why:

- **NO MINIMUM ORDERS, NO STOCKING REQUIREMENTS,
NO DROP SHIP FEES**

We don't believe in minimum order quantities or stocking requirements.

Buy what you want, when you want it! As a Bondhus® distributor, you are never forced to stock our products in your inventory – minimizing your overhead costs.

- **NO HASSLE RETURNS**

We want you to be satisfied with every aspect of doing business with Felo and Bondhus. Too much stock of a particular item? Simply call us at 800-328-8310 for a Returned Goods Authorization (RGA) and send it back freight prepaid for a full credit to your account. Bondhus never charges a restocking fee on items in our standard product line!

- **LIFETIME WARRANTY**

All Felo products are guaranteed for life. If you or your customer are not happy with a Felo tool – for any reason – simply return it. A replacement will be shipped right out at no cost – no questions asked!

- **HIGHLY TRAINED, EXPERIENCED IN-HOUSE CUSTOMER
SERVICE DEPARTMENT**

Bondhus' in-house Customer Service staff is made up of highly-trained professionals with an average of 16 years experience in the hex tool industry. Always willing to answer your questions or address any ordering / shipping issues, they can be reached weekdays, 7 am to 5 pm CST, at 800-328-8310 or via email at cservice@bondhus.com

63

63 years of Felo!

Our customers and employees are proud of this anniversary. In 1950 Felo Werkzeugfabrik was founded in Neustadt (Hessen), Germany. Driven by innovative power, quality consciousness and enthusiasm the company grew from humble beginnings with 2 employees into one of the leading manufacturers of screwdrivers and bits.

Today 200 people work for Felo.



2000

stocked items are at the daily disposal of our customers.

On top of this we manufacture the same number of products in customized versions, as special tools and under private brand.

135

years of experience in the development, production and marketing of screwdrivers.

In 1878 the »Hammermühle« factory for tools was founded. The assortment included forged screwdrivers as well as chisels, hammers and pliers. The foundation of Felo in 1950 was based on this company.



40

Felo tools are exported to 40 countries:

we are a global player and specialist, offering a wide variety of products for the most different markets and requirements. Felo is traditionally strong in exports: almost 100 years ago we began using catalogues in 4 languages. Since then Felo has become a byword for quality.



260

applications for industrial property rights document our innovative power!

Progressive ideas like 2-component handles, Titanium-coated bits and screwdrivers with exchangeable blades for electricians originated from Felo developments. Our curiosity and creativity have made us a leader in product and production.

1


mission:

We want to inspire our customers!
This doesn't just show in our products
but also in our flexibility, service,
reliability and cost-efficiency.

Test for yourself our strengths!



										
		Rgonic Series 400 Pg. 6 - 15	frico Series 550 Pg. 16 - 17	frico Series 500 Pg. 18 - 25	PP Series 206 Pg. 26 - 27	PP Series 200 290 ESD Pg. 28 - 31	Wood Series 330/ Series 490 Pg. 32 - 33	PP Series 800 Pg. 34 - 37	VDE VDE/ Insulated Pg. 38 - 43	Nm Series Nm Pg. 44 - 47
for slotted screws		8-10, 13-14	17	19-25	27	29-31	32	35-37	39-43	45-47
PH Phillips		8-10, 13-14	17	19-25	27	29-31	32	36-37	39-43	45-47
PZ Pozidriv-Superdriv		8, 10		19, 21, 25					43	45-47
+ / - Plus - Minus	 									47
Torx® Torx		11, 13, 15		20-21, 24-25				36-37	43	45-47
Torx TR Torx®Tammer Resistant		11		20, 25						
Torx Plus®										45-47
Inner Hexagon Innensechskant										47
Nut Drivers Steckschlüssel										
SQ Square for Robertson® screws		11, 13, 15							43	
XZN XZN										
Clutch										
Spanner										
TS for TorqSet® screws										
Tri-Wing®										
Bitholder		12-13		22					41	45-47



49, 51-53		57, 59, 61-62	65-67	69-70	72-73	74-77, 79, 81-83	85-88			
49, 51-53		57, 59, 61-62	65-67	69-70	72-73	74-77, 80-83	85-89			
52		59, 62	65, 67	69-70	72-73	77, 80				
						81				
50-52	55	57, 59, 62	65, 67	69-70	72-73	75-76, 78, 80, 82-83	85-90			
		62	67			78	87, 90			
						78, 80				
50-52		59, 62	65, 67				90			
50		57-58, 61	66			81	89			
		57, 59, 61	67	70	73	77, 82	86-87			
			67			79	90			
							90			
		59					90			
						79	90			
							90			
	55	57, 59, 61-62			73		84-90	91-93		



Ergonic, the first handle that adapts to the users hand!



smooth, seamless handle for maximum comfort

hand and handle interlock, causing less strain


Fits all!
Serie 400 *ERGonic*® (pat.)

stronger, adaptable, truly ergonomic

hexagon bolsters available on series 410

blades manufactured from chrome-molybdenum-vanadium steel

superior torque which exceeds DIN and ISO requirements by up to 100%



anti-roll handle design

hanging hole for easy storage or inserting lever

screw symbols on handle cap



GS tested for safety



EAN code on every product



full length, impact proof handle core



black tip for precision fit



There are numerous ergonomic handle designs:
It is always the user's hand that has to adjust to the handle.
ERGONIC is the only handle adjusting to the individual hand!

The new standard in ergonomics, torque transmission and responsiveness!

ERGONIC[®]


The impact proof handle core is coated with elastic, scratch resistant elastomer containing cells of highly flexible plastics.



The handle fits perfectly into the hand at all times.
Hand and handle interlock, causing less strain and work fatigue, allowing higher maximum torque!
Responsiveness of material results in enhanced sensitivity and perfect control of torque.

>felo **INNOVATIONS**

410



							410		EAN-Code	Item No
5/32"	3"	3.7"	1.2"	0.16"	12		410 042 40	60	40 07157	53121 6
7/32"	4"	3.9"	1.3"	0.20"	12		410 553 40	74	40 07157	52785 1
1/4"	5"	4.2"	1.4"	0.26"	12		410 654 40	100	40 07157	52787 5
5/16"	6"	4.4"	1.5"	0.31"	12		410 085 40	162	40 07157	52789 9
3/8"	7"	4.4"	1.5"	0.31"	6		410 105 40	219	40 07157	53125 4
1/2"	8"	4.4"	1.5"	0.39"	6		410 127 40	253	40 07157	53127 8

411



PZ																																																																																																									
----	---	---	---	---	---	---	---	--	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	--

412



PH							412		EAN-Code	Item No
1	3 1/8"	3.7"	1.2"	0.20"	12		412 102 40	56	40 07157	52795 0
2	4"	4.2"	1.4"	0.26"	12		412 203 40	92	40 07157	52797 4
3	6"	4.4"	1.5"	0.31"	6		412 305 40	162	40 07157	53131 5

410



410 | 412



EAN-Code Item No

Set 6 pcs.

410 961 48

526

40 07157 **53167** 4

(4 x) **400 - 410:** 1/8" x 3 1/8" | 5/32" x 3" | 7/32" x 4" | 1/4" x 5"

(2 x) **412:** PH 1 x 3 1/8" | PH 2 x 4"

410



410 | 412



EAN-Code Item No

Set 3 pcs.

410 931 48

313

40 07157 **53173** 5

(2 x) **410:** 7/32" x 4" | 1/4" x 5"

412: PH 2 x 4"

410



410 | 412



EAN-Code Item No

Set 3 pcs.

410 932 48

283

40 07157 **57521** 5

410: 7/32" x 4"

(2 x) **412:** PH 1 x 3 1/8" | PH 2 x 4"

400



						400				EAN-Code	Item No
3/32"	3"	3.4	1"	2,5	12		400 022 10	27	40 07157	53679	2
1/8"	3 1/8"	3.4	1"	0.12"	12		400 032 10	30	40 07157	53117	9
9/64"	4"	3.4	1"	0.14"	12		400 353 10	33	40 07157	53119	3
5/32"	4"	3.7	1.2"	0.16"	12		400 043 10	49	40 07157	53611	2
3/16"	6"	3.9	1.3"	0.20"	12		400 055 10	75	40 07157	53619	8
7/32"	5"	3.9	1.3"	0.20"	12		400 554 10	72	40 07157	53621	1
7/32"	6"	3.9	1.3"	0.20"	12		400 555 10	82	40 07157	53623	5
15/64"	6"	4.2	1.4"	0.24"	12		400 065 10	99	40 07157	57591	3
15/64"	8"	4.2	1.4"	0.24"	12		400 067 10	112	40 07157	57593	7
1/4"	4"	4.2	1.4"	0.24"	12		400 653 10	79	40 07157	53627	3
1/4"	6"	4.2	1.4"	0.24"	12		400 655 10	102	40 07157	52799	8
1/4"	8"	4.2	1.4"	0.24"	12		400 657 10	112	40 07157	53629	7
5/16"	7"	4.4	1.5"	0.31"	12		400 086 10	135	40 07157	52801	8
3/8"	8"	4.4	1.5"	0.31"	6		400 107 10	162	40 07157	53681	5

401




PZ							401		EAN-Code	Item No
1	3 1/8"	3.7	1.2"	0.18"	12		401 102 10	50	40 07157	53683 9
2	4"	4.2	1.4"	0.24"	12		401 203 10	92	40 07157	53685 3
3	6"	4.4	1.5"	0.31"	6		401 305 10	148	40 07157	53687 7

402



PH						402		EAN-Code	Item No
1	3 1/8"	3.7	1.2"	0.18"	12	402 102 10	50	40 07157	52803 2
2	4"	4.2	1.4"	0.24"	12	402 203 10	92	40 07157	52805 6
2	6"	4.2	1.4"	0.24"	12	402 205 10	103	40 07157	53637 2
2	8"	4.2	1.4"	0.24"	6	402 207 10	114	40 07157	53639 6
3	6"	4.4	1.5"	0.31"	6	402 305 10	146	40 07157	53689 1


404



SQ						404		EAN-Code	Item No
1	5"	3.7"	1.2"	0.18"	12	404 100 40	56	40 07157	53507 8
2	6"	4.2"	1.4"	0.20"	12	404 200 40	91	40 07157	53509 2
3	6"	4.2"	1.4"	0.24"	12	404 300 40	105	40 07157	53511 5


New!

407



TorxTR						407		EAN-Code	
10	4"	3.4"	1"	0.14"	12	407 103 40	33	40 07157	60903 8
15	4"	3.7"	1.2"	0.16"	12	407 153 40	50	40 07157	60905 2
20	4"	3.9"	1.3"	0.16"	12	407 203 40	68	40 07157	60907 6
25	4"	4.2"	1.4"	0.20"	12	407 253 40	82	40 07157	60909 0

408



Torx						408		EAN-Code	Item No
7	2 3/8"	3.4"	1"	0.12"	12	408 071 40	27	40 07157	52807 0
8	2 3/8"	3.4"	1"	0.12"	12	408 083 40	29	40 07157	52809 4
9	2 3/8"	3.4"	1"	0.14"	12	408 093 40	29	40 07157	52811 7
10	4"	3.4"	1"	0.14"	12	408 103 40	45	40 07157	52813 1
15	4"	3.7"	1.2"	0.16"	12	408 153 40	45	40 07157	52815 5
20	4"	3.9"	1.3"	0.20"	12	408 203 40	69	40 07157	52817 9
25	4"	4.2"	1.4"	0.20"	12	408 253 40	69	40 07157	52819 3
27	4"	4.2"	1.4"	0.20"	12	408 273 40	69	40 07157	52821 6
30	4 1/2"	4.4"	1.5"	0.24"	6	408 303 40	96	40 07157	52823 0
40	5"	4.4"	1.5"	0.31"	6	408 404 40	143	40 07157	52825 4

429



1/4" 6 3/4" 4.2" 1.4"

6

429

429 635 40



146

EAN-Code Item No

40 07157 60365 4



438



1/4" 4" 3.9" 1.3"

6

438

438 125 40



102

EAN-Code Item No

40 07157 53711 9



Adapter for sockets 1/4"

4" 3.9" 1.3"

6

497

497 110 40



107

EAN-Code


40 07157 61479 7

New!

497

1/4"

New!
Stubby



400 402




EAN-Code

Stubby

7/32"	1"	2.4"	0.8"	12	400 550 10	36	40 07157 61509 1
PH 2	1"	2.4"	0.8"	12	402 020 10	38	40 07157 61511 4

New!
Stubby



438



EAN-Code

Stubby Bitholder 1/4"

0.7"	2.4"	0.8"	12	438 026 40	48	40 07157 61727 9
------	------	------	----	------------	----	-------------------------



400



EAN-Code Item No

Ergonic XXL-Rack SQ 17-pcs

400 927 43

2337

40 07157 **61391** 2

(5 x) **400**: 1/8" x 3 1/8" | 5/32" x 4" | 7/32" x 5" | 1/4" x 5" | 5/16" x 7"

(2 x) **404**: SQ1 x 5" | SQ2 x 6"

(2 x) **402**: PH1 x 3 1/8" | PH2 x 4"

(2 x) **413**: 9/64" x 4" | 5/32" x 4" **AC 1000V IEC 60900 : 2004**

(2 x) **414**: PH1 x 3 1/8" | PH2 x 4" **AC 1000V IEC 60900 : 2004**

(4 x) **408**: Torx 10 x 4" | Torx 15 x 4" | Torx 20 x 4" | Torx 25 x 4"

Steel Rack


400



400



400



EAN-Code Item No

Set 5-pcs

400 951 18

492

40 07157 **53693** 8


(3 x) **400:** 5/32" x 4" | 7/32" x 5" | 1/4" x 5"

(2 x) **402:** PH1 x 3 1/8" | PH2 x 4"

400



400



EAN-Code Item No

Set 3-pcs

400 931 18

312

40 07157 **53701** 0


(2 x) **400:** 7/32" x 5" | 1/4" x 5"

402: PH2 x 4"

404



404



EAN-Code Item No

Set 3 pcs. SQ

404 931 48

90


40 07157 53517 7

(3 x) 404: SQ 1 | SQ 2 | SQ 3

408



408



EAN-Code Item No

Set 6 pcs. Torx

408 961 48

402


40 07157 53165 0

(6 x) 408: Torx 8 | Torx 9 | Torx 10 | Torx 15 |
Torx 20 | Torx 25

408



408



EAN-Code Item No

Set 3 pcs. Torx

408 931 48

206

40 07157 53171 1

(3 x) 408: Torx 10 | Torx 15 | Torx 20



steelcap




pleasant soft grip material
for highest torque



GS tested for safety


The strongest of series 500 Serie 550

steelcap / full length blade
hexagon bolster / hexagon blade




hexagon bolster

anti-roll
handle design





hexagon blades manufactured from
chrome-molybdenum-vanadium steel

superior torque
which exceeds DIN
and ISO requirements
by up to 100%




EAN code
on every product

full length blade



black tip
for precision fit

550




550



EAN-Code Item No

3/16"	3 1/2"	3.5"	1.1"	0.20"	12		550 045 40	85	40 07157	50699	3
7/32"	3 1/2"	3.9"	1.3"	0.20"	12		550 055 40	108	40 07157	32354	5
1/4"	5"	3.9"	1.3"	0.26"	12		550 065 40	133	40 07157	32356	9
5/16"	6"	4.1"	1.2"	0.31"	6		550 080 40	199	40 07157	32358	3
23/64"	6 1/2"	4.1"	1.2"	0.31"	6		550 090 40	205	40 07157	50701	3
3/8"	7"	4.1"	1.2"	0.31"	6		550 100 40	210	40 07157	32360	6
1/2"	8"	4.1"	1.2"	0.39"	6		550 120 40	293	40 07157	32362	0

552



552




EAN-Code Item No

PH											
1	3 1/2"	3.5"	1.1"	0.20"	12		552 102 40	95	40 07157	50703	7
2	4"	3.9"	1.3"	0.26"	12		552 203 40	127	40 07157	32368	2
3	6"	4.1"	1.2"	0.31"	6		552 305 40	198	40 07157	32370	5

550



550 | 552



Set 5 pcs.

550 952 48



EAN-Code Item No

(3 x 1) 550: 3/16" x 3 1/2" | 7/32" x 4" | 1/4" x 5"

(2 x 1) 552: PH 1 x 3 1/2" | PH 2 x 4"


886

40 07157 **50707** 5

550



550 | 552



Set 3 pcs.

550 931 34




EAN-Code Item No

(2 x) 550 3/16" x 3 1/2" | 1/4" x 5"


552 PH 2 x 4"

363

40 07157 **53523** 8



full length, impact proof handle core



pleasant soft grip material
for highest torque

smooth,
seamless handle for
maximum comfort



GS tested for safety


The Original Serie 500

The leaders in
handle-design / blade quality
2-component-technology

blades manufactured from
chrome-molybdenum-
vanadium steel

ergonomically refined design




superior torque which
exceeds DIN and ISO
requirements by
up to 100%



hanging hole for easy
storage or inserting lever

EAN code on every product

black tip for precision fit



500



								500		EAN-Code	Item No
3/32"	3"	3.2"	1"	0.10"	12			500 022 10	26	40 07157	22091 2
1/8"	3 1/8"	3.2"	1"	0.12"	12			500 032 10	28	40 07157	22092 9
9/64"	4"	3.2"	1"	0.14"	12			500 353 10	32	40 07157	22093 6
5/32"	4"	3.5"	1.1"	0.16"	12			500 043 10	45	40 07157	22094 3
5/32"	8"	3.5"	1.1"	0.16"	12			500 047 10	58	40 07157	50693 1
5/32"	12"	3.5"	1.1"	0.16"	12			500 049 10	58	40 07157	51379 3
3/16"	6"	3.9"	1.3"	0.20"	12			500 505 10	76	40 07157	50572 9
7/32"	5"	3.9"	1.3"	0.20"	12			500 554 10	71	40 07157	22095 0
7/32"	6"	3.9"	1.3"	0.20"	12			500 556 10	77	40 07157	51811 8
7/32"	12"	3.9"	1.3"	0.20"	12			500 559 10	95	40 07157	50695 5
New! 1/4"	4"	3.9"	1.3"	0.24"	12			500 656 10	77	40 07157	51841 5
1/4"	6"	3.9"	1.3"	0.24"	12			500 655 10	89	40 07157	22096 7
1/4"	8"	3.9"	1.3"	0.24"	12			500 657 10	115	40 07157	51843 9
5/16" x 0.05"	7"	4.1"	1.5"	0.28"	12			500 086 10	129	40 07157	22097 4
5/16" x 0.05"	12"	4.1"	1.5"	0.31"	6			500 088 10	180	40 07157	51809 5
5/16" x 0.06"	7"	4.1"	1.5"	0.31"	6			500 096 10	150	40 07157	22098 1
3/8"	8"	4.1"	1.5"	0.31"	6			500 107 10	170	40 07157	50697 9

501



PZ								501		EAN-Code	Item No
1	3 1/8"	3.5"	1.1"	0.18"	12			501 102 10	51	40 07157	22101 8
2	4"	3.9"	1.3"	0.24"	12			501 203 10	79	40 07157	22102 5
3	6"	4.1"	1.5"	0.31"	6			501 305 10	138	40 07157	31330 0

502



PH								502		EAN-Code	Item No
0	2 3/8"	3.2"	1"	0.12"	12			502 001 10	26	40 07157	22106 3
1	3 1/8"	3.5"	1.1"	0.18"	12			502 102 10	51	40 07157	22107 0
1	8"	3.5"	1.1"	0.18"	12			502 107 10	70	40 07157	22111 7
2	4"	3.9"	1.3"	0.24"	12			502 203 10	79	40 07157	22108 7
2	6"	3.9"	1.3"	0.24"	12			502 205 10	85	40 07157	51845 3
2	8"	3.9"	1.3"	0.24"	6			502 207 10	99	40 07157	22112 4
2	12"	3.9"	1.3"	0.24"	6			502 209 10	99	40 07157	51381 6
3	6"	4.1"	1.5"	0.31"	6			502 305 10	138	40 07157	31331 7

Stubby



						500 502		EAN-Code	Item No
7/32"	1"	2.2"	1.4"	0.20"	12	500 550 10	35	40 07157	22099 8
PH 1	1"	2.2"	1.4"	0.18"	12	502 010 10	35	40 07157	22109 4
PH 2	1"	2.2"	1.4"	0.24"	12	502 020 10	38	40 07157	22110 0

507



Torx TR						507		EAN-Code	Item No
10	4"	3.2"	1"	0.14"	12	507 103 40	46	40 07157	32234 0
15	4"	3.5"	1.1"	0.16"	12	507 153 40	48	40 07157	32236 4
20	4"	3.9"	1.3"	0.16"	12	507 203 40	69	40 07157	32238 8
25	4"	3.9"	1.3"	0.20"	12	507 253 40	69	40 07157	32240 1
27	4"	3.9"	1.3"	0.20"	12	507 273 40	69	40 07157	32242 5
30	4 1/2"	4.1"	1.5"	0.24"	6	507 303 40	97	40 07157	32244 9
40	5"	4.1"	1.5"	0.31"	6	507 404 40	129	40 07157	32246 3

508



Torx						508		EAN-Code	Item No
5	2 3/8"	2.7"	0.8"	0.12"	12	508 051 40	27	40 07157	22188 9
6	2 3/8"	2.7"	0.8"	0.12"	12	508 061 40	27	40 07157	22154 4
7	2 3/8"	3.2"	1"	0.12"	12	508 071 40	27	40 07157	22156 8
8	2 3/8"	3.2"	1"	0.12"	12	508 083 40	29	40 07157	22157 5
9	2 3/8"	3.2"	1"	0.14"	12	508 093 40	29	40 07157	22158 2
10	4"	3.2"	1"	0.14"	12	508 103 40	45	40 07157	22159 9
15	4"	3.5"	1.1"	0.16"	12	508 153 40	45	40 07157	22160 5
20	4"	3.9"	1.3"	0.20"	12	508 203 40	69	40 07157	22161 2
25	4"	3.9"	1.3"	0.20"	12	508 253 40	69	40 07157	22162 9
27	4"	3.9"	1.3"	0.20"	12	508 273 40	69	40 07157	22163 6
30	4 1/2"	4.1"	1.5"	0.24"	6	508 303 40	96	40 07157	22164 3
40	5"	4.1"	1.5"	0.31"	6	508 404 40	143	40 07157	22165 0
45	5"	4.1"	1.5"	0.31"	6	508 454 40	143	40 07157	22166 7

500



1/8"	3 1/8"	3.2"	1"	0.12"	6	
1/8"	8"	3.2"	1"	0.12"	6	
9/64"	4"	3.2"	1"	0.14"	6	
9/64"	10"	3.2"	1"	0.14"	6	
5/32"	4"	3.5"	1.1"	0.16"	6	
5/32"	8"	3.5"	1.1"	0.16"	6	

500


500 032 30



38

EAN-Code

40 07157 **51681** 7



501



PZ						
1	3 1/8"	3.5"	1.1"	0.18"	6	
2	4"	3.9"	1.3"	0.24"	6	
2	8"	3.9"	1.3"	0.24"	6	

501


501 102 30



61

EAN-Code

40 07157 **51677** 0



502



PH						
1	3 1/8"	3.5"	1.1"	0.18"	6	
1	8"	3.5"	1.1"	0.18"	6	
2	4"	3.9"	1.3"	0.24"	6	
2	8"	3.9"	1.3"	0.24"	6	

502


502 102 30



61

EAN-Code

40 07157 **51673** 2



508



Torx						
10	4"	3.2"	1"	0.14"	6	
15	4"	3.5"	1.1"	0.16"	6	
20	4"	3.9"	1.3"	0.20"	6	
25	4"	3.9"	1.3"	0.20"	6	

508

508 103 30



55

EAN-Code

40 07157 **51665** 7



520



5/32"	6"	3.5"	1.1"	0.16"	6	520		EAN-Code	Item No
						520 045 10	66	40 07157	50072 4
7/32"	6"	3.9"	1.3"	0.22"	6	520 055 10	92	40 07157	50074 8

522



PH									
1	6"	3.5"	1.1"	0.16"	6	522		EAN-Code	Item No
						522 105 10	67	40 07157	50076 2
2	6"	3.9"	1.3"	0.22"	6	522 205 10	91	40 07157	50078 6

538



1/4"									
	4"	3.9"	1.3"		6	538		EAN-Code	Item No
						538 100 40	123	40 07157	51397 7

538



1/4"									
	4"	3.9"	1.3"		6	538		EAN-Code	Item No
						538 125 40	103	40 07157	32348 4

500



500 | 502



EAN-Code

Set 6 pcs.

500 961 17

549

40 07157 **50174** 5

(4 x) **500:** 9/64" x 4" | 5/32" x 4" | 7/32" x 5" | 1/4" x 6"

(2 x) **502:** PH 1 x 3 1/8" | PH 2 x 4"

500



500 | 502



EAN-Code

Set 6 pcs.

500 961 18


556

40 07157 **53521** 4

(4 x) **500:** 9/64" x 4" | 5/32" x 4" | 7/32" x 5" | 1/4" x 6"

(2 x) **502:** PH 1 x 3 1/8" | PH 2 x 4"

500



500 | 502 | 508



EAN-Code

M-TEC Set 7 pcs.

500 971 37


625

40 07157 **51699 2**

(3 x) **500:** 1/8" x 3 1/8" | 9/64" x 4" | 5/32" x 4"

(2 x) **502:** PH 1 x 3 1/8" | PH 2 x 4"

(2 x) **508:** Torx 10 x 4" | Torx 15 x 4"



508



507 | 508



EAN-Code **Item No**



Set 7 pcs.

507 971 48

600

40 07157 **50200** 1

(7 x) **507:** Torx TR 10 | Torx TR 15 | Torx TR 20 | Torx TR 25
Torx TR 27 | Torx TR 30 | Torx TR 40



Set 7 pcs.

508 973 48

600

40 07157 **50981** 9

(7 x) **508:** Torx 6 | Torx 8 | Torx 10 | Torx 15
Torx 20 | Torx 25 | Torx 30



Set 7 pcs.

508 972 48

600

40 07157 **50979** 6

(7 x) **508:** Torx 9 | Torx 10 | Torx 15 | Torx 20 |
Torx 25 | Torx 30 | Torx 40

500



500



EAN-Code **Item No**

Case 11-pcs

500 111 16

964

40 07157 **32558** 7

(4 x) **500:** 5/32" x 4" | 7/32" x 1" | 7/32" x 5" | 1/4" x 6"

501: PZ 2 x 4"

(3 x) **502:** PH 1 x 3 1/8" | PH 2 x 1" | PH 2 x 4"


(2 x) **613:** 3/32" x 3" | 9/64" x 4"



AC 1000V
IEC 60900 : 2004


361: Mains testing screwdriver VDE 0680. 220-225V

handles manufactured
from shock-proof
polypropylene




ergonomically refined
design

steelcap




The strongest of series 200 Serie 206

steelcap / full length blade
hexagon bolster /hexagon blade



hexagon bolster


anti-roll handle design



hexagon blades manufactured from
chrome-molybdenum-vanadium steel




GS tested for safety



superior torque
which exceeds DIN
and ISO requirements
by up to 100%




EAN code
on every product




black tip
for precision fit

full length blade




206




								206		EAN-Code	Item No
7/32"	4"	3.9"	1.3"	0.20"	12			206 055 90	75	40 07157	31690 5
1/4"	5"	3.9"	1.3"	0.26"	12			206 065 90	100	40 07157	24036 1
5/16"	6"	4.1"	1.2"	0.31"	6			206 080 90	180	40 07157	30876 4
3/8"	7"	4.1"	1.2"	0.31"	6			206 100 90	231	40 07157	13166 9
1/2"	8"	4.1"	1.2"	0.39"	6			206 120 90	310	40 07157	31692 9

226




PH								226		EAN-Code	Item No
2	4"	3.9"	1.3"	0.26"	12			226 203 90	109	40 07157	31698 1
3	6"	4.1"	1.2"	0.31"	6			226 305 90	186	40 07157	31700 1

206




								206 226		EAN-Code	Item No
Set 5 pcs.								206 951 98	755	40 07157	31720 9
(3 x) 206:	7/32" x 4" 1/4" x 5" 5/16" x 6"										
(2 x) 226:	PH 2 x 4" PH 3 x 6"										



handles manufactured from shock-proof polypropylene




GS tested for safety




ergonomically refined design



High quality and comprehensive range Series 200






blades manufactured from chrome-molybdenum-vanadium steel



superior torque which exceeds DIN and ISO requirements by up to 100%



hanging hole for easy storage or inserting lever



EAN code on every product



black tip for precision fit





																			
200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200	200
3/32"	3"	3.2"	1"	0.10"	12		200 022 90	22	40 07157	13001	3								
1/8"	3 1/8"	3.2"	1"	0.12"	12		200 032 90	26	40 07157	13003	7								
9/64"	4"	3.2"	1"	0.14"	12		200 353 90	29	40 07157	13035	8								
5/32"	4"	3.5"	1.1"	0.16"	12		200 043 90	42	40 07157	13010	5								
3/16"	5"	3.5"	1.1"	0.20"	12		200 054 90	54	40 07157	13016	7								
7/32"	5"	3.9"	1.3"	0.20"	12		200 554 90	68	40 07157	13041	9								
1/4"	5"	3.9"	1.3"	0.24"	12		200 654 90	80	40 07157	16050	8								
5/16"	7"	4.1"	1.2"	0.28"	12		200 086 90	123	40 07157	13028	0								
3/8"	8"	4.1"	1.2"	0.31"	6		200 107 90	159	40 07157	13032	7								

202



PH						202		EAN-Code	Item No
0	2 3/8"	3.2"	1"	0.12"	12	202 001 90	24	40 07157	13099 0
1	3 1/8"	3.5"	1.1"	0.18"	12	202 102 90	47	40 07157	13106 5
2	4"	3.9"	1.3"	0.24"	12	202 203 90	74	40 07157	13111 9
3	6"	4.1"	1.2"	0.31"	6	202 305 90	135	40 07157	13117 1

Stubby



								200 202		EAN-Code	Item No
7/32"	1"	2.3"	1.3"	0.20"	12			200 550 90	30	40 07157	13037 2
1/4"	1"	2.3"	1.3"	0.24"	12			200 650 90	33	40 07157	13045 7
PH 2	1"	2.3"	1.3"	0.24"	12			202 020 90	33	40 07157	13103 4

200



200 | 202



EAN-Code Item No

Set 5 pcs.

200 951 98

347

40 07157 **16052** 2

(3 x) 200: 9/64" x 4" | 5/32" x 4" | 7/32" x 5"

(2 x) 202: PH 1 x 3 1/8" | PH 2 x 4"

200



200 | 202



EAN-Code Item No

Set 7 pcs.

200 972 98

579

40 07157 **16054** 6

(5 x) 200: 9/64" x 4" | 5/32" x 4" | 7/32" x 5"

1/4" x 6" | 5/16" x 7"

(2 x) 202: PH 1 x 3 1/8" | PH 2 x 4"





2001-02-21

[Dns, 200-02-0000] R11

ESD-APPROVAL CERTIFICATE

Validity of the approval
Until 2004-02-21.

Holder of the approval
Felix-Werkhagshälsch Richard-Lenz GmbH, Neusand, Germany

Category of product
Hand tools

Products

Manufacturer / supplier	Type designation	Description
Felix-Werkhagshälsch Richard-Lenz GmbH	250-ESD	Screwdrivers with black, grey and blue plastic handles
Felix-Werkhagshälsch Richard-Lenz GmbH	280-ESD	Screwdrivers in different sizes with grey plastic handles

Documentation for approval
Test report F1 05047

The ESD approval does not include any requirements on electrical safety properties. If work will be performed close to live voltages, requirements according to The Swedish National Electric Safety Board shall be obeyed. For other countries corresponding regulations are applicable.

Conditions for approval
General conditions, according to SP-Method 2473, for approval and registration of approval products with regard to ESD-protection questions.

SP Swedish National Testing and Research Institute
Electronics - ESD Protection

Anders Nilsson
Technical Manager

Örme Rydholm
Technical Officer

This is a translation of the Swedish original document.

Borås, 2001-02-21


Anders Nilsson
ESEA Rydholm

Box 367
401 06, KÖPENH.
Tel. 0045-18 33 00

Box 333
7400 Roskilde
Tel. 45 46 10 00

2001-02-21

Dnr 230-01-0001

3/01

ESD – GODKÆNNANDE

Godkønnende gillighedsattest

T + m 2004-02-21.

Indehavere af godkønnende

Foto-Workshop ApS, Høland-Lets GmbH, Nørreåb, Tyskland

Produktbeting

Handwriting

Produktet

Tilførsels- / leverandør:
Foto-Workshop ApS
Høland-Lets GmbH
Foto-Workshop ApS
Høland-Lets GmbH

Typoskriftning, stiletter
230-ESD

230-ESD

Beskrivelse
Stemmerør med sorte, grå og
blå plettering
Stemmerør i røde stiletter med
grå plettering.

Underlag for godkønnende

Prøvningsrapport P1 03147.

ESD-godkønnende indeholder et brev på etableringsgrundlaget. Ved at være med farlig oplysning skal Etableringsbrevets fredsretter tillægges. For andre lande skal motoriserede Beskrivelser tillægges.

Vilkår for godkønnende

Allemaal vilkår, enligt SP-Metod 2072. En godkønnende skal tilføjes i Etablering over produkter som godkønnende og eventuelt på ESD-aflytningsskemaet.

SP Sveriges Prøvnings- og Forskningsinstitut Elektronik - ESD-skyl



Anders Nilsson
Teknisk ansvarig


Søren Jørgensen
Teknisk hovedansvar

Commitment to fine,
traditional hand tools

Series 330

335



335 | 337

Set 5 pcs.

335 951 98



EAN-Code **Item No**

420

40 07157 **22155 1**

(3 x) **335:** 7/32" x 3 1/2" | 9/32" x 5" | 23/64" x 6 1/2"

(2 x) **337:** PH 1 x 3 1/8" | PH 2 x 3 1/2"



Series 490

490



Awl



2 3/8"



2 3/8"



1.3"



0.16"



12

490

490 041 10



38

EAN-Code Item No

40 07157 31078 1

493



Awl



4"



3 1/8"



1.3"



0.24"



12

493

493 063 10



72

EAN-Code Item No

40 07157 23006 5

498



Reamer



4"



3 1/8"



1.3"



0.24"



12

498

498 063 10

6.43



72

EAN-Code Item No

40 07157 23013 3

494



Tacklifter



4"



3 1/8"



1.3"



12

494


494 003 30




79

EAN-Code Item No

40 07157 24022 4



handles manufactured from shock-proof polypropylene




ergonomically refined design



GS tested for safety


Excellent value for money Serie 800

anti-roll handle design




blades manufactured from chrome-vanadium steel

hanging hole for easy storage or inserting lever



hardened and tempered to exceed DIN and ISO specifications

EAN code on every product



Torx blades are phosphated for precision fit






800



Blade: CV-Ni
Handle: PPC



800



EAN-Code Item No


1/8"	3 1/8"	3.2"	1"	0.12"	12		800 032 90	25	40 07157 17000 2
9/64"	4"	3.2"	1"	0.14"	12		800 353 90	29	40 07157 17011 8
5/32"	4"	3.5"	1.1"	0.16"	12		800 043 90	42	40 07157 17002 6
3/16"	6"	3.9"	1.3"	0.20"	12		800 505 90	71	40 07157 28010 7
7/32"	3 1/2"	3.9"	1.3"	0.20"	12		800 553 90	64	40 07157 28012 1
7/32"	5"	3.9"	1.3"	0.20"	12		800 554 90	68	40 07157 17013 2
1/4"	4"	3.9"	1.3"	0.24"	12		800 653 90	74	40 07157 28013 8
1/4"	6"	3.9"	1.3"	0.24"	12		800 655 90	85	40 07157 17015 6
5/16"	6"	4.1"	1.5"	0.28"	12		800 705 90	114	40 07157 17017 0
5/16" x 0.06"	7"	4.1"	1.5"	0.31"	12		800 096 90	143	40 07157 17004 0



805



Blade: CV-Ni
Handle: PPC



805



EAN-Code Item No

5/16"	6"	4.1"	1.2"	0.31"	12		805 805 90	141	40 07157 28017 6
3/8"	7"	4.1"	1.2"	0.31"	12		805 100 90	192	40 07157 30768 2
1/2"	8"	4.1"	1.2"	0.39"	6		805 120 90	227	40 07157 50274 2

802



Blade: CV-Ni
Handle: PPC



PH						802		EAN-Code	Item No
0	2 3/8"	3.2"	1"	0.12"	12	802 001 90	24	40 07157	17055 2
1	3 1/8"	3.5"	1.1"	0.18"	12	802 102 90	47	40 07157	17026 2
2	4"	3.9"	1.3"	0.24"	12	802 203 90	74	40 07157	17028 6
3	6"	4.1"	1.5"	0.31"	6	802 305 90	135	40 07157	17056 9

Stubby



Blade: CV-Ni
Handle: PPC



						800		EAN-Code	Item No
7/32"	1"	2.2"	1.4"	0.20"	12	800 550 90	30	40 07157	28011 4
PH 2	1"	2.2"	1.4"	0.24"	12	802 020 90	33	40 07157	17057 6

808



Blade: CMV-BC
Handle: PPC



Torx						808		EAN-Code	Item No
6	2 3/8"	3.2"	1"	0.12"	12	808 061 90	24	40 07157	17046 0
7	2 3/8"	3.2"	1"	0.12"	12	808 071 90	24	40 07157	17047 7
8	2 3/8"	3.2"	1"	0.12"	12	808 083 90	25	40 07157	17048 4
10	4"	3.5"	1.1"	0.14"	12	808 103 90	40	40 07157	17049 1
15	4"	3.5"	1.1"	0.16"	12	808 153 90	42	40 07157	17050 7
20	4"	3.9"	1.3"	0.20"	12	808 203 90	65	40 07157	17051 4
25	4"	3.9"	1.3"	0.20"	12	808 253 90	65	40 07157	17052 1
27	4"	3.9"	1.3"	0.20"	12	808 273 90	65	40 07157	17053 8
30	4 1/2"	4.1"	1.5"	0.24"	6	808 303 90	88	40 07157	17054 5

800



800 | 802



EAN-Code Item No

Set 5 pcs.

25

800 951 98

348

40 07157 28005 3

[3 x] 800: 9/64" x 4" | 5/32" x 4" | 7/32" x 5"

[2 x] 802: PH 1 x 3 1/8" | PH 2 x 4"

800



800 | 802



EAN-Code Item No

Set 7 pcs.

15

800 972 98

592

40 07157 28009 1

[5 x] 800: 9/64" x 4" | 5/32" x 4" | 7/32" x 5" | 1/4" x 6"

805: 5/16" x 6"  Blade

[2 x] 802: PH 1 x 3 1/8" | PH 2 x 4"

Set 7 pcs. Torx

15

808 970 18

492

40 07157 28003 9

[7 x] 808: Torx 8 | Torx 10 | Torx 15 | Torx 20 | Torx 25 | Torx 27 | Torx 30



Ergonic, the first handle that adapts to the user's hand!



**smooth, seamless
handle for maximum
comfort**

**hand and handle
interlock, causing
less strain**

VDE
Serie 400 ***ergonic***® (pat.)

**stronger
adaptable
truly ergonomic**


AC 1000V
IEC 60900 : 2004



**blades manufactured from
chrome-molybdenum-
vanadium steel**

**hanging hole for easy storage or
inserting lever**

anti-roll handle design



**superior torque which
exceeds DIN and ISO
requirements by
up to 100%**

GS tested for safety



EAN code on every product



**black tip for
precision fit**

screw symbols on handle cap



full length, impact proof handle core



413



AC 1000V
IEC 60900 : 2004




							413		EAN-Code	Item No
	3/32"	3"	3.4"	1"	0.10"	12	413 025 90	22	40 07157	53133 9
	1/8"	4"	3.4"	1"	0.12"	12	413 030 90	28	40 07157	53135 3
	9/64" x 0.027"	4"	3.4"	1"	0.14"	12	413 035 90	30	40 07157	53139 1
New!	9/64" x 0.031"	4"	3.4"	1"	0.14"	12	413 038 90	34	40 07157	61731 6
	5/32"	4"	3.7"	1.2"	0.14"	12	413 040 90	44	40 07157	53141 4
	3/16"	5"	3.9"	1.3"	0.18"	12	413 045 90	73	40 07157	53143 8
	7/32"	5"	3.9"	1.3"	0.18"	12	413 055 90	70	40 07157	53145 2
	1/4"	6"	4.2"	1.4"	0.22"	6	413 065 90	86	40 07157	53147 6
	5/16"	7"	4.4"	1.5"	0.28"	6	413 080 90	135	40 07157	53149 0


414




AC 1000V
IEC 60900 : 2004



PH							414		EAN-Code	Item No
0	2 3/8"	3.4"	1"	0.12"	12	12	414 001 90	25	40 07157	53151 3
1	3 1/8"	3.7"	1.2"	0.20"	12	12	414 102 90	52	40 07157	53153 7
2	4"	4.2"	1.4"	0.24"	12	12	414 203 90	80	40 07157	53155 1
3	6"	4.4"	1.5"	0.31"	6	6	414 304 90	145	40 07157	53157 5



100% testing (10.000 V)



+ 5 additional tests on every material lot

413



413

AC 1000V
IEC 60900 : 2004



Set 3 pcs.VDE

413 931 94



EAN-Code Item No

240

40 07157 **53175 9**

(2 x) **413:** 5/32" x 4" | 7/32" x 5"

414: PH 2 x 4"

413



413 | 414

AC 1000V
IEC 60900 : 2004



Set 6 pcs. VDE

413 961 98



EAN-Code Item No

460

40 07157 **53169 8**

(4 x) **413:** 1/8" x 4" | 5/32" x 4" | 7/32" x 5" | 1/4" x 6"

(2 x) **414:** PH 1 x 3 1/8" | PH 2 x 4"



The Original VDE Serie 500

The leaders in • handle-design • blade quality
• 2-component-technology

513



AC 1000V
IEC 60900 : 2004

						513		EAN-Code	Item No
3/32"	3"	2.7"	0.8"	0.10"	12	513 025 90	22	40 07157	22141 4
1/8"	4"	2.7"	0.8"	0.12"	12	513 030 90	28	40 07157	22113 1
9/64"	4"	2.7"	0.8"	0.14"	12	513 035 90	30	40 07157	22114 8
5/32"	4"	3.2"	1"	0.14"	12	513 040 90	44	40 07157	22115 5
3/16"	5"	3.9"	1.3"	0.18"	12	513 045 90	73	40 07157	50124 0
7/32"	5"	3.9"	1.3"	0.18"	12	513 055 90	70	40 07157	22116 2
1/4"	6"	3.9"	1.3"	0.22"	6	513 065 90	86	40 07157	22117 9
5/16"	7"	4.1"	1.5"	0.28"	6	513 080 90	135	40 07157	22118 6

514



AC 1000V
IEC 60900 : 2004

PH						514		EAN-Code	Item No
0	2 3/8"	3.2"	1"	0.12"	12	514 001 90	25	40 07157	22142 1
1	3 1/8"	3.5"	1.1"	0.20"	12	514 102 90	52	40 07157	22119 3
2	4"	3.9"	1.3"	0.24"	12	514 203 90	80	40 07157	22120 9
3	6"	4.1"	1.5"	0.31"	6	514 304 90	145	40 07157	22143 8

518



AC 1000V
IEC 60900: 2004



Bitholder					518		EAN-Code	Item No
1/4"	4"	3.9"	1.3"	6	518 125 40	103	40 07157	50785 3

513



AC 1000V
IEC 60900 : 2004



EAN-Code **Item No**

VDE Set 6 pcs.

513 | 514

463

40 07157 **50176 9**

(4 x) **513:** 1/8" x 4" | 9/64" x 4" | 5/32" x 4" | 7/32" x 5"

(2 x) **514:** PH 1 x 3 1/8" | PH 2 x 4"

New!

513



AC 1000V
IEC 60900 : 2004



EAN-Code

Set 6-pcs.

513

487

40 07157 **50120 2**

(3 x) **513:** 9/64"x4" | 5/32"x4" | 7/32"x5"

(2 x) **514:** PH 1 x 1 1/8" | PH 2 x 4"

361: **Mains testing screwdriver** VDE 0680/6, 220-250 Volt

020



AC 1000V
IEC 60900 : 2004



020



EAN-Code Item No

E-Pro	6	020 912 06	218	40 07157 51427 1
-------	---	------------	-----	------------------

518:	1/4" x 4" Bit Holder
------	----------------------

(4 x) 020:	1/8" 5/32" 7/32" 9/32"
-------------	------------------------------

(2 x) 021:	PZ 1 / PZ 2
-------------	-------------

(3 x) 022:	PH 0 / PH 1 / PH 2
-------------	--------------------

(2 x) 026:	Torx 15 / Torx 20
-------------	-------------------

E-Pro SQ	6	020 912 26	218	40 07157 53235 0
----------	---	------------	-----	------------------

518:	1/4" x 4" Bit Holder
------	----------------------

(4 x) 020:	1/8" 5/32" 7/32" 9/32"
-------------	------------------------------

(3 x) 022:	PH 0 / PH 1 / PH 2
-------------	--------------------

(4 x) 025:	SQ 0 SQ 1 SQ 2 SQ 3
-------------	---------------------------

VDE Serie 600

High quality and
comprehensive range



AC 1000V
IEC 60900 : 2004

613

613 | 614



EAN-Code Item No

VDE Set 7 pcs.	613 973 97	483	40 07157 51401 1
----------------	------------	-----	------------------

(5 x) 613:	3/32" x 3" 1/8" x 4" 9/64" x 4" 5/32" x 4" 7/32" x 5
-------------	--

(2 x) 614:	PH 1 x 3 1/8" PH 2 x 4"
-------------	---------------------------

easy adjustment
of torque


coloured ring indicating torque range




Torque screwdrivers with precise adjustment Serie Nm (pat.)

ergonomically refined design


blades manufactured from
chrome-molybdenum-
vanadium steel



superior torque which
exceeds DIN and ISO
requirements by
up to 100%




Precise release – indicated
by acoustic and mechanic
signals



black tip
for precision fit

exchangeable blades for greatest
flexibility in all areas of use



100



100



EAN-Code Item No

Nm-Box 0,6 Nm – 1,5 Nm (5.3 – 13.3 lb-in)

100 991 16

1190

40 07157 **52039 5**

(12 x) Torx 6 | Torx 7 | Torx 8

IP 6 | IP 7 | IP 8 | IP 9

1/8" | 9/64"

PH 0

PZ 0

Magnetic Bitholder**Handle** 5.3 - 13.3 lb-in**Adjustment Tool****Metal Case:** L: 8 5/8" W: 4 5/16" H: 1 3/8"

100



EAN-Code Item No

Nm-Box 1,5 Nm – 3,0 Nm (13.3 - 26.6 lb-in)

100 992 16

1201

40 07157 **52041 8**

(12 x) Torx 9 | Torx 10 | Torx 15

IP 9 | IP 10 | IP 15

5/32"

PH 1 | PH 2


PZ 1 | PZ 2

Magnetic Bitholder**Handle** 13.3 - 26.6 lb-in**Adjustment Tool****Metal Case:** L: 8 5/8" W: 4 5/16" H: 1 3/8"

100




100



100

Nm-Box 3.0 Nm - 5.4 Nm (26.6-47.8 lb-in)							
(12 x)	Torx 15 Torx 20 Torx 25						
	IP 9 IP 10 IP 15						
	5/32"						
	PH 1 PH 2						
	PZ 1 PZ 2						
	Magnetic Bitholder						
	Handle 26.6-47.8 lb-in						
	Adjustment Tool						
	Metal Case: L: 8 5/8" W: 4 5/16" H: 1 3/8"						

100



Handle	Nm max						
5.3 - 13.3 lb-in		4.13"	1.26"	1	100 001 06	142	40 07157 52149 1
13.3 - 26.6 lb-in		4.13"	1.26"	1	100 002 06	144	40 07157 52151 4
26.6 - 47.8 lb-in		4.13"	1.26"	1	100 003 06	148	40 07157 52153 8

100



100

Torque-Seal	5/16"	0.24"	1				

100



100

Adjustment-Key 6mm	3 3/8"	1/4"	1				

108



		Nm max			108		EAN-Code
Torx 6	6 3/4"		1/4"	1	108 061 04	43	40 07157 51991 7
Torx 7	6 3/4"		1/4"	1	108 071 04	43	40 07157 51993 1
Torx 8	6 3/4"		1/4"	1	108 083 04	43	40 07157 51995 5
Torx 9	6 3/4"		1/4"	1	108 093 04	43	40 07157 51997 9
Torx 10	6 3/4"		1/4"	1	108 103 04	43	40 07157 51999 3
Torx 15	6 3/4"		1/4"	1	108 153 04	44	40 07157 52001 2
Torx 20	6 3/4"		1/4"	1	108 203 04	45	40 07157 52003 6
Torx 25	6 3/4"		1/4"	1	108 253 04	46	40 07157 52005 0
IP 6	6 3/4"		1/4"	1	109 061 04	43	40 07157 52007 4
IP 7	6 3/4"		1/4"	1	109 071 04	43	40 07157 52009 8
IP 8	6 3/4"		1/4"	1	109 083 04	43	40 07157 52011 1
IP 9	6 3/4"		1/4"	1	109 093 04	43	40 07157 52013 5
IP 10	6 3/4"		1/4"	1	109 103 04	43	40 07157 52015 9
IP 15	6 3/4"		1/4"	1	109 153 04	44	40 07157 52017 3
1/8"	6 3/4"		1/4"	1	100 032 04	43	40 07157 52019 7
9/64"	6 3/4"		1/4"	1	100 353 04	44	40 07157 52021 0
5/32"	6 3/4"		1/4"	1	100 043 04	44	40 07157 52023 4
New! 7/32"	6 3/4"		1/4"	1	100 554 04	45	40 07157 61245 8
PH 0	6 3/4"		1/4"	1	102 001 04	43	40 07157 52025 8
PH 1	6 3/4"		1/4"	1	102 102 04	45	40 07157 52027 2
PH 2	6 3/4"		1/4"	1	102 203 04	46	40 07157 52029 6
PZ 0	6 3/4"		1/4"	1	101 001 04	43	40 07157 52031 9
PZ 1	6 3/4"		1/4"	1	101 102 04	45	40 07157 52033 3
PZ 2	6 3/4"		1/4"	1	101 203 04	47	40 07157 52035 7
New! 1,5mm	6 3/4"		1/4"	1	104 015 04	43	41 07157 61625 8
New! 2mm	6 3/4"		1/4"	1	104 020 04	43	42 07157 61627 2
New! 2,5mm	6 3/4"		1/4"	1	104 025 04	43	43 07157 61629 6
New! 3mm	6 3/4"		1/4"	1	104 030 04	44	44 07157 61631 9
New! 4mm	6 3/4"		1/4"	1	105 040 04	44	45 07157 61633 3
Bitholder	6 3/4"		1/4"	1	118 125 04	65	40 07157 52037 1

1/4"

New!

108



AC 1000V
IEC 60900 : 2004



Nm VDE		Nm max			100		EAN-Code
9/64"	6 3/4"		1/4"	1	100 353 14	23	40 07157 61651 7
5/32"	6 3/4"		1/4"	1	100 043 14	24	40 07157 61653 1
7/32"	6 3/4"		1/4"	1	100 554 14	26	40 07157 61655 5
PH1	6 3/4"		1/4"	1	102 102 14	26	40 07157 61657 9
PH2	6 3/4"		1/4"	1	102 203 14	31	40 07157 61659 3
PZ1	6 3/4"		1/4"	1	101 102 14	26	40 07157 61661 6
PZ2	6 3/4"		1/4"	1	101 203 14	31	40 07157 61663 0
H2 +/-	6 3/4"		1/4"	1	106 203 14	31	40 07157 61665 4
Z2 +/-	6 3/4"		1/4"	1	107 203 14	31	40 07157 61667 8

freely rotating cap
for minimal friction

hanging hole for easy
storage or inserting lever



EAN code on every
product

felo Precision Screwdrivers are setting the standards in all functional aspects. Serie 240/250

pleasant soft grip
material for added
comfort

ergonomically refined
design

anti-roll handle design

full-length
polypropylene core

blades manufactured from
chrome-molybdenum-
vanadium steel




felo Precision Screw-
drivers are also availa-
ble with ceramic
blades or manufactu-
red to ESD standards.

ESD Safe
 $10^8 - 10^{10} \Omega$



superior torque which
exceeds DIN and ISO
requirements by
up to 100%



black tip for precision fit



240



							240		EAN-Code	Item No
1/16"	2 3/8"	3 1/2"	0.8"	0.10"	12		240 151 50	19	40 07157	31738 4
5/64"	2 3/8"	3 1/2"	0.8"	0.10"	12		240 201 50	20	40 07157	31740 7
3/32"	2 3/8"	3 1/2"	0.8"	0.10"	12		240 252 50	20	40 07157	31742 1
3/32"	6"	3 1/2"	0.8"	0.10"	12		240 255 50	25	40 07157	31744 5
3/32"	8"	3 1/2"	0.8"	0.10"	12		240 257 50	27	40 07157	31746 9
1/8"	2 3/8"	3 1/2"	0.8"	0.12"	12		240 033 50	22	40 07157	31748 3
1/8"	4"	4"	0.8"	0.12"	12		240 035 50	25	40 07157	31750 6
1/8"	8"	4"	0.8"	0.12"	12		240 037 50	30	40 07157	31752 0
New! 9/64"	2 3/8"	3 1/2"	0.8"	0.12"	12		240 333 50	24	40 07157	61307 3
9/64"	4"	4"	0.8"	0.14"	12		240 353 50	26	40 07157	31754 4
9/64"	6"	4"	0.8"	0.14"	12		240 355 50	29	40 07157	31756 8
9/64"	10"	4"	0.8"	0.14"	12		240 358 50	36	40 07157	31758 2
5/32"	4"	4"	0.8"	0.16"	12		240 043 50	28	40 07157	31760 5
5/32"	6"	4"	0.8"	0.16"	12		240 045 50	33	40 07157	31762 9
5/32"	8"	4"	0.8"	0.16"	12		240 047 50	38	40 07157	31764 3

242



PH							242		EAN-Code	Item No
000	2 3/8"	3 1/2"	0.8"	0.10"	12		242 000 50	20	40 07157	31770 4
00	2 3/8"	3 1/2"	0.8"	0.10"	12		242 009 50	20	40 07157	31772 8
0	2 3/8"	3 1/2"	0.8"	0.12"	12		242 001 50	21	40 07157	31774 2
1	3 1/8"	4"	0.8"	0.18"	12		242 102 50	31	40 07157	31776 6
1	6"	4"	0.8"	0.18"	12		242 105 50	40	40 07157	31778 0



246



mm							246		EAN-Code Item No
1.5 mm	2 3/8"	3 1/2"	0.8"	0.06"	12		246 151 50	18	40 07157 31782 7
2 mm	2 3/8"	3 1/2"	0.8"	0.08"	12		246 201 50	18	40 07157 31784 1
2.5 mm	3"	3 1/2"	0.8"	0.10"	12		246 252 50	23	40 07157 31786 5
3 mm	3"	4"	0.8"	0.12"	12		246 302 50	26	40 07157 31788 9

248



Torx							248		EAN-Code Item No
5	2 3/8"	3 1/2"	0.8"	0.12"	12		248 051 50	21	40 07157 31790 2
6	2 3/8"	3 1/2"	0.8"	0.12"	12		248 061 50	22	40 07157 31792 6
7	2 3/8"	3 1/2"	0.8"	0.12"	12		248 071 50	22	40 07157 31794 0
8	2 3/8"	3 1/2"	0.8"	0.12"	12		248 081 50	22	40 07157 31796 4
9	2 3/8"	3 1/2"	0.8"	0.14"	12		248 091 50	24	40 07157 31798 8
10	4"	4"	0.8"	0.14"	12		248 103 50	28	40 07157 31800 8
10	10"	4"	0.8"	0.14"	6		248 108 50	30	40 07157 50276 6
15	4"	4"	0.8"	0.16"	12		248 153 50	29	40 07157 31802 2
15	10"	4"	0.8"	0.16"	6		248 158 50	32	40 07157 50278 0
20	10"	4"	0.8"	0.16"	6		248 208 50	34	40 07157 50280 3

249



mm						249		EAN-Code	Item No
3 mm	2 3/8"	4"	0.8"		6	249 300 50	28	40 07157	50709 9
3.5 mm	2 3/8"	4"	0.8"		6	249 350 50	28	40 07157	50711 2
4 mm	2 3/8"	4"	0.8"		6	249 400 50	28	40 07157	50713 6
4.5 mm	2 3/8"	4"	0.8"		6	249 450 50	28	40 07157	50715 0
5 mm	2 3/8"	4"	0.8"		6	249 500 50	28	40 07157	50717 4
5.5 mm	2 3/8"	4"	0.8"		6	249 550 50	28	40 07157	50719 8



240



Box 6 pcs.

240 | 248



EAN-Code **Item No**

240 961 56

200

40 07157 **31844 2**

(4 x) **240:** 1/16" x 2 3/8" | 5/64" x 2 3/8" | 3/32" x 2 3/8" | 1/8" x 2 3/8"

(2 x) **242:** PH 00 x 2 3/8" | PH 0 x 2 3/8"



Box 6 pcs.

248 961 56

200

40 07157 **31846 6**

(4 x) **248:** Torx 6 x 2 3/8" | Torx 7 x 2 3/8" | Torx 8 x 2 3/8" | Torx 9 x 2 3/8"

(2 x) **246:** Hex 1.5 mm x 2 3/8" | Hex 2.0 mm x 2 3/8"



280



		280		EAN-Code Item No
T 4 - Box I. 7 pcs.		280 907 06	161	40 07157 50723 5
[6 x]	Blade			
	1/16" - 1/8" 5/64" - 9/64" 3/32" - 5/32"			
	PH 1 - PH 0 PH 00 - PH 000			
	PZ 1 - PZ 0			
	Handle 4" x 3/4"			



T 4 - Box II. 7 pcs.		280 907 16	161	40 07157 50725 9
[6 x]	Blade			
	Hex 1.3 - 4.0 mm 1.5 - 2.0 mm 2.5 - 3.0 mm			
	Torx 6 - Torx 15 Torx 7 - Torx 10 Torx 8 - Torx 9			
	Handle 4" x 3/4"			



T 4 - Box III. 7 pcs.		280 907 26	161	40 07157 50727 3
[6 x]	Blade			
	5/64" - 9/64"			
	PH 1 - PH 0 PH 00 - PH 000			
	Torx 6 - Torx 15 Torx 7 - Torx 10 Torx 8 - Torx 9			
	Handle 4" x 3/4"			

280



				280		EAN-Code Item No
1/16" - 1/8"	4 5/16"	0.16"	1	280 153 14	12	40 07157 50729 7
5/64" - 9/64"	4 5/16"	0.16"	1	280 235 14	12	40 07157 50731 0
3/32" - 5/32"	4 5/16"	0.16"	1	280 245 14	12	40 07157 50733 4
PH 00 - PH 000	4 5/16"	0.16"	1	282 000 14	12	40 07157 50737 2
PH 1 - PH 0	4 5/16"	0.16"	1	282 001 14	12	40 07157 50735 8
PZ 1 - PZ 0	4 5/16"	0.16"	1	281 010 14	12	40 07157 50739 6
Hex 1.3 mm - 4 mm	4 5/16"	0.16"	1	284 134 14	12	40 07157 50741 9
Hex 1.5 mm - 2 mm	4 5/16"	0.16"	1	284 152 14	12	40 07157 50743 3
Hex 2.5 mm - 3 mm	4 5/16"	0.16"	1	284 253 14	12	40 07157 50745 7
Torx 6 - Torx 15	4 5/16"	0.16"	1	286 615 14	12	40 07157 50747 1
Torx 7 - Torx 10	4 5/16"	0.16"	1	286 710 14	12	40 07157 50749 5
Torx 8 - Torx 9	4 5/16"	0.16"	1	286 890 14	12	40 07157 50751 8

52

280

New!



4" 3/4"



280



EAN-Code Item No

T4 handle
for reversible blades

280 100 00

18

40 07157 51259 8

250



ESD Safe
10⁸ - 10¹⁰ Ω



250



EAN-Code Item No



1/16"	2 3/8"	4"	0.8"	0.10"	12
5/64"	2 3/8"	4"	0.8"	0.10"	12
3/32"	2 3/8"	4"	0.8"	0.10"	12
1/8"	2 3/8"	4"	0.8"	0.12"	12
1/8"	4"	4"	0.8"	0.12"	12

250 151 80

19

40 07157 31806 0

250 201 80

19

40 07157 31808 4

250 252 80

19

40 07157 31810 7

250 033 80

20

40 07157 31812 1

250 035 80

22

40 07157 31814 5

252



ESD Safe
10⁸ - 10¹⁰ Ω



252



EAN-Code Item No



PH	2 3/8"	4"	0.8"	0.08"	12
00	2 3/8"	4"	0.8"	0.08"	12
0	2 3/8"	4"	0.8"	0.12"	12
1	3 1/8"	4"	0.8"	0.18"	12

252 009 80

20

40 07157 31816 9

252 001 80

20

40 07157 31818 3

252 102 80

20

40 07157 31820 6

250



ESD Safe
10⁸ - 10¹⁰ Ω



250



EAN-Code Item No

ESD Box 6 pcs.

250 961 86

200

40 07157 31848 0

(4 x) 250: 1/16" x 2 3/8" | 5/64" x 2 3/8"
3/32" x 2 3/8" | 1/8" x 2 3/8"
(2 x) 252: PH 00 x 2 3/8" | PH 0 x 2 3/8"

ergonomically refined soft grip coating

2-component handle for added comfort

Made by professionals
for professionals

T-Griffe

strong, durable core for
the highest torque

hanging hole for easy
storage



Without soft-grip
coating: extreme
pressure points



With soft grip
coating: reduced
pressure points

EAN code on every product



GS tested for safety




blades made from chrome-vanadium
and chrome-molybdenum-vanadium

superior hardness which
exceeds DIN and ISO
requirements by
up to 100%



matt chrome-plated blades
with black tips for precision fit



308



Torx					308		EAN-Code Item No
10	5"	4"	0.14"	8	308 103 80	83	40 07157 50813 3
15	5"	4"	0.16"	8	308 153 80	83	40 07157 50815 7
20	5"	4"	0.20"	8	308 204 80	83	40 07157 32316 3
20	8"	4"	0.20"	8	308 207 80	95	40 07157 32318 7
25	5"	4"	0.20"	8	308 254 80	83	40 07157 32320 0
25	8"	4"	0.20"	8	308 257 80	95	40 07157 32322 4
27	8"	4"	0.20"	8	308 277 80	95	40 07157 32324 8
30	8"	4"	0.24"	8	308 307 80	113	40 07157 32326 2
40	8"	4"	0.31"	8	308 407 80	151	40 07157 32328 6
45	5 1/2"	4"	0.31"	8	308 455 80	128	40 07157 32330 9

338



				338		EAN-Code Item No
1/4"	5"	4"	6	338 125 80	111	40 07157 32350 7

303



Set 6 pcs.	308 962 84	600	EAN-Code Item No
(6 x) 308: Torx 10 Torx 15 Torx 20 Torx 25 Torx 27 Torx 30			40 07157 50849 2
Set 6 pcs.	308 961 84	700	EAN-Code Item No
(6 x) 308: Torx 20 Torx 25 Torx 27 Torx 30 Torx 40 Torx 45			40 07157 50783 9



Extremely strong ratcheting mechanism with super fine toothing:
885 lb/in (100 Nm) 72 teeth, 5° ratcheting angle



Sockets safely locked
and easily released by push-button

Handle permanently connected
to ratchet by injection molding

R-GO

1/4" tool sets with ERGONIC ratchet:
perfect and reliable without compromises



U.S. Patent No 7,877,843

Patented ERGONIC handle with
cushion effect:
the ultimate of comfort!

Each component available
individually

Practice oriented assortments
stored in robust StrongBox


Long lasting premium quality
in every detail:
Lifetime guarantee
on every component





New!

057



057





EAN-Code

1/4"



R-GO XL Inch	36-pce	057 836 56	955	40 07157 62053 8
	ERGONIC Ratchet 1/4"			
	ERGONIC Stubby 1/4"			
(13 x)	Sockets			
	1/8" 9/64" 5/32" 3/16" 7/32" 1/4" 9/32" 5/16" 11/32" 3/8" 7/16" 1/2" 9/16"			
(15 x)	Bits (C6,3 x 1/4")			
	3/16" 7/32"			
	SQ 0 SQ 1 SQ 2 SQ 3			
	PH1 PH2 PH3			
	Torx 8 Torx 10 Torx 15 Torx 20 Torx 25 Torx 30			
	Extension (4") 1/4" - 1/4"			
	Extension (2") 1/4" - 1/4"			
	U-Joint 1/4"			
	Bitholder E6,3 x 2 1/4"			
	Adapter E 6,3 - 1/4" (2")			
	Adapter 1/4" SQ - 1/4" Hex			
	StrongBox L: 9 1/2" W: 5 7/64" H: 2 9/32"			




New!

057



	R-GO M-Tec	Box 10-pcs	057		EAN-Code
		ERGONIC Ratchet 1/4"	057 810 06	1050g	40 07157 61553 4
		ERGONIC Screwdriver with 1/4" adapter for sockets			
(6 x)		M-Tec Nutdrivers			
		5,5mm 6mm 7mm 8mm 10mm 13mm			
		Extension (4") 1/4" - 1/4"			
		U-Joint 1/4"			
		StrongBox L: 9 1/2" W: 5 7/64" H: 2 9/32"			



New!

057



	R-GO 19 Inch	Box 19-pcs	057		EAN-Code
		ERGONIC Ratchet 1/4"	057 819 56	955g	40 07157 62055 2
		ERGONIC Screwdriver with 1/4" adapter for sockets			
(13 x)		Sockets			
		1/8" 9/64" 5/32" 3/16" 7/32" 1/4" 9/32" 5/16" 11/32" 3/8" 7/16" 1/2" 9/16"			
		Extension (4") 1/4" - 1/4"			
		Extension (2") 1/4" - 1/4"			
		U-Joint 1/4"			
		Adapter E 6,3 - 1/4" (2")			
		StrongBox L: 9 1/2" W: 5 7/64" H: 2 9/32"			



New!

057

1/4"



R-GO 36 Box 36-pcs

ERGONIC Ratchet 1/4"

ERGONIC 438 Screwdriver with Bitholder

(30 x)

Bits (C6,3 x 25mm)

1/8" | 3/16" | 7/32" | 1/4"

2mm | 3mm | 4mm | 5mm | 6mm

PH0 | PH1 | PH2 | PH3

PZ1 | PZ2 | PZ3

Torx 5 | Torx 6 | Torx 7 | Torx 8 | Torx 10 | Torx 15 | Torx 20 | Torx 25 | Torx 30 | Torx 40

SQ1 | SQ2

Spanner 6 | Spanner 8

Extension (4") 1/4" - 1/4"

Extension (2") 1/4" - 1/4"

Bitholder E6,3 x 2 1/2"

Adapter 1/4" SQ - 1/4" Hex

StrongBox L: 9 1/2" W: 5 7/64" H: 2 9/32"

057

057 836 06



900g

EAN-Code

40 07157 61557 2



looking for
innovations?



New!

497



497

497 635 41



128

EAN-Code

40 07157 61481 0



looking for
innovations?





Super strong ratcheting mechanism with fine toothing:
575 lb/in (65 Nm) 60 teeth, 6° ratcheting angle

Direct fit for bits =
extreme low operating height



Slightly angled handle makes work
more comfortable and protects
the fingers

XS

Pocket size tool sets
built for tough work in tight spaces




Ratchet forged in one piece
from chrom-vanadium steel

Each component available
individually

Practice oriented assortments
stored in robust, splashproof
mini StrongBox

Long lasting premium quality
in every detail:
Lifetime guarantee on every
component





New!
057



	Item No		EAN-Code
XS 11 Inch	11-pcs	057 711 56	410 40 07157 62057 6
Mini Ratchet 1/4"			
(7 x)	Sockets	3/16" 7/32" 1/4" 9/32" 5/16" 3/8" 1/2"	
	Extension (4")	1/4" - 1/4"	
	Adapter E	6,3 - 1/4" (2")	
	Adapter C	6,3 - 1/4" (1")	
	StrongBox	L: 5,31" W: 2,95" H: 1,46"	



New!
057



	Item No		EAN-Code
XS 18 Inch	18-pcs	057 718 56	420 40 07157 62059 0
Mini Ratchet 1/4"			
(7 x)	Sockets	3/16" 7/32" 1/4" 9/32" 5/16" 3/8" 1/2"	
(7 x)	Bits (C6,3 x 25mm)	3/16" 7/32" 1/4"	
		PH1 PH2 PH3	
		SQ2	
	Extension (2")	1/4" - 1/4"	
	Adapter C	6,3 - 1/4" (1")	
	Bitholder	E6,3 x 2 1/4"	
	StrongBox	L: 5,31" W: 2,95" H: 1,46"	



New!

057



	057		EAN-Code	Item No
XS 33 Inch33-pcs	057 733 06	425	40 07157	61545 9
Mini ratchet 1/4" hex				
Adapter 1/4" hex to square drive (30mm)				
Bitholder 58mm				
(30 x)	Bits (C6,3 x 1")			
1/8" 3/16" 1/4"				
Hex 2,0mm 2,5mm 3,0mm 4,0mm 5,0mm 6,0mm 8,0mm				
PH0 PH1 PH2 PH2 PH3				
PZ1 PZ2 PZ2 PZ3				
Torx 6 Torx 7 Torx 8 Torx 9				
Torx TR 10 Torx TR 15 Torx TR 20 Torx TR 25 Torx TR 27 Torx TR 30 Torx TR 40				
StrongBox: L: 5,31" W: 2,95" H: 1,46"				

New!
057



Mini Ratchet 1/4"
with Adapter C 6,3 - 1/4" in Blister



1

057

057 635 01



118



EAN-Code

40 07157 **61569 5**

New!
438



ERGONIC Stubby Handle 1/4"



61



25



1

438

438 025 40



32

EAN-Code

40 07157 **61585 5**

New!
389



Belt-Pouch for XS StrongBox in blister



1

389

389 800 01



100

EAN-Code

40 07157 **61733 0**

2component handle with pleasant soft grip material for highest torque

screwdriver and T-handle in one

Professional quality & great versatility

felo smart



ergonomically refined design

replaces 48 single tools

blades made from high-quality bit-steels, exceeding the DIN/ISO requirements by up to 100%

anti-roll handle design

GS tested for safety



fitting the complete 1/4" range

black tip for precision fit

060



060



EAN-Code Item No

Felo-SMART Box - metric

060 913 06

1088

40 07157 **32094 0**

[12 x]

Blade

PH 1 - 5/32" Slotted | PH 2 - PH 3 | PZ 1 - 3/16" Slotted

PZ 2 - 1/4" Slotted | PZ 3 - 9/32" Slotted | 3 mm - 4 mm Hex

5 mm - 6 mm Hex | Torx 6 - Torx 7 | Torx 8 - Torx 9

Torx 10 - Torx 15 | Torx 20 - Torx 25 | Torx 30 - Torx 40

Handle 4 1/8" x 1 1/2"**StrongBox:** L: 9 1/2" W: 5 7/64" H: 2 9/32"**Felo-SMART Box - Inch**

060 913 16

1088

40 07157 **50630 6**

[12 x]

Blade

PH 1 - 5/32" Slotted | PH 2 - 1/4" Slotted

Hex 7/64" - 1/8" | 9/64" - 5/32" | 3/16" - 1/4"

Hex 3 mm - 4 mm | 5 mm - 6 mm

Torx 6 - Torx 7 | Torx 8 - Torx 9 | Torx 10 - Torx 15 | Torx 20 - Torx 25 | Torx 30 - Torx 40

Handle: 4 1/8" x 1 1/2"**StrongBox:** L: 9 1/2" W: 5 7/64" H: 2 9/32"

060



EAN-Code Item No

Felo-SMART belt pouch

060 909 14

530

40 07157 **50624 5**

[8 x]

Blade

PH 1 - 5/32" Slotted | PH 2 - 1/4" Slotted

PH 3 - 1/8" Slotted

Torx 6 - Torx 7 | Torx 8 - Torx 9 | Torx 20 - Torx 25 | Torx 30 - Torx 40

Torx TR10 - Torx TR15

Handle 4 1/8" x 1 1/2"**Nylon Pouch**

069



Handle 4 1/8" x 1 1/2"

069

069 205 00



108

EAN-Code Item No

40 07157 **60427** 9

069



Nylon Pouch

Item No

389 900 00



50

EAN-Code Item No

40 07157 **50456** 2

068



068



EAN-Code Item No

7/32"	6"	E 6,3 1/4"	1	068 555 04	50	40 07157 53195 7
1/4"	6"	E 6,3 1/4"	1	068 635 04	50	40 07157 53197 1
9/32"	6"	E 6,3 1/4"	1	068 714 04	50	40 07157 53199 5
5/16"	6"	E 6,3 1/4"	1	068 793 04	53	40 07157 53201 5
3/8"	6"	E 6,3 1/4"	1	068 952 04	56	40 07157 53203 9
7/16"	6"	E 6,3 1/4"	1	068 111 04	57	40 07157 53205 3
1/2"	6"	E 6,3 1/4"	1	068 127 04	68	40 07157 53207 7
9/16"	6"	E 6,3 1/4"	1	068 142 04	82	40 07157 53209 1

343



PH



343



EAN-Code Item No

1/4" + PH2	6"	0.24"	12	343 260 04	44	40 07157 57557 9
------------	----	-------	----	------------	----	-------------------------

Offset Screwdriver in pouch

062



						EAN-Code	Item No
PH1 - 5/32"	6 1/4"	1/4"	1	062 104 04	44	40 07157	32116 9
PH1 - 9/32"	6 1/4"	1/4"	1	062 107 04	44	40 07157	50312 1
PH2 - PH3	6 1/4"	1/4"	1	062 023 04	44	40 07157	32118 3
PH2 - 1/4"	6 1/4"	1/4"	1	062 206 04	44	40 07157	50310 7
PZ1 - 3/16"	6 1/4"	1/4"	1	061 105 04	44	40 07157	32110 7
PZ2 - 1/4"	6 1/4"	1/4"	1	061 206 04	44	40 07157	32112 1
PZ3 - 9/32"	6 1/4"	1/4"	1	061 307 04	44	40 07157	32114 5
Hex 3 mm - 4 mm	6 1/4"	1/4"	1	064 034 04	44	40 07157	32106 0
Hex 5 mm - 6 mm	6 1/4"	1/4"	1	064 056 04	44	40 07157	32130 5
Torx 6 - Torx 7	6 1/4"	1/4"	1	066 067 04	44	40 07157	32096 4
Torx 8 - Torx 9	6 1/4"	1/4"	1	066 089 04	44	40 07157	32098 8
Torx 10 - Torx 15	6 1/4"	1/4"	1	066 115 04	44	40 07157	32100 8
Torx 20 - Torx 25	6 1/4"	1/4"	1	066 225 04	44	40 07157	32102 2
Torx 30 - Torx 40	6 1/4"	1/4"	1	066 340 04	44	40 07157	32104 6
SQ 0 - SQ 1	6 1/4"	1/4"	1	065 001 04	44	40 07157	50346 6
SQ 2 - SQ 3	6 1/4"	1/4"	1	065 023 04	44	40 07157	50348 0
XZN M6 - XZN M5	6 1/4"	1/4"	1	068 065 04	44	40 07157	50344 2
TX10TR - TX15TR	6 1/4"	1/4"	1	067 115 04	44	40 07157	32120 6
TX20TR - TX25TR	6 1/4"	1/4"	1	067 225 04	44	40 07157	32122 0
TX30TR - TX40TR	6 1/4"	1/4"	1	067 340 04	44	40 07157	32124 4
PH2 - 1/4"	6 1/4"	1/4"	1	062 263 04	44	40 07157	50628 3
PH3 - 1/8"	6 1/4"	1/4"	1	062 331 04	44	40 07157	50626 9
7/64" - 1/8" Hex	6 1/4"	1/4"	1	062 278 04	44	40 07157	50634 4
9/64" - 5/32" Hex	6 1/4"	1/4"	1	062 357 04	44	40 07157	50636 8
3/16" - 1/4" Hex	6 1/4"	1/4"	1	064 476 04	44	40 07157	50638 2
Torx 27 - Torx 27	6 1/4"	1/4"	1	066 270 00	44	40 07157	53595 5

097



						EAN-Code	Item No
Adapter	6"	E 6,3 1/4"	1	097 150 14	58	40 07157	32128 2

12 interchangeable IEC screwdriver blades with 2-component handle in sturdy smart box

every screwdriver individually tested to 10.000 Volts, fully conforming to DIN EN 60900

The first compact smart tool for electricians.
Esmart (pat.)

AC 1000V
IEC 60900 : 2004




secure fit of blades, quick-release button on handle against unwanted extraction



precision cap and soft-grip zone on blades for low torque application



063



AC 1000V
IEC 60900 : 2004



063



EAN-Code Item No

Felo E-SMART Box

063 913 06

830

40 07157 **51719** 7

[12 x]

Blade

Slotted 3/32" | 1/8" | 9/64" | 5/32" | 7/32" | 1/4"

PH 1 | PH 2 | PZ 2 | Torx 10 | Torx 15 | Torx 20

Handle: 3.74" x 1.26"**Precision Cap****StrongBox:** L: 9 1/2" W: 5 7/64" H: 2 9/32"**dto. in blister**

063 913 01

965

40 07157 **53077** 6**Felo E-SMART Box SQ2**

063 913 26

830

40 07157 **53439** 2

[12 x]

Blade

Slotted 3/32" | 1/8" | 9/64" | 5/32" | 7/32" | 1/4"

PH 1 | PH 2 | SQ 2 | Torx 10 | Torx 15 | Torx 20

Handle 3.74" x 1.26"**Precision Cap****StrongBox:** L: 9 1/2" W: 5 7/64" H: 2 9/32"**dto. in blister**

063 913 21

965

40 07157 **53447** 7

063



063



EAN-Code Item No

Handle 3.74" x 1.26"

063 105 00

42

40 07157 **51749** 4

063



AC 1000V
IEC 60900 : 2004



			063		EAN-Code	Item No
3/32"	3"	1	063 025 04	44	40 07157	51721 0
1/8"	4"	1	063 030 04	44	40 07157	51723 4
9/64"	4"	1	063 035 04	44	40 07157	51725 8
5/32"	4"	1	063 040 04	44	40 07157	51727 2
7/32"	4"	1	063 055 04	44	40 07157	51729 6
1/4"	4"	1	063 065 04	44	40 07157	51731 9



PH 1	3 1/8"	1	063 102 04	44	40 07157	51733 3
PH 2	4"	1	063 203 04	44	40 07157	51735 7



PZ 1	3 1/8"	1	063 102 14	44	40 07157	51737 1
PZ 2	4"	1	063 203 14	44	40 07157	51739 5



Torx 8	4"	1	063 083 04	44	40 07157	51741 8
Torx 10	4"	1	063 103 04	44	40 07157	51743 2
Torx 15	4"	1	063 153 04	44	40 07157	51745 6
Torx 20	4"	1	063 203 24	44	40 07157	51747 0



SQ 0	4"	1	063 000 04	44	40 07157	53089 9
SQ 1	4"	1	063 100 04	44	40 07157	53091 2
SQ 2	4"	1	063 200 04	44	40 07157	53093 6
SQ 3	4"	1	063 300 04	44	40 07157	53095 0





telescopic depot for 7 bits




ergonomically refined handle design for highest comfort and heavy duty use

smooth, seamless handle for maximum comfort

easy to reach bits safely stored inside the handle

pleasant soft-grip outer material for highest torque



Allround versatility and advanced ergonomics

Serie 370 (pat.)



Serie 373

with bitholder for power tool

bitholder with stainless steel sleeve and extremely strong magnet



Serie 374

Magazine handle with ratchet

professional reversible ratchet – max. torque >212 lb/in (>24Nm)





376



376



EAN-Code **Item No**

Magazine Handle Bitholder on card

6

376 041 05

190

40 07157 **52221 4**

[8 x]

Bits C 6,3 x 1"

Slotted 3/16" | 7/32" | 1/4"

PH 0 | PH 1 | PH 2

PZ 1 | PZ 2



374



374



EAN-Code **Item No**

Magazine Handle with Ratchet on card

6

374 004 05

220

40 07157 **52223 8**

[8 x]

Bits C 6,3 x 1"

Slotted 3/16" | 7/32" | 1/4"

PH 0 | PH 1 | PH 2

PZ 1 | PZ 2

Magazine Handle with Ratchet on card

6

374 204 05

220

40 07157 **52225 2**

[8 x]

Bits C 6,3 x 1"

Slotted 7/32"

PH 1 | PH 2

PZ 1 | PZ 2

Torx 15 | Torx 20 | Torx 25



373



			Item No			EAN-Code	Item No
Magazine handle with bitholder for power-tool, on card	6	373 108 05	19.29	190	40 07157	52227	6
(8 x)	Bits C 6,3 x 1"						
	Slotted 3/16" 7/32" 1/4"						
	PH 0 PH 1 PH 2						
	PZ 1 PZ 2						
Magazine handle with bitholder for power-tool, on card	6	373 208 05		190	40 07157	52229	0
(8 x)	Bits C 6,3 x 1"						
	Slotted 7/32"						
	PH 1 PH 2						
	PZ 1 PZ 2						
	Torx 15 Torx 20 Torx 25						
Magazine handle with bitholder for power-tool, on card	6	373 308 05		190	40 07157	52769	1
(8 x)	Bits C 6,3 x 1"						
	Slotted 7/32" 1/4"						
	PH 1 PH 2						
	SQ 0 SQ 1 SQ 2 SQ 3						

Bits Challenger



**Diamond
coated**



**020
C 6,3**




						020		EAN-Code	Item No
3/16"	1"	C 6,3	1/4"	10		020 400 80	5	40 07157	50647 4
7/32"	1"	C 6,3	1/4"	10		020 520 80	5	40 07157	50649 8
1/4"	1"	C 6,3	1/4"	10		020 610 80	5	40 07157	50651 1
5/16"	1"	C 6,3	1/4"	10		020 800 80	6	40 07157	50653 5

**022
C 6,3**



PH					022		EAN-Code	Item No
1	1"	C 6,3	1/4"	10	022 010 80	5	40 07157	50655 9
2	1"	C 6,3	1/4"	10	022 020 80	5	40 07157	50657 3
3	1"	C 6,3	1/4"	10	022 030 80	6	40 07157	50659 7

**032
E 6,3**



PH					032		EAN-Code	Item No
1	2"	E 6,3	1/4"	10	032 015 80	8	40 07157	50679 5
2	2"	E 6,3	1/4"	10	032 025 80	11	40 07157	50681 8
3	2"	E 6,3	1/4"	10	032 035 80	13	40 07157	50683 2

Bits TiN Plus

TiN (>90 HRC)

SX 75 (>60 HRC)



020 C 6,3 TiN



						020		EAN-Code	Item No
3/16"		1"	C 6,3	1/4"	10	020 500 70	5	40 07157	30907 5
7/32"		1"	C 6,3	1/4"	10	020 520 70	5	40 07157	30911 2
1/4"		1"	C 6,3	1/4"	10	020 610 70	6	40 07157	30916 7
5/16"		1"	C 6,3	1/4"	10	020 800 70	7	40 07157	30921 1

022 C 6,3 TiN



PH					022		EAN-Code	Item No
1	1"	C 6,3	1/4"	10	022 010 70	5	40 07157	10316 1
2	1"	C 6,3	1/4"	10	022 020 70	5	40 07157	10317 8
3	1"	C 6,3	1/4"	10	022 030 70	5	40 07157	10318 5

026 C 6,3 TiN



Torx					026		EAN-Code	Item No
6	1"	C 6,3	1/4"	10	026 060 70	5	40 07157	50212 4
7	1"	C 6,3	1/4"	10	026 070 70	5	40 07157	50214 8
8	1"	C 6,3	1/4"	10	026 080 70	5	40 07157	50216 2
9	1"	C 6,3	1/4"	10	026 090 70	5	40 07157	50218 6
10	1"	C 6,3	1/4"	10	026 100 70	6	40 07157	50220 9
15	1"	C 6,3	1/4"	10	026 150 70	6	40 07157	50222 3
20	1"	C 6,3	1/4"	10	026 200 70	6	40 07157	50224 7
25	1"	C 6,3	1/4"	10	026 250 70	7	40 07157	50226 1
27	1"	C 6,3	1/4"	10	026 270 70	7	40 07157	50228 5
30	1"	C 6,3	1/4"	10	026 300 70	7	40 07157	50230 8
40	1"	C 6,3	1/4"	10	026 400 70	8	40 07157	50232 2
45	1"	C 6,3	1/4"	10	026 450 70	9	40 07157	50234 6

030 E 6,3 TiN



030



EAN-Code **Item No**

3/16"	2"	E 6,3	1/4"	10	030 505 70	9	40 07157 30780 4
7/32"	2"	E 6,3	1/4"	10	030 525 70	10	40 07157 30785 9
1/4"	2"	E 6,3	1/4"	10	030 615 70	12	40 07157 30792 7
5/16"	2"	E 6,3	1/4"	10	030 805 70	14	40 07157 30798 9

032 E 6,3 TiN



032



EAN-Code **Item No**

PH							
1	2"	E 6,3	1/4"	10	032 015 70	8	40 07157 30818 4
2	2"	E 6,3	1/4"	10	032 025 70	11	40 07157 30824 5
3	2"	E 6,3	1/4"	10	032 035 70	13	40 07157 30831 3

036 E 6,3 TiN



036



EAN-Code **Item No**


Torx							
10	2"	E 6,3	1/4"	10	036 105 70	8	4007157 32372 9
15	2"	E 6,3	1/4"	10	036 155 70	9	4007157 32374 3
20	2"	E 6,3	1/4"	10	036 205 70	9	4007157 32376 7
25	2"	E 6,3	1/4"	10	036 255 70	9	4007157 32378 1
30	2"	E 6,3	1/4"	10	036 305 70	11	4007157 32380 4
40	2"	E 6,3	1/4"	10	036 405 70	12	4007157 32382 8



Bits Industrial



020 C 6,3



						020		EAN-Code	Item No
5/32"	1"	C 6,3	1/4"	10		020 210 10	4	40 07157	24037 8
1/8"	1"	C 6,3	1/4"	10		020 300 10	4	40 07157	30066 9
9/64"	1"	C 6,3	1/4"	10		020 310 10	4	40 07157	30070 6
3/16" x 0.06"	1"	C 6,3	1/4"	10		020 400 10	4	40 07157	30904 4
5/32"	1"	C 6,3	1/4"	10		020 410 10	4	40 07157	30079 9
3/16" x 0.08"	1"	C 6,3	1/4"	10		020 500 10	5	40 07157	30089 8
7/32" x 0.031"	1"	C 6,3	1/4"	10		020 510 10	5	40 07157	30097 3
7/32" x 0.039"	1"	C 6,3	1/4"	10		020 520 10	5	40 07157	30105 5
1/4" x 0.039"	1"	C 6,3	1/4"	10		020 600 10	6	40 07157	30112 3
1/4" x 0.047"	1"	C 6,3	1/4"	10		020 610 10	6	40 07157	30119 2
5/16"	1"	C 6,3	1/4"	10		020 800 10	7	40 07157	30918 1

021 C 6,3



PZ



						021		EAN-Code	Item No
2	1"	C 6,3	1/4"	10		021 020 10	5	40 07157	30169 7

022 C 6,3



PH



						022		EAN-Code	Item No
0	1"	C 6,3	1/4"	10		022 000 10	5	40 07157	30937 2
1	1"	C 6,3	1/4"	10		022 010 10	5	40 07157	30193 2
1 (100)	1"	C 6,3	1/4"	1		022 010 17	500	40 07157	30940 2
2	1"	C 6,3	1/4"	10		022 020 10	5	40 07157	30205 2
2 (100)	1"	C 6,3	1/4"	1		022 020 17	500	40 07157	30943 3
3	1"	C 6,3	1/4"	10		022 030 10	6	40 07157	30218 2
3 (100)	1"	C 6,3	1/4"	1		022 030 17	600	40 07157	31351 5
4	1 1/4"	C 6,3	1/4"	10		022 042 10	12	40 07157	30229 8

025 C 6,3



SQ



						025		EAN-Code	Item No
0	1"	C 6,3	1/4"	10		025 000 10	5	40 07157	50350 3
1	1"	C 6,3	1/4"	10		025 100 10	5	40 07157	50352 7
2	1"	C 6,3	1/4"	10		025 200 10	5	40 07157	50354 1
3	1"	C 6,3	1/4"	10		025 300 10	5	40 07157	50356 5

026 C 6,3



Torx					026		EAN-Code	Item No
5	1"	C 6,3	1/4"	10	026 050 10	4	40 07157	50779 2
6	1"	C 6,3	1/4"	10	026 060 10	4	40 07157	30953 2
7	1"	C 6,3	1/4"	10	026 070 10	4	40 07157	30954 9
8	1"	C 6,3	1/4"	10	026 080 10	4	40 07157	30955 6
9	1"	C 6,3	1/4"	10	026 090 10	4	40 07157	30956 3
10	1"	C 6,3	1/4"	10	026 100 10	4	40 07157	30957 0
15	1"	C 6,3	1/4"	10	026 150 10	4	40 07157	30959 4
20	1"	C 6,3	1/4"	10	026 200 10	5	40 07157	30961 7
25	1"	C 6,3	1/4"	10	026 250 10	5	40 07157	30963 1
27	1"	C 6,3	1/4"	10	026 270 10	6	40 07157	30965 5
30	1"	C 6,3	1/4"	10	026 300 10	6	40 07157	30967 9
40	1"	C 6,3	1/4"	10	026 400 10	6	40 07157	30969 3
45	1"	C 6,3	1/4"	10	026 450 10	8	40 07157	32076 6

027 C 6,3



TorxTR					027		EAN-Code	Item No
7	1"	C 6,3	1/4"	10	027 070 10	4	40 07157	50771 6
8	1"	C 6,3	1/4"	10	027 080 10	4	40 07157	50773 0
9	1"	C 6,3	1/4"	10	027 090 10	4	40 07157	50775 4
10	1"	C 6,3	1/4"	10	027 100 10	4	40 07157	30971 6
15	1"	C 6,3	1/4"	10	027 150 10	4	40 07157	30972 3
20	1"	C 6,3	1/4"	10	027 200 10	5	40 07157	30973 0
25	1"	C 6,3	1/4"	10	027 250 10	5	40 07157	30974 7
27	1"	C 6,3	1/4"	10	027 270 10	6	40 07157	30975 4
30	1"	C 6,3	1/4"	10	027 300 10	6	40 07157	30976 1
40	1"	C 6,3	1/4"	10	027 400 10	6	40 07157	30977 8

023 C 6,3



TorxPlus					023		EAN-Code	Item No
6 IP	1"	C 6,3	1/4"	10	023 060 10	4	40 07157	51341 0
7 IP	1"	C 6,3	1/4"	10	023 070 10	4	40 07157	51343 4
8 IP	1"	C 6,3	1/4"	10	023 080 10	4	40 07157	51345 8
9 IP	1"	C 6,3	1/4"	10	023 090 10	4	40 07157	51347 2
10 IP	1"	C 6,3	1/4"	10	023 100 10	4	40 07157	51349 6
15 IP	1"	C 6,3	1/4"	10	023 150 10	4	40 07157	51351 9
20 IP	1"	C 6,3	1/4"	10	023 200 10	5	40 07157	51353 3
25 IP	1"	C 6,3	1/4"	10	023 250 10	5	40 07157	51355 7
27 IP	1"	C 6,3	1/4"	10	023 270 10	6	40 07157	51357 1
30 IP	1"	C 6,3	1/4"	10	023 300 10	6	40 07157	51359 5
40 IP	1"	C 6,3	1/4"	10	023 400 10	6	40 07157	51361 8

028 C 6,3



XZN					028		EAN-Code	Item No
M 4	1"	C 6,3	1/4"	10	028 040 10	5	40 07157	50360 2
M 5	1"	C 6,3	1/4"	10	028 050 10	5	40 07157	50362 6
M 6	1"	C 6,3	1/4"	10	028 060 10	5	40 07157	50364 0
M 8	1"	C 6,3	1/4"	10	028 080 10	5	40 07157	50366 4
M 10	1"	C 6,3	1/4"	10	028 100 10	5	40 07157	50368 8

029 C 6,3



TS					029		EAN-Code	Item No
0	1"	C 6,3	1/4"	10	029 000 10	5	40 07157	50370 1
1	1"	C 6,3	1/4"	10	029 010 10	5	40 07157	50372 5
2	1"	C 6,3	1/4"	10	029 020 10	5	40 07157	50374 9
3	1"	C 6,3	1/4"	10	029 030 10	5	40 07157	50376 3
4	1"	C 6,3	1/4"	10	029 040 10	5	40 07157	50378 7
5	1"	C 6,3	1/4"	10	029 050 10	5	40 07157	50380 0
6	1"	C 6,3	1/4"	10	029 060 10	5	40 07157	50382 4

030 E 6,3



					030		EAN-Code	Item No
1/8"	2"	E 6,3	1/4"	10	030 305 10	7	40 07157	30772 9
9/64"	2"	E 6,3	1/4"	10	030 315 10	7	40 07157	30275 5
5/32"	2"	E 6,3	1/4"	10	030 415 10	7	40 07157	30277 9
3/16" x 0.023"	2"	E 6,3	1/4"	10	030 455 10	8	40 07157	30779 8
3/16" x 0.031"	2"	E 6,3	1/4"	10	030 505 10	9	40 07157	30280 9
7/32" x 0.031"	2"	E 6,3	1/4"	10	030 515 10	10	40 07157	30283 0
7/32" x 0.039"	2"	E 6,3	1/4"	10	030 525 10	10	40 07157	30285 4
1/4" x 0.039"	2"	E 6,3	1/4"	10	030 605 10	10	40 07157	30287 8
1/4" x 0.05"	2"	E 6,3	1/4"	10	030 615 10	12	40 07157	30290 8
5/16" x 0.05"	2"	E 6,3	1/4"	10	030 805 10	14	40 07157	30292 2
5/16" x 0.06"	2"	E 6,3	1/4"	10	030 815 10	14	40 07157	30294 6
3/8"	2"	E 6,3	1/4"	10	030 105 10	17	40 07157	30272 4

031 E 6,3



					031		EAN-Code Item No
PZ							
2	2"	E 6,3	1/4"	10	031 025 10	11	40 07157 30312 7

032 E 6,3



					032		EAN-Code Item No
PH							
0	2"	E 6,3	1/4"	10	032 005 10	13	40 07157 51015 0
1	2"	E 6,3	1/4"	10	032 015 10	8	40 07157 30317 2
2	2"	E 6,3	1/4"	10	032 025 10	11	40 07157 30320 2
3	2"	E 6,3	1/4"	10	032 035 10	13	40 07157 30323 3

033 E 6,3



					033		EAN-Code Item No
TorxPlus							
10 IP	2"	E 6,3	1/4"	10	033 105 10	10	40 07157 51363 2
15 IP	2"	E 6,3	1/4"	10	033 155 10	10	40 07157 51365 6
20 IP	2"	E 6,3	1/4"	10	033 205 10	11	40 07157 51367 0
25 IP	2"	E 6,3	1/4"	10	033 255 10	11	40 07157 51369 4
30 IP	2"	E 6,3	1/4"	10	033 305 10	11	40 07157 51371 7

036 E 6,3



					036		EAN-Code Item No
Torx							
5	2"	E 6,3	1/4"	10	036 055 10	10	40 07157 50973 4
6	2"	E 6,3	1/4"	10	036 065 10	10	40 07157 51375 5
7	2"	E 6,3	1/4"	10	036 075 10	10	40 07157 51377 9
8	2"	E 6,3	1/4"	10	036 085 10	9	40 07157 30834 4
9	2"	E 6,3	1/4"	10	036 095 10	9	40 07157 30835 1
10	2"	E 6,3	1/4"	10	036 105 10	10	40 07157 30836 8
15	2"	E 6,3	1/4"	10	036 155 10	10	40 07157 24026 2
20	2"	E 6,3	1/4"	10	036 205 10	11	40 07157 30839 9
25	2"	E 6,3	1/4"	10	036 255 10	11	40 07157 30841 2
27	2"	E 6,3	1/4"	10	036 275 10	11	40 07157 30843 6
30	2"	E 6,3	1/4"	10	036 305 10	11	40 07157 30845 0
40	2"	E 6,3	1/4"	10	036 405 10	12	40 07157 30847 4

039 E 6,3



Hex					039		EAN-Code	Item No
5	2 5/8"	E 6,3	1/4"	5	039 050 10	36	40 07157	50404 3
6	2 5/8"	E 6,3	1/4"	5	039 060 10	36	40 07157	50406 7
7	2 5/8"	E 6,3	1/4"	5	039 070 10	37	40 07157	51373 1
8	2 5/8"	E 6,3	1/4"	5	039 080 10	37	40 07157	50408 1
10	2 5/8"	E 6,3	1/4"	5	039 100 10	38	40 07157	50410 4

039 E 6,3



Hex					039		EAN-Code	Item No
5/16"	2 5/8"	E 6,3	1/4"	5	039 516 10	37	40 07157	50414 2
3/8"	2 5/8"	E 6,3	1/4"	5	039 038 10	38	40 07157	50416 6

030 E 6,3



					030		EAN-Code	Item No
1/8"	2 7/8"	E 6,3	1/4"	5	030 307 10	7	40 07157	30274 8
9/64"	2 7/8"	E 6,3	1/4"	5	030 317 10	8	40 07157	30773 6
5/32"	2 7/8"	E 6,3	1/4"	5	030 417 10	9	40 07157	30279 3
7/32"	2 7/8"	E 6,3	1/4"	5	030 527 10	13	40 07157	30787 3
1/4"	2 7/8"	E 6,3	1/4"	5	030 617 10	17	40 07157	30794 1

032 E 6,3



PH					032		EAN-Code	Item No
1	2 7/8"	E 6,3	1/4"	5	032 017 10	11	40 07157	30319 6
2	2 7/8"	E 6,3	1/4"	5	032 027 10	15	40 07157	30322 6
3	2 7/8"	E 6,3	1/4"	5	032 037 10	22	40 07157	30833 7

032 E 6,3



For terminal block screws



H (+/-)					032		EAN-Code	Item No
2	2 7/8"	E 6,3	1/4"	5	032 202 10	16	40 07157	51881 1

035 E 6,3



SQ					035		EAN-Code	Item No
0	2 7/8"	E 6,3	1/4"	5	035 007 10	22	40 07157	31520 5
1	2 7/8"	E 6,3	1/4"	5	035 017 10	22	40 07157	31522 9
2	2 7/8"	E 6,3	1/4"	5	035 027 10	22	40 07157	31524 3
3	2 7/8"	E 6,3	1/4"	5	035 037 10	22	40 07157	31526 7

036 E 6,3



Torx					036		EAN-Code	Item No
10	2 7/8"	E 6,3	1/4"	3	036 107 10	8	40 07157	30837 5
15	2 7/8"	E 6,3	1/4"	3	036 157 10	8	40 07157	30838 2
20	2 7/8"	E 6,3	1/4"	3	036 207 10	11	40 07157	30840 5
25	2 7/8"	E 6,3	1/4"	3	036 257 10	11	40 07157	30842 9
27	2 7/8"	E 6,3	1/4"	3	036 277 10	11	40 07157	30844 3
30	2 7/8"	E 6,3	1/4"	3	036 307 10	15	40 07157	30846 7
40	2 7/8"	E 6,3	1/4"	3	036 407 10	19	40 07157	30848 1

030 E 6,3



					030		EAN-Code	Item No
5/32"	4"	E 6,3	1/4"	3	030 418 10	12	40 07157	30778 1
7/32"	4"	E 6,3	1/4"	3	030 528 10	18	40 07157	30788 0
1/4"	4"	E 6,3	1/4"	3	030 618 10	23	40 07157	30795 8
5/16"	4"	E 6,3	1/4"	3	030 818 10	32	40 07157	30800 9

032 E 6,3



PH					032		EAN-Code	Item No
1	4"	E 6,3	1/4"	3	032 018 10	15	40 07157	30822 1
2	4"	E 6,3	1/4"	3	032 028 10	21	40 07157	30828 3

032 E 6,3



PH					032		EAN-Code	Item No
1	6"	E 6,3	1/4"	3	032 019 10	21	40 07157	30823 8
2	6"	E 6,3	1/4"	3	032 029 10	32	40 07157	30830 6

020



Industrial



020



EAN-Code Item No

2 x	9/64"	1"	C 6,3	10	020 310 36	15	40 07157 10263 8
2 x	5/32"	1"	C 6,3	10	020 410 36	15	40 07157 10264 5
2 x	7/32"	1"	C 6,3	10	020 520 36	17	40 07157 10265 2
2 x	1/4"	1"	C 6,3	10	020 610 36	17	40 07157 10266 9
2 x	5/16"	1"	C 6,3	10	020 800 36	18	40 07157 10267 6
3 x 1	9/64" 5/32" 7/32"	1"	C 6,3	10	020 931 16	21	40 07157 10278 2
3 x 1	15/64" 1/4" 5/16"	1"	C 6,3	10	020 932 16	21	40 07157 10279 9
3 x 1	9/64" 7/32" 1/4"	2"	C 6,3	10	030 931 16	38	40 07157 52239 9
2 x	PH 1	1"	C 6,3	10	022 010 36	15	40 07157 10270 6
2 x	PH 2	1"	C 6,3	10	022 020 36	15	40 07157 10271 3
2 x	PH 3	1"	C 6,3	10	022 030 36	17	40 07157 10272 0
3 x 1	PH 1 PH 2 PH 3	1"	C 6,3	10	022 931 16	22	40 07157 10280 5
2 x	TX 6	1"	C 6,3	10	026 060 36	13	40 07157 10303 1
2 x	TX 7	1"	C 6,3	10	026 070 36	13	40 07157 10302 4
2 x	TX 8	1"	C 6,3	10	026 080 36	13	40 07157 10301 7
2 x	TX 9	1"	C 6,3	10	026 090 36	13	40 07157 10300 0
2 x	TX 10	1"	C 6,3	10	026 100 36	15	40 07157 10299 7
2 x	TX 15	1"	C 6,3	10	026 150 36	15	40 07157 10298 0
2 x	TX 20	1"	C 6,3	10	026 200 36	15	40 07157 10297 3
2 x	TX 25	1"	C 6,3	10	026 250 36	15	40 07157 10296 6
2 x	TX 27	1"	C 6,3	10	026 270 36	17	40 07157 10295 9
2 x	TX 30	1"	C 6,3	10	026 300 36	20	40 07157 10294 2
2 x	TX 40	1"	C 6,3	10	026 400 36	23	40 07157 22194 0
2 x	PH 2	2"	E 6,3	10	032 025 36	25	40 07157 10286 7



Felo Star automatic-holder is a unique power-tool accessory, providing decisive advantages to the industrial user.




- secure hold of screw
- automatic adjustment to depth of screw head
- genuine one-hand operation
- quick and easy replacement of bits
- compact size

Making work safer, faster and more efficient!

felo star



038



2 3/4" E 6,3



1/4"



6

038

038 165 94



40



EAN-Code

40 07157 **52673 1**

020



Diamond



020



EAN-Code Item No

AllStar Bit Box Slotted, PH, Torx C 6,3 x 1"

8 020 902 86

165

40 07157 53525 2

Felo Star + 10 Challenger Bits

(2 x) 020: 7/32" | 1/4" Slotted

(3 x) 022: PH 2

022: PH 3

(4 x) 026: Torx 20 | Torx 25 | Torx 30 | Torx 40

038: Felo Star

026



026



EAN-Code Item No

AllStar Bit Box Torx, C 6,3 x 1"

8 026 901 16

148

40 07157 50797 6

Felo Star + 10 Bits

(4 x) 026: Torx 20

(2 x) 026: Torx 25

026: Torx 27

(2 x) 026: Torx 30

026: Torx 40

038: Felo Star

026



020



EAN-Code Item No

AllStar Bit Box Torx, C 6,3 x 25 mm

8 020 908 76

165

40 07157 53527 6

Felo Star + 10 TiN Bits

(2 x) 020: 7/32" | 1/4" Slotted

(3 x) 022: PH 2

022: PH 3

(4 x) 026: Torx 20 | Torx 25 | Torx 30 | Torx 40

038: Felo Star



020



020



EAN-Code Item No

AllStar Bit Box Universal SQ Torx C 6,3 x 1"

8 020 908 16

165

40 07157 53015 8

Felo Star + 10 Bits

(2 x) 020: 7/32" | 1/4" Slotted

(3 x) 022: PH 2

022: PH 3

(2 x) 025: SQ 2 | SQ 3

(2 x) 026: Torx 20 | Torx 25

038: Felo Star



020



020



EAN-Code Item No

AllStar Bit Box Slotted, PH, SQ C 6,3 x 1"

8 020 909 16

165

40 07157 53529 0

Felo Star + 10 Bits


(2 x) 020: 7/32" | 1/4" Slotted

(3 x) 022: PH 2

022: PH 3

(2 x 2) 025: SQ 2 | SQ 3

038: Felo Star



020



020



EAN-Code Item No

AllStar Bit Box SQ Torx C 6,3 x 1"

8 020 905 16

165

40 07157 52755 4

Felo Star + 10 Bits


(2 x) 020: 7/32" | 1/4" Slotted

(2 x) 022: PH 2 | PH 3

(2 x) 025: SQ 2 | SQ 3

(4 x) 026: Torx 20 | Torx 25 | Torx 30 | Torx 40

038: Felo Star



felo swift

- All sizes at one glance
- easy selection of bits by pick and pull (one-hand operation)
- auxiliary-screwdriver function



020



Swift Box Torx TiN C 6,3 x 1"



020



EAN-Code

10 020 604 76

73

40 07157 **51389** 2

6 Bits + Magnetholder

(6 x) **026:** TiN Torx 10 | Torx 15 | Torx 20 | Torx 25 | Torx 30 | Torx 40

dto. on card

10 020 604 71

84

40 07157 **52731** 8



Swift Box Torx-PH TiN C 6,3 x 1"

10 020 607 76

75

40 07157 **51925** 2

6 Bits + Magnetholder

(3 x) **026:** TiN Torx 10 | Torx 15 | Torx 20

(3 x) **022:** TiN PH 1 | PH 2 | PH 3

dto. on card

10 020 607 71

90

40 07157 **53545** 0



Swift Box Torx C 6,3 x 1"

10 020 603 16

75

40 07157 **51395** 3

6 Bits + Magnetholder

(6 x) **026:** Torx 10 | Torx 15 | Torx 20 | Torx 25 | Torx 30 | Torx 40

dto. on card

10 020 603 11

90

40 07157 **52721** 9



Swift Box Universal C 6,3 x 1"

10 020 604 16

75

40 07157 **51923** 8

6 Bits + Magnetholder

(2 x) **020:** 7/32" | 1/4" Slotted

(2 x) **026:** Torx 10 | Torx 20

(2 x) **022:** PH 1 | PH 2

dto. on card

10 020 604 11

90

40 07157 **53531** 3



Swift Box Industry C 6,3 x 1"

10 020 605 16

75

40 07157 **53535** 1

6 Bits + Magnetholder

(2 x) **020:** 7/32" | 1/4" Slotted

(2 x) **022:** PH 1 | PH 2

(2 x) **025:** SQ 1 | SQ 2

dto. on card

10 020 605 11

90

40 07157 **53539** 9



New!

Torx TR Box Swift C 6,3 x 1"

10 020 610 16

73

40 07157 **61669** 2

6 Bits + Magnetholder

(6 x) **027:** Torx TR 10 | Torx TR 15 | Torx TR 20 | Torx TR 25 | Torx TR 30 | Torx TR 40

dto. on card

10 020 610 11

85

40 07157 **60917** 5



Bitboxes

020



020



EAN-Code Item No

Profi Bit Box 12 Bits C 6,3 x 1" + Magnetholder

10

020 918 16

120

40 07157 **53541** 2

(4 x) **026:** 3/16" | 7/32" | 1/4" | 5/16" Slotted

022: PH 1

(2 x) **022:** PH 2

022: PH 3

026: Torx 15

(2 x) **026:** Torx 20

026: Torx 25

038: Magnetholder

030



030



EAN-Code Item No

Profi Bit Box. 6 Bits E 6,3 x 2"

10

030 915 16

120

40 07157 **31410** 9

(6 x) **030:** 9/64" | 5/32" | 3/16"

7/32" | 1/4" | 5/16" Slotted

036



036



EAN-Code Item No

Profi Bit Box. 6 Bits E 6,3 x 2"

10 036 915 16

120 40 07157 **31419 2**

[6 x] **030:** Torx 10 | Torx 15 | Torx 20 | Torx 25 | Torx 30 | Torx 40

057



057



EAN-Code Item No

1/4" Nut-Box – metric. 8 Sockets + Adapter

6 057 981 06

170 40 07157 **22198 8**

[8 x] 4 mm | 5 mm | 5.5 mm | 6 mm | 7 mm

8 mm | 10 mm | 13 mm

097: **Adapter** (EAN-Code Item No 40 07157 **30481 0**)

022



022



EAN-Code Item No

PH Box. 25 Bits + Magnetholder C 6,3 x 1"

6 022 026 16

196 40 07157 **53543 6**

[5 x] PH 1

[15 x] PH 2

[5 x] PH 3

Magnetholder 2 3/8"

020



026



EAN-Code Item No

		6	026 026 16	196	40 07157 50803 4
Torx-Box. 25 Bits + Magnetholder C 6,3 x 1"					
(4 x)	Torx 5 Torx 8 Torx 9 Torx 27				
(2 x 2)	Torx 6 Torx 10				
(3 x 3)	Torx 15 Torx 30 Torx 40				
(2 x 4)	Torx 20 Torx 25				
	Magnetholder 2 3/8"				

020



020



EAN-Code Item No

		6	020 326 16	196	40 07157 51565 0
Security Bitbox C 6,3 x 1"					
(2 x) 024:	Hex 4,0 3,0 mm				
(3 x) 028:	XZN M6 XZN M5 XZN M4				
(5 x) 029:	TS 10 TS 8 TS 6 TS 4 TS 0				
(5 x) 027:	TxTR 30 TxTR 25 TxTR 20 TxTR 15 TxTR 10				
(5 x) 029:	Tri-Wing 5 4 3 2 1				
(3 x) 020:	Spanner 6 8 10				
(2 x) 028:	Clutch 5/32 1/4				
038:	Magnetholder 2 3/8"				

Bitholders & Adapters

429



Bitholder	6 3/4"	4.2"	1.4"	6	429		EAN-Code	Item No
					429 635 40	146	40 07157	60365 4

438



Bitholder	4"	3.9"	1.3"	6	438		EAN-Code	Item No
					438 125 40	102	40 07157	53711 9

538



Felo Star	4"	3.9"	1.3"	6	538		EAN-Code	Item No
					538 100 40	123	40 07157	51397 7

538



Bitholder	4"	3.9"	1.3"	6	538		EAN-Code	Item No
					538 125 40	103	40 07157	32348 4

518



Bitholder					
	1/4"	4"	3.9"	1.3"	6



AC 1000V
IEC 60900 : 2004



518

518 125 40



103

EAN-Code **Item No**

40 07157 **50785 3**

338



Bitholder			
	5"	4"	6



338

338 125 80



111

EAN-Code **Item No**

40 07157 **32350 7**



038



FeloStar on card				
	2 3/4"	E 6,3	1/4"	6

038

038 165 94



40

EAN-Code

40 07157 **52673 1**



038



Magnetholder				
---------------------	--	--	--	--

038

038 109 90



20

EAN-Code **Item No**

40 07157 **30850 4**

Magnetholder

extra strong

1 7/8"

E 6,3

1/4"

6

Magnetholder

2 1/4"

E 6,3

1/4"

6

dto. in PP-Box

038 103 90

30

40 07157 **30340 0**

038 103 96

32

40 07157 **10288 1**

058



Magnetholder				
	4"	SDS	1/4"	6

058

058 102 90



62

EAN-Code **Item No**

40 07157 **30978 5**

059



Indenter					059		EAN-Code	Item No
Bit Holder	max. 3 1/8"	E 6,3	1/4"	6	059 103 90	67	40 07157	51897 2
incl. Bit PH 2 x 25								

097



Adapter					097		EAN-Code	Item No
	2"	E 6,3	1/4"	6	097 013 10	15	40 07157	30481 0

097



Adapter					097		EAN-Code	Item No
	1"	1/4"	1/4"	6	097 018 10	11	40 07157	30851 1

097



Adapter					097		EAN-Code	Item No
	2"	E 6,3	3/8"	6	097 020 10	22	40 07157	30489 6

»felo is your specialist with great experience in custom made items and solutions of the highest quality.



finely-serrated jaws
providing firm grip

induction-hardened cutting edge,
60 / 64 HRC

precise joint for optimum leverage



optimum long-lasting
corrosion protection
from special matte
chromium surface

Outstanding cutting
performance and
highest precision

**Professional quality
for heavy duty use**

Pliers

Slip-stop wings for secure grip

ergonomically refined design
for maximum comfort

Red/yellow model indi-
vidually tested up to
1000V, VDE IEC 60900

superior hardness
which exceeds DIN
and ISO requirements
by up to 100%

Quality of Workmanship
and materials guaranteed

drop-forged
from special steel

2-component
handle technology



GS tested for safety



EAN code
on every product

590



590



EAN-Code Item No

6 5/16" Combination Pliers

6

590 016 10

230

40 07157 50020 5

7" Combination Pliers

6

590 018 10

260

40 07157 50022 9

591



591



EAN-Code Item No

5 3/4" Diagonal Nippers

6

591 014 10

285

40 07157 50024 3

6 5/16" Diagonal Nippers

6

591 016 10

300

40 07157 50026 7

7" Diagonal Nippers

6

591 018 10

325

40 07157 50028 1

591



591



EAN-Code Item No

7" Heavy-duty Diagonal Nippers

6

591 118 10

350

40 07157 50030 4

592



592



EAN-Code Item No

6 5/16" Chain Nose Radio Pliers

6

592 016 10

200

40 07157 50034 2

7 7/8" Chain Nose Radio Pliers

6

592 020 10

222

40 07157 50036 6

592



592



EAN-Code Item No

7 7/8" Chain Nose Radio Pliers Angled 45° 6

592 220 10

222

40 07157 50038 0

593



6 5/16" Insulation Stripping Pliers

6

593

593 016 10



230

EAN-Code **Item No**

40 07157 **50040 3**

592



6 5/16" Pincers

6

894

894 016 20



310

EAN-Code **Item No**

40 07157 **50042 7**

7 7/8" Pincers

6

894 020 20

330

40 07157 **50044 1**

895



10" Waterpump Pliers

6

895

895 025 20



350

EAN-Code **Item No**

40 07157 **50064 9**

592



Lineman's Pliers

1

Item No

590 020 10



350

EAN-Code **Item No**

40 07157 **53649 5**

580



AC 1000V
IEC 60900 : 2004

		580		EAN-Code	Item No
6 5/16" Insulated Combination Pliers	6	580 016 10	230	40 07157	50859 1
7" Insulated Combination Pliers	6	580 018 10	260	40 07157	50861 4

581



AC 1000V
IEC 60900 : 2004

		581		EAN-Code	Item No
6 5/16" Insulated Diagonal Nippers	6	581 016 10	300	40 07157	50863 8
7" Insulated Diagonal Nippers	6	581 018 10	325	40 07157	50865 2

582



AC 1000V
IEC 60900 : 2004

		582		EAN-Code	Item No
6 1/4" Insulated Chain Nose Radio Pliers	6	582 017 10	210	40 07157	50869 0

582



AC 1000V
IEC 60900 : 2004

		582		EAN-Code	Item No
8" Insulated Chain Nose Radio Pliers Angled 45°	6	582 225 10	225	40 07157	50871 3

583



AC 1000V
IEC 60900 : 2004

		583		EAN-Code	Item No
6 5/16" Insulated Insulation Stripping Pliers	6	583 016 10	230	40 07157	50867 6

Article Index

Felo PART #	Page	Felo PART #	Page	Felo PART #	Page
07157 10263	83	07157 13028	29	07157 17052	36
07157 10264	83	07157 13032	29	07157 17053	36
07157 10265	83	07157 13035	29	07157 17054	36
07157 10266	83	07157 13037	29	07157 17055	36
07157 10267	83	07157 13041	29	07157 17056	36
07157 10270	83	07157 13045	29	07157 17057	36
07157 10271	83	07157 13099	29	07157 22091	19
07157 10272	83	07157 13103	29	07157 22092	19
07157 10278	83	07157 13106	29	07157 22093	19
07157 10279	83	07157 13111	29	07157 22094	19
07157 10280	83	07157 13117	29	07157 22095	19
07157 10286	83	07157 13166	27	07157 22096	19
07157 10288	92	07157 16050	29	07157 22097	19
07157 10294	83	07157 16052	30	07157 22098	19
07157 10295	83	07157 16054	30	07157 22099	20
07157 10296	83	07157 17000	35	07157 22101	19
07157 10297	83	07157 17002	35	07157 22102	19
07157 10298	83	07157 17004	35	07157 22106	19
07157 10299	83	07157 17011	35	07157 22107	19
07157 10300	83	07157 17013	35	07157 22108	19
07157 10301	83	07157 17015	35	07157 22109	20
07157 10302	83	07157 17017	35	07157 22110	20
07157 10303	83	07157 17026	36	07157 22111	19
07157 10316	75	07157 17028	36	07157 22112	19
07157 10317	75	07157 17046	36	07157 22113	41
07157 10318	75	07157 17047	36	07157 22114	41
07157 13001	29	07157 17048	36	07157 22115	41
07157 13003	29	07157 17049	36	07157 22116	41
07157 13010	29	07157 17050	36	07157 22117	41
07157 13016	29	07157 17051	36	07157 22118	41

Felo PART #	Page	Felo PART #	Page	Felo PART #	Page
07157 22119	41	07157 30070	77	07157 30778	82
07157 22120	41	07157 30079	77	07157 30779	79
07157 22141	41	07157 30089	77	07157 30780	76
07157 22142	41	07157 30097	77	07157 30785	76
07157 22143	41	07157 30105	77	07157 30787	81
07157 22154	20	07157 30112	77	07157 30788	82
07157 22155	32	07157 30119	77	07157 30792	76
07157 22156	20	07157 30169	77	07157 30794	81
07157 22157	20	07157 30193	77	07157 30795	82
07157 22158	20	07157 30205	77	07157 30798	76
07157 22159	20	07157 30218	77	07157 30800	82
07157 22160	20	07157 30229	77	07157 30818	76
07157 22161	20	07157 30272	79	07157 30822	82
07157 22162	20	07157 30274	81	07157 30823	82
07157 22163	20	07157 30275	79	07157 30824	76
07157 22164	20	07157 30277	79	07157 30828	82
07157 22165	20	07157 30279	81	07157 30830	82
07157 22166	20	07157 30280	79	07157 30831	76
07157 22188	20	07157 30283	79	07157 30833	81
07157 22194	83	07157 30285	79	07157 30834	80
07157 22198	89	07157 30287	79	07157 30835	80
07157 23006	33	07157 30290	79	07157 30836	80
07157 23013	33	07157 30292	79	07157 30837	82
07157 24022	33	07157 30294	79	07157 30838	82
07157 24026	80	07157 30312	80	07157 30839	80
07157 24036	27	07157 30317	80	07157 30840	82
07157 24037	77	07157 30319	81	07157 30841	80
07157 28003	37	07157 30320	80	07157 30842	82
07157 28005	37	07157 30322	81	07157 30843	80
07157 28009	37	07157 30323	80	07157 30844	82
07157 28010	35	07157 30340	92	07157 30845	80
07157 28011	36	07157 30481	93	07157 30846	82
07157 28012	35	07157 30489	93	07157 30847	80
07157 28013	35	07157 30768	35	07157 30848	82
07157 28017	35	07157 30772	79	07157 30850	92
07157 30066	77	07157 30773	81	07157 30851	93

Felo PART #	Page	Felo PART #	Page	Felo PART #	Page
07157 30876	27	07157 31522	82	07157 31800	50
07157 30904	77	07157 31524	82	07157 31802	50
07157 30907	75	07157 31526	82	07157 31806	53
07157 30911	75	07157 31690	27	07157 31808	53
07157 30916	75	07157 31692	27	07157 31810	53
07157 30918	77	07157 31698	27	07157 31812	53
07157 30921	75	07157 31700	27	07157 31814	53
07157 30937	77	07157 31720	27	07157 31816	53
07157 30940	77	07157 31738	49	07157 31818	53
07157 30943	77	07157 31740	49	07157 31820	53
07157 30953	78	07157 31742	49	07157 31844	51
07157 30954	78	07157 31744	49	07157 31846	51
07157 30955	78	07157 31746	49	07157 31848	53
07157 30956	78	07157 31748	49	07157 32076	78
07157 30957	78	07157 31750	49	07157 32094	65
07157 30959	78	07157 31752	49	07157 32096	67
07157 30961	78	07157 31754	49	07157 32098	67
07157 30963	78	07157 31756	49	07157 32100	67
07157 30965	78	07157 31758	49	07157 32102	67
07157 30967	78	07157 31760	49	07157 32104	67
07157 30969	78	07157 31762	49	07157 32106	67
07157 30971	78	07157 31764	49	07157 32110	67
07157 30972	78	07157 31770	49	07157 32112	67
07157 30973	78	07157 31772	49	07157 32114	67
07157 30974	78	07157 31774	49	07157 32116	67
07157 30975	78	07157 31776	49	07157 32118	67
07157 30976	78	07157 31778	49	07157 32120	67
07157 30977	78	07157 31782	50	07157 32122	67
07157 30978	92	07157 31784	50	07157 32124	67
07157 31078	33	07157 31786	50	07157 32128	67
07157 31330	19	07157 31788	50	07157 32130	67
07157 31331	19	07157 31790	50	07157 32234	20
07157 31351	77	07157 31792	50	07157 32236	20
07157 31410	88	07157 31794	50	07157 32238	20
07157 31419	89	07157 31796	50	07157 32240	20
07157 31520	82	07157 31798	50	07157 32242	20

Felo PART #	Page
07157 32244	20
07157 32246	20
07157 32316	55
07157 32318	55
07157 32320	55
07157 32322	55
07157 32324	55
07157 32326	55
07157 32328	55
07157 32330	55
07157 32348	22
07157 32348	91
07157 32350	55
07157 32350	92
07157 32354	17
07157 32356	17
07157 32358	17
07157 32360	17
07157 32362	17
07157 32368	17
07157 32370	17
07157 32372	76
07157 32374	76
07157 32376	76
07157 32378	76
07157 32380	76
07157 32382	76
07157 32558	25
07157 50020	95
07157 50022	95
07157 50024	95
07157 50026	95
07157 50028	95
07157 50030	95
07157 50034	95
07157 50036	95

Felo PART #	Page
07157 50038	95
07157 50040	96
07157 50042	96
07157 50044	96
07157 50064	96
07157 50072	22
07157 50074	22
07157 50076	22
07157 50078	22
07157 50120	42
07157 50124	41
07157 50174	23
07157 50176	42
07157 50200	25
07157 50212	75
07157 50214	75
07157 50216	75
07157 50218	75
07157 50220	75
07157 50222	75
07157 50224	75
07157 50226	75
07157 50228	75
07157 50230	75
07157 50232	75
07157 50234	75
07157 50274	35
07157 50276	50
07157 50278	50
07157 50280	50
07157 50282	31
07157 50284	31
07157 50286	31
07157 50288	31
07157 50290	31
07157 50292	31

Felo PART #	Page
07157 50294	31
07157 50310	67
07157 50312	67
07157 50344	67
07157 50346	67
07157 50348	67
07157 50350	77
07157 50352	77
07157 50354	77
07157 50356	77
07157 50360	79
07157 50362	79
07157 50364	79
07157 50366	79
07157 50368	79
07157 50370	79
07157 50372	79
07157 50374	79
07157 50376	79
07157 50378	79
07157 50380	79
07157 50382	79
07157 50404	81
07157 50406	81
07157 50408	81
07157 50410	81
07157 50414	81
07157 50416	81
07157 50456	66
07157 50572	19
07157 50624	65
07157 50626	67
07157 50628	67
07157 50630	65
07157 50634	67
07157 50636	67

Felo PART #	Page	Felo PART #	Page	Felo PART #	Page
07157 50638	67	07157 50749	52	07157 51361	78
07157 50647	74	07157 50751	52	07157 51363	80
07157 50649	74	07157 50771	78	07157 51365	80
07157 50651	74	07157 50773	78	07157 51367	80
07157 50653	74	07157 50775	78	07157 51369	80
07157 50655	74	07157 50779	78	07157 51371	80
07157 50657	74	07157 50783	55	07157 51373	81
07157 50679	74	07157 50785	41	07157 51375	80
07157 50681	74	07157 50785	92	07157 51377	80
07157 50683	74	07157 50797	85	07157 51379	19
07157 50693	19	07157 50803	90	07157 51381	19
07157 50695	19	07157 50813	55	07157 51389	87
07157 50697	19	07157 50815	55	07157 51395	87
07157 50699	17	07157 50849	55	07157 51397	22
07157 50701	17	07157 50859	97	07157 51397	91
07157 50703	17	07157 50861	97	07157 51401	43
07157 50707	17	07157 50863	97	07157 51427	43
07157 50709	50	07157 50865	97	07157 51565	90
07157 50711	50	07157 50867	97	07157 51659	74
07157 50713	50	07157 50869	97	07157 51665	21
07157 50715	50	07157 50871	97	07157 51667	21
07157 50717	50	07157 50973	80	07157 51669	21
07157 50719	50	07157 50979	25	07157 51671	21
07157 50723	52	07157 50981	25	07157 51673	21
07157 50725	52	07157 51015	80	07157 51675	21
07157 50727	52	07157 51259	53	07157 51677	21
07157 50729	52	07157 51341	78	07157 51679	21
07157 50731	52	07157 51343	78	07157 51681	21
07157 50733	52	07157 51345	78	07157 51683	21
07157 50735	52	07157 51347	78	07157 51685	21
07157 50737	52	07157 51349	78	07157 51699	24
07157 50739	52	07157 51351	78	07157 51719	69
07157 50741	52	07157 51353	78	07157 51721	70
07157 50743	52	07157 51355	78	07157 51723	70
07157 50745	52	07157 51357	78	07157 51725	70
07157 50747	52	07157 51359	78	07157 51727	70

Felo PART #	Page
07157 51729	70
07157 51731	70
07157 51733	70
07157 51735	70
07157 51737	70
07157 51739	70
07157 51741	70
07157 51743	70
07157 51745	70
07157 51747	70
07157 51749	69
07157 51757	21
07157 51759	21
07157 51761	21
07157 51809	19
07157 51811	19
07157 51841	19
07157 51843	19
07157 51845	19
07157 51881	81
07157 51897	93
07157 51903	31
07157 51923	87
07157 51925	87
07157 51981	21
07157 51983	21
07157 51985	21
07157 51991	47
07157 52001	47
07157 52003	47
07157 52005	47
07157 52007	47
07157 52009	47
07157 52013	47
07157 52015	47
07157 52017	47

Felo PART #	Page
07157 52019	47
07157 52021	47
07157 52023	47
07157 52025	47
07157 52027	47
07157 52029	47
07157 52031	47
07157 52033	47
07157 52035	47
07157 52037	47
07157 52039	45
07157 52041	45
07157 52043	46
07157 52100	47
07157 52149	46
07157 52151	46
07157 52153	46
07157 52155	46
07157 52221	72
07157 52223	72
07157 52225	72
07157 52227	73
07157 52229	73
07157 52239	83
07157 52673	84
07157 52673	92
07157 52721	87
07157 52731	87
07157 52755	86
07157 52769	73
07157 52785	8
07157 52787	8
07157 52789	8
07157 52791	8
07157 52793	8
07157 52795	8

Felo PART #	Page
07157 52797	8
07157 52799	10
07157 52801	10
07157 52803	10
07157 52805	10
07157 52807	11
07157 52809	11
07157 52811	11
07157 52813	11
07157 52815	11
07157 52817	11
07157 52819	11
07157 52821	11
07157 52823	11
07157 52825	11
07157 53015	86
07157 53077	69
07157 53089	70
07157 53091	70
07157 53093	70
07157 53095	70
07157 53117	10
07157 53119	10
07157 53121	8
07157 53125	8
07157 53127	8
07157 53129	8
07157 53131	8
07157 53133	39
07157 53135	39
07157 53139	39
07157 53141	39
07157 53143	39
07157 53145	39
07157 53147	39
07157 53149	39

Felo PART #	Page	Felo PART #	Page	Felo PART #	Page
07157 53151	39	07157 53545	87	07157 61479	12
07157 53153	39	07157 53595	67	07157 61481	59
07157 53155	39	07157 53611	10	07157 61509	13
07157 53157	39	07157 53619	10	07157 61511	13
07157 53165	15	07157 53621	10	07157 61545	62
07157 53167	9	07157 53623	10	07157 61553	58
07157 53169	40	07157 53627	10	07157 61557	59
07157 53171	15	07157 53629	10	07157 61569	63
07157 53173	9	07157 53637	10	07157 61585	63
07157 53175	40	07157 53639	10	07157 61625	47
07157 53195	66	07157 53649	96	07157 61627	47
07157 53197	66	07157 53679	10	07157 61629	47
07157 53199	66	07157 53681	10	07157 61631	47
07157 53201	66	07157 53683	10	07157 61633	47
07157 53203	66	07157 53685	10	07157 61651	47
07157 53205	66	07157 53687	10	07157 61653	47
07157 53207	66	07157 53689	10	07157 61655	47
07157 53209	66	07157 53693	14	07157 61657	47
07157 53235	43	07157 53701	14	07157 61659	47
07157 53413	46	07157 53711	12	07157 61661	47
07157 53439	69	07157 53711	91	07157 61663	47
07157 53447	69	07157 57521	9	07157 61665	47
07157 53507	11	07157 57557	66	07157 61667	47
07157 53509	11	07157 57591	10	07157 61669	87
07157 53511	11	07157 57593	10	07157 61727	13
07157 53517	15	07157 60365	12	07157 61731	39
07157 53521	23	07157 60365	91	07157 61733	63
07157 53523	17	07157 60427	66	07157 62053	57
07157 53525	85	07157 60903	11	07157 62055	58
07157 53527	85	07157 60905	11	07157 62057	61
07157 53529	86	07157 60907	11	07157 62059	61
07157 53531	87	07157 60909	11	07157 91993	47
07157 53535	87	07157 60917	87	07157 91995	47
07157 53539	87	07157 61245	47	07157 91997	47
07157 53541	88	07157 61307	49	07157 91999	47
07157 53543	89	07157 61391	13		





Timesaving GorillaProof Tools

Tough, Long Lasting Tools

Innovative, Time-Saving Product Design

In-Stock, On Time Order Fulfillment

Outstanding Customer Service

1-800-328-8310

1400 E. Broadway

P.O. Box 660

Monticello, MN 55362

Phone: 763-295-2162

Fax: 763-295-4440

E-mail: cservice@bondhus.com

Website: www.bondhus.com

Item No. 07157 90002

