



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	L2	REDRAWN AND REV. BY ECO-16-005813	30JUN2016	HC	WLS



① - REELED WITH PAPER INTERLEAVE.

② - Ø 5,3 FOR M5 HOLE.

OBSOLETE	TIN-PLATED	BRASS	626029-6	①
OBSOLETE	TIN-PLATED	PH. BRONZE	626029-5	
OBSOLETE	NICKEL PLATED	BRASS	626029-4	
OBSOLETE		PH. BRONZE	626029-3	
	TIN-PLATED	BRASS	626029-2	
	—	BRASS	626029-1	①
	FINISH	MATERIAL	PART NUMBER	

WIRE RANGE 0,5-1,5mm²


INSUL. RANGE Ø 1,8-3,0mm.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0,4
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-



DWN 30JUN2016

H.C. CANTERI

CHK 30JUN2016

W.L. STEFANI

APVD -

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

CUSTOMER DRAWING

MATERIAL

SEE TABLE

FINISH

SEE TABLE



TE Connectivity

NAME RING TONGUE

SIZE

A4

CAGE CODE

-

DRAWING NO

©-626029

RESTRICTED TO

-

SCALE

4:1

SHEET

1 OF 1

REV

L2