

Fuse modular terminal block - USIG - 0920083

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse modular terminal block, without fuse plug, Connection method: Screw connection, Cross section: 0.5 mm²- 16 mm², AWG: 20 - 6, Nominal current: 10 A, Nominal voltage: 500 V, Width: 10.2 mm, Fuse type: G / 5 x 20 / 5 x 25 / 5 x 30 / 6.3 x 32, Fuse type: Glass, Mounting type: NS 35/7,5, NS 35/15, NS 32, Color: black

The illustration shows a combination of versions USIG and ST1-SILED 24



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 010133
Weight per Piece (excluding packing)	28.02 GRM
Custom tariff number	85363010
Country of origin	Germany

Technical data

General

Number of levels	1
Number of connections	2
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0
Fuse	G / 5 x 20 / 5 x 25 / 5 x 30 / 6.3 x 32
Fuse type	Glass
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-3

Fuse modular terminal block - USIG - 0920083

Technical data

General

Current	40 A
Additional text	is determined by the fuse used
Nominal current I_N	10 A
Nominal voltage U_N	500 V (As a fuse terminal block)
	500 V (As a disconnect terminal block)
Open side panel	nein

Dimensions

Width	10.2 mm
Length	61 mm
Height NS 35/7,5	51.6 mm
Height NS 35/15	59.1 mm
Height NS 32	56.6 mm

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	16 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	16 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm ²
Cross section with insertion bridge, solid max.	16 mm ²
Cross section with insertion bridge, stranded max.	16 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	4 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
Cross section with insertion bridge, solid max.	16 mm ²

Fuse modular terminal block - USIG - 0920083

Technical data

Connection data

Cross section with insertion bridge, stranded max.	16 mm ²
Connection method	Screw connection
Stripping length	13 mm
Internal cylindrical gage	A5
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

Classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

CSA / UL Recognized / BV / PRS / EAC

Fuse modular terminal block - USIG - 0920083

Approvals

Ex Approvals

Approvals submitted

BV

Approval details

CSA 	
mm ² /AWG/kcmil	24-8
Nominal current IN	40 A
Nominal voltage UN	600 V

UL Recognized 		C
mm ² /AWG/kcmil	18-8	
Nominal current IN	40 A	
Nominal voltage UN	600 V	

BV


PRS

EAC

Drawings

Fuse modular terminal block - USIG - 0920083


Circuit
diagram



Circuit diagram

UK - SI

USIG



1 = partition plate
2 = insertion bridge