





1. FINISH: PLATED 0.001 MIN THICK TIN.
2. PART LUBRICATED WITH ANTI-FRETTING LUBRICANT, MSDS 125-6344
3. FEATURE ON CARRIER STRIP IS DEPRESSED ON TIN PLATED PRODUCT. FEATURE APPEARS ADJACENT TO EVERY OTHER CONTACT MIN.
4. SEE FIGURE 1 FOR REELING DIRECTION.
5. SEE FIGURE 2 FOR REELING DIRECTION.
6. FOR LEVER ASSISTED CONNECTORS WITH SIDE SLIDE ACTION THE ALLOWABLE WIRE BRUSH LENGTH RANGE IS 0.10-0.70MM.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. R. SHUEY 02SEP99	STE TE Connectivity			
DIMENSIONS: mm		CHK J. M. MYER 02SEP99				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. DENLINGER 02SEP99	NAME			
0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±3° FINISH		PRODUCT SPEC 108-2220 APPLICATION SPEC 114-13006 WEIGHT -	CONTACT, FEMALE, 0.64mm TIN PLATED			
MATERIAL 0.25 THK COPPER ALLOY		CUSTOMER DRAWING	SIZE A260779	CAGE CODE C-638551	DRAWING NO.	RESTRICTED TO
			SCALE 10:1	SHEET 1	OF 1	REV B2