

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING
V3L-2436

CQ-XI552

5

V3L-2436

M

DRAWING
NUMBER

28

28

ISSUE

4

REPLACES

RELEASE NO. PR-7605

CHECK

REVISIONS

A	PR-7605
C E B	
20 JAN 79	
CO	
59921	
BMA	
29 SEPT 89	
C	CO
76448	
DCS	
28 JAN 94	

CHECK

20 JAN 79

C E B


CHECK

20 JAN 79

C J H

17 JAN 79

DRAWN




NOTE-



FORCE CHARACTERISTICS CHECKED WITH SWITCH LYING ON SIDE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE --- 7 GRAMS MAX

RELEASE TRAVEL --- .030 MIN


DIFFERENTIAL TRAVEL --- .055 MAX

OVERTRAVEL --- .160 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L162 5A-125, 250, 277VAC
1/10HP-250VAC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/04	
ONE PLACE	X, X	0.4/016	X X
TWO PLACES	X, XX	0.15/006	X XX
THREE PLACES	X, XXX	0.38/015	X XXX
ANGLES		0.13/005	

SI METRIC

DESIGN UNITS

US CUSTOMARY

WEIGHT

FO-52848-A