

GENERAL INFORMATION

AVX SR Series


Conformally Coated Radial Ledged MLC

Temperature Coefficients: COG (NP0), X7R, Z5U

200, 100, 50 Volts (300V, 400V & 500V also available)

Case Material: Epoxy

Lead Material: RoHS Compliant, 100% Tin



HOW TO ORDER


SR21	5	E	104	M	A	R	TR1
AVX Style SR15 SR20 SR21 SR22 SR27 SR30 SR40 SR50	Voltage 5 = 50V 1 = 100V 2 = 200V 9 = 300V 8 = 400V 7 = 500V	Temperature Coefficient A = COG (NP0) C = X7R E = Z5U	Capacitance First two digits are the significant figures of capacitance. Third digit indicates the additional number of zeros. For example, order 100,000 pF as 104. (For values below 10pF use "R" in place of decimal point, e.g., 1R4 = 1.4pF)	Capacitance Tolerance COG (NP0): C = $\pm 0.25\text{pF}$ D = $\pm 0.5\text{pF}$ F = $\pm 1\%$ ($>50\text{pF}$ only) G = $\pm 2\%$ ($>25\text{pF}$ only) J = $\pm 5\%$ K = $\pm 10\%$	Failure Rate A = Not Applicable	Leads R = RoHS Long Lead 1.0" minimum	Packaging Blank = Bulk Packaging T = Trimmed Leads .230" $\pm$.030" Bulk packaging TR1 = Tape and Reel Packaging AP1 = Ammopack Packaging See packaging specification page 33-34.

Drawings are for illustrative purposes only.
Actual lead form shape could vary within stated tolerances based on body size.




MARKING

FRONT



BACK



PACKAGING REQUIREMENTS

	Quantity per Bag
SR15, 20, 21, 22, 27, 30	1000 Pieces
SR40, 50	500 Pieces

Note: SR15, SR20, SR21, SR30, and SR40 available on tape and reel per EIA specifications RS-468. See Pages 33 and 34.

Radial Leads/SkyCap®/SR Series



C0G (NP0) Dielectric

SIZE AND CAPACITANCE SPECIFICATIONS

EIA Characteristic

Dimensions: Millimeters (Inches)

AVX Style		SR15			SR20			SR21			SR22			SR27			SR30			SR40			SR50		
AVX “Insertable”		SR07			SR29			SR59			N/A			N/A			SR65			SR75			N/A		
Width (W)		3.81 (.150)			5.08 (.200)			5.08 (.200)			5.08 (.200)			6.604 (.260)			7.62 (.300)			10.16 (.400)			12.70 (.500)		
Height (H)		3.81 (.150)			5.08 (.200)			5.08 (.200)			5.08 (.200)			6.35 (.250)			7.62 (.300)			10.16 (.400)			12.70 (.500)		
Thickness (T)		2.54 (.100)			3.175 (.125)			3.175 (.125)			3.175 (.125)			4.06 (.160)			3.81 (.150)			3.81 (.150)			5.08 (.200)		
Lead Spacing (L.S.)		2.54 (.100)			2.54 (.100)			5.08 (.200)			6.35 (.250)			7.62 (.300)			5.08 (.200)			5.08 (.200)			10.16 (.400)		
Lead Diameter (L.D.)		.508 (.020)			.508 (.020)			.508 (.020)			.508 (.020)			.508 (.020)			.508 (.020)			.508 (.020)			.635 (.025)		
Cap. in.* Industry Preferred pF Values in Blue		WVDC 200 100 50			WVDC 200 100 50			WVDC 200 100 50			WVDC 200 100 50			WVDC 200 100 50			WVDC 100 50			WVDC 100 50			WVDC 100 50		
1.0-9.9 10 15	SR151A1R0DAR																								
	SR151A100KAR																								
	SR.....A150KAR																								
22 33 39	SR.....A220KAR																								
	SR.....A330KAR																								
	SR.....A390KAR																								
47 68 100	SR.....A470KAR																								
	SR.....A680KAR																								
	SR151A101KAR																								
150 220 330	SR.....A151KAR																								
	SR.....A221KAR																								
	SR.....A331KAR																								
390 470 680	SR.....A391KAR																								
	SR.....A471KAR																								
	SR.....A681KAR																								
1000 1500 2200	SR211A102KAR																								
	SR.....A152KAR																								
	SR.....A222KAR																								
3900 4700 6800	SR.....A392KAR																								
	SR.....A472KAR																								
	SR.....A682KAR																								
8200 10,000 15,000	SR.....A822KAR																								
	SR305A103KAR																								
	SR-----A153KAR																								
22,000 33,000 39,000	SR.....A223KAR																								
	SR.....A333KAR																								
	SR.....A393KAR																								
47,000 68,000 100,000	SR.....A473KAR																								
	SR.....A683KAR																								
	SR.....A104KAR																								

For other styles, voltages, tolerances and lead lengths see Part No. Codes or contact factory.

*Other capacitance values available upon special request.

 = Industry preferred values
 = SR20 only

Capacitance ranges available for SR12 and SR07 same as SR15
 SR62 and SR59 same as SR21
 SR64 and SR65 same as SR30
 SR75 same as SR40
 SR13 same as SR21

NOTE: For others voltages, tolerances, electrical specifications and NPO typical characteristics, see the AVX Multilayer Ceramic Leaded Capacitors Catalog.



Radial Leads/SkyCap®/SR Series



X7R Dielectric

SIZE AND CAPACITANCE SPECIFICATIONS

EIA Characteristic

Dimensions: Millimeters (Inches)

AVX Style	SR15	SR20	SR21	SR22	SR27	SR30	SR40	SR50												
AVX “Insertable”	SR07	SR29	SR59	N/A	N/A	SR65	SR75	N/A												
Width (W)	3.81 (.150)	5.08 (.200)	5.08 (.200)	5.08 (.200)	6.604 (.260)	7.62 (.300)	10.16 (.400)	12.70 (.500)												
Height (H)	3.81 (.150)	5.08 (.200)	5.08 (.200)	5.08 (.200)	6.35 (.250)	7.62 (.300)	10.16 (.400)	12.70 (.500)												
Thickness (T)	2.54 (.100)	3.175 (.125)	3.175 (.125)	3.175 (.125)	4.06 (.160)	3.81 (.150)	3.81 (.150)	5.08 (.200)												
Lead Spacing (L.S.)	2.54 (.100)	2.54 (.100)	5.08 (.200)	6.35 (.250)	7.62 (.300)	5.08 (.200)	5.08 (.200)	10.16 (.400)												
Lead Diameter (L.D.)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.635 (.025)												
Cap. in.* pF	Industry Preferred Values in Blue	WVDC			WVDC			WVDC			WVDC			WVDC			WVDC			
		200	100	50	200	100	50	200	100	50	100	50	100	50	200	100	50	200	100	50
470	SR.....C471KAR																			
1000	SR155C102KAR																			
1500	SR.....C152KAR																			
2200	SR.....C222KAR																			
3300	SR.....C332KAR																			
4700	SR.....C472KAR																			
6800	SR.....C682KAR																			
10,000	SR215C103KAR																			
15,000	SR.....C153KAR																			
22,000	SR.....C223KAR																			
33,000	SR.....C333KAR																			
47,000	SR.....C473KAR																			
68,000	SR.....C683KAR																			
100,000	SR215C104KAR																			
150,000	SR.....C154KAR																			
220,000	SR215C224KAR																			
330,000	SR.....C334KAR																			
390,000	SR.....C394KAR																			
470,000	SR305C474KAR																			
1.0 uF	SR305C105KAR																			
2.2 uF	SR405C225KAR																			
2.7 uF	SR505C275KAR																			
4.7 uF	SR505C475KAR																			
10.0 uF	SR655C106KAR																			

For other styles, voltages, tolerances and lead lengths see Part No. Codes or contact factory.

-  = Industry preferred values
-  = Extended range
-  = Extended range with 0.150" thickness maximum

Radial Leads/SkyCap®/SR Series



Z5U Dielectric

SIZE AND CAPACITANCE SPECIFICATIONS

EIA Characteristic

Dimensions: Millimeters (Inches)

AVX Style	SR15	SR20	SR21	SR22	SR27	SR30	SR40	SR50
AVX "Insertable"	SR07	SR29	SR59	N/A	N/A	SR65	SR75	N/A
Width (W)	3.81 (.150)	5.08 (.200)	5.08 (.200)	5.08 (.200)	6.604 (.260)	7.62 (.300)	10.16 (.400)	12.70 (.500)
Height (H)	3.81 (.150)	5.08 (.200)	5.08 (.200)	5.08 (.200)	6.35 (.250)	7.62 (.300)	10.16 (.400)	12.70 (.500)
Thickness (T)	2.54 (.100)	3.175 (.125)	3.175 (.125)	3.175 (.125)	4.06 (.160)	3.81 (.150)	3.81 (.150)	5.08 (.200)
Lead Spacing (L.S.)	2.54 (.100)	2.54 (.100)	5.08 (.200)	6.35 (.250)	7.62 (.300)	5.08 (.200)	5.08 (.200)	10.16 (.400)
Lead Diameter (L.D.)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.508 (.020)	.635 (.025)
Cap. in.* Industry Preferred pF Values in Blue	WVDC 100 50	WVDC 100 50	WVDC 100 50	WVDC 100 50	WVDC 100 50	WVDC 100 50	WVDC 100 50	WVDC 100 50
10,000 SR15E103ZAR								
47,000 SR.....E473ZAR								
100,000 SR215E104ZAR								
150,000 SR.....E154ZAR								
220,000 SR215E224ZAR								
330,000 SR215E334ZAR								
470,000 SR215E474ZAR								
680,000 SR.....E684ZAR								
1.0 µF SR.....105ZAR								
1.5 µF SR30E155ZAR								
2.2 µF SR30E225ZAR								
3.3 µF SR30E335ZAR								
4.7 µF SR30E475ZAR								

For other styles, voltages, tolerances and lead lengths see Part No. Codes or contact factory.

*Other capacitance values available upon special request.

 = Industry preferred values
 = SR20 only

Capacitance ranges available for SR12 and SR07 same as SR15
 SR62 and SR59 same as SR21
 SR64 and SR65 same as SR30
 SR75 same as SR40
 SR13 same as SR21

NOTE: For others voltages, tolerances, electrical specifications and NPO typical characteristics, see the AVX Multilayer Ceramic Leaded Capacitors Catalog.

AVX 500 VOLT SKYCAPS**

STYLE*	MAXIMUM CAPACITANCE VALUE	
	C0G (NP0)	X7R
SR29	900 pF	.015 µF
SR20	1800 pF	.033 µF
SR28 SR59	900 pF	.015 µF
SR13 SR21	1800 pF	.033 µF
SR30 SR61 SR65	7200 pF	.12 µF
SR40 SR75	.015 µF	.27 µF
SR22	1800 pF	.033 µF
SR27	1800 pF	.033 µF
SR76	.015 µF	.27 µF
SR50	.036 µF	.59 µF

*Consult pages 27 and 28 for style sizes.

**Voltage rating based on DWV of 150% of rated voltage.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AVX:

[SR221C104KAA](#) [SR201C103KAATR2](#) [SR405C225JAA](#) [SR221A681KAA](#) [SR301A223KAT](#) [SR505A223JAA](#)
[SR212A360GAA](#) [SR211C563JAA](#) [SR215A682JAA](#) [SR155C392KAA](#) [SR211A122JAATR1](#) [SR215E154MAA](#)
[SR211A152KAA](#) [SR215A472FAA](#) [SR211C153JAATR1](#) [SR305C474MAA](#) [SR751C105JAATR2](#) [SR215A102KAA](#)
[SR215C152KAATR2](#) [SR301E474MAATR1](#) [SR211A272GAATR1](#) [SR301E105ZAATR1](#) [SR291C103KAT](#)
[SR212A221JAA](#) [SR121C103KAATR2](#) [SR212A121JAA](#) [SR211A332JAT](#) [SR215C103KAAAP2](#) [SR152A470KAATR1](#)
[SR212A391KAA](#) [SR301A223GAA](#) [SR305A103KAATR2](#) [SR211C332KAT](#) [SR211A561KAA](#) [SR505E225MAATR1](#)
[SR405A683JAT](#) [SR211A682FAATR1](#) [SR151A181JAATR2](#) [SR202C103MAA](#) [SR201C683MAA](#) [SR211A821JAA](#)
[SR211A332FAA](#) [SR301A822JAA](#) [SR071A391JAA](#) [SR592A101KAATR1](#) [SR221C223KAA](#) [SR215A102FAA](#)
[SR275C682KAT](#) [SR295C332KAT](#) [SR152A390JAATR1](#) [SR211A682JAA](#) [SR655C105MAA](#) [SR201C393KAA](#)
[SR151C392KAA](#) [SR215C823KAA](#) [SR211E103ZAA](#) [SR305C105JAATR1](#) [SR201A272JAATR1](#) [SR301C394KAATR1](#)
[SR075C472KAATR1](#) [SR212A220KAATR1](#) [SR211A471GAATR1](#) [SR152A100KAA](#) [SR215C682MAATR1](#)
[SR405E475MAATR1](#) [SR301E474ZAA](#) [SR595E334MAATR1](#) [SR211C823KAA](#) [SR752C224MAATR1](#)
[SR215C104MAT](#) [SR212A270KAATR1](#) [SR205C683MAA](#) [SR275E224ZAA](#) [SR215C333MAA](#) [SR205C104JAATR1](#)
[SR152A390KAA](#) [SR201A102JAT](#) [SR215A222JAT](#) [SR201C473JAATR1](#) [SR595C153KAA](#) [SR221C473KAA](#)
[SR301A103FAATR1](#) [SR211C152JAA](#) [SR211A102FAT](#) [SR151C821KAA](#) [SR205C393KAA](#) [SR202A751JAA](#)
[SR501C474KAA](#) [SR201A102KAATR1](#) [SR305E225ZAATR1](#) [SR212A180JAA](#) [SR152A101KAA](#) [SR151A101JAT](#)
[SR215E473ZAA](#) [SR211C223JAA](#) [SR201A272KAA](#) [SR205C473KAATR1](#) [SR215C223JAA](#) [SR225C103KAA](#)
[SR211A332JAA](#)