

Ultra Fast Diode



**RoHS
Compliant**



Features:

- Fast reverse recovery time, t_{rr}
- Low forward voltage, V_F
- Low cost axial packages
- Void-free plastic in DO-41 package
- 1 Ampere operation at $T_A = 55^\circ\text{C}$ with no thermal runaway
- Exceeds environmental standards of MIL-S-19500/228
- Ultra fast switching for high efficiency

Specifications:

Mechanical Data:

Case	: Moulded plastic
Terminals	: Axial leads, solderable per MIL-STD-202, Method 208
Polarity	: Band denotes cathode
Mounting Position	: Any
Weight	: 0.013oz, 0.3g

Maximum Ratings and Electrical Characteristics:

Rating at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.



Description	UF102	UF108	Units
Peak Reverse Voltage, Repetitive; V_{RM}	200	800	V
Maximum RMS Voltage	140	560	
DC Blocking Voltage; V_R	200	800	
Average Forward Current, I_o at $T_A = 55^\circ\text{C}$ 3.8" lead Length, 60Hz, Resistive or Inductive Load	1		A
Peak Forward Surge Current IFM (Surge) 8.3m Seconds Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method)		30	
Maximum Forward Voltage V_F at 1A, 25°C	1	1.7	V
Maximum Reverse Current at Rated, $T_J = 25^\circ$ Reverse voltage $T_J = 100^\circ\text{C}$		10 50	μA μA

Description	UF102	UF108	Units
Typical Junction Capacitance (Note 1) C_J		17	pF
Typical Junction Resistance (Note 2) $R_{\theta JA}$	60		°C/W
Reverse Recovery Time $I_F = 0.5A$, $I_R = 1A$, $I_{rr} = 0.25A$	50	75	nS
Operating and Storage Temperature Range	-55 to +150		°C

Notes:

1. Measured at 1MHz and Applied Reverse Voltage of 4V DC.
2. Thermal Resistance from Junction to Ambient and from Junction to Lead Length 0.375" (9.5mm) PCB Mounted.

Ratings and Characteristic Curves:



Set Time Base For 50ns/cm

Notes:

1. Rise Time = 7ns Maximum. Input Impedance = 1MΩ 22pf
2. Rise Time = 10ns Maximum Source Impedance = 50Ω

Figure 1 - Reverse Recovery Time Characteristics and Test Circuit Diagram

Typical Trace




Figure 2 - Forward Characteristics




Figure 3 - Forward Current Derating Curve




Figure 4 - Typical Junction Capacitance





Figure 5 - Peak Forward Surge Current

Ultra Fast Diode



Dimensions : Inches (Millimetres)

Part Number Table

Description	Part Number
Diode, Ultrafast, 1A, 200V	UF102
Diode, Ultrafast, 1A, 800V	UF108

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com

