



SAW Components

SAW Rx Filter

WCDMA Diversity Band I Rx

Series/type:	B9869
Ordering code:	B39212B9869P810
Date:	January 15, 2013
Version:	2.0



SAW Components

B9869

SAW Rx Filter


2140.0MHz

Data sheet




Application

- Low-loss RF filter for mobile telephone
WCDMA Band I systems (diversity) receive path (RX)
- Low amplitude ripple
- Usable passband 60 MHz
- Impedance transform from 50 Ω to 100 Ω
- Unbalanced to balanced operation




Features

- Package size 1.1 x 0.9 x 0.4 mm³
- RoHS compatible
- Approx. weight 0.003g
- Package for **Surface Mount Technology (SMT)**
- Ni, gold-plated terminals
- **Electrostatic Sensitive Device (ESD)**
- **Moisture Sensitive Level 3**



Pin configuration

- 1 Input, unbalanced
- 3,4 Output, balanced
- 2,5 Case-ground





SAW Components	B9869
SAW Rx Filter	2140.0MHz

Data sheet



Characteristics

Temperature range for specification:	$T = -30\text{ °C to }+85\text{ °C}$
Terminating source impedance:	$Z_S = 50\ \Omega$
Terminating load impedance:	$Z_L = 100\ \Omega \parallel 15\text{nH (balanced)}$

		min.	typ. @ 25°C	max.	
Center frequency	f_C	—	2140.0	—	MHz
Maximum insertion attenuation	$\alpha_{\max}$				
2110.0 ... 2170.0 MHz		—	1.4	2.1	dB
Amplitude ripple (p-p)	$\Delta\alpha$				
2110.0 ... 2170.0 MHz		—	0.5	1.2	dB
Input VSWR					
2110.0 ... 2170.0 MHz		—	1.8	2.1	
Output VSWR					
2110.0 ... 2170.0 MHz		—	1.8	2.1	
CMRR ($S_{21}-S_{31} / S_{21}+S_{31}$)					
2110.0 ... 2170.0 MHz		20 ¹⁾	26	—	dB
Attenuation					
100.0 ... 810.0 MHz		40	63	—	dB
810.0 ... 849.0 MHz		50	60	—	dB
849.0 ... 898.0 MHz		40	60	—	dB
898.0 ... 925.0 MHz		50	61	—	dB
925.0 ... 1620.0 MHz		40	52	—	dB
1620.0 ... 1710.0 MHz		40	53	—	dB
1710.0 ... 1755.0 MHz		46	53	—	dB
1755.0 ... 1920.0 MHz		40	54	—	dB
1920.0 ... 1980.0 MHz		50	58	—	dB
1980.0 ... 2050.0 MHz		25	40	—	dB
2400.0 ... 2484.0 MHz		30	42	—	dB
2484.0 ... 3000.0 MHz		32	42	—	dB
3000.0 ... 4600.0 MHz		34	51	—	dB
4600.0 ... 6000.0 MHz		34	56	—	dB

¹⁾ A CMRR of 19.6dB corresponds to a phase balance of 10° together with an amplitude balance of 1.0dB



SAW Components		B9869
SAW Rx Filter		2140.0MHz
Data sheet	SMD	

Maximum ratings

Operable temperature range	T	−40/+85	°C	machine model, 10 pulse
Storage temperature range	T _{stg}	−40/+85	°C	
DC voltage	V _{DC}	5	V	
ESD voltage	V _{ESD}	50 ¹⁾	V	
Input Power at 1920.0 .. 1980.0MHz Tx band	P _{IN}	17	dBm	CW

¹⁾ acc. to JESD22-A115A (machine model), 10 negative & 10 positive pulse.



SAW Components

B9869


SAW Rx Filter

2140.0MHz


Data sheet

SMD

Transfer function (narrow band)




Transfer function (wide band)




Please read cautions and warnings and important notes at the end of this document.

S_{11} function



S_{22} function





SAW Components	B9869
SAW Rx Filter	2140.0MHz

Data sheet



References

Type	B9869
Ordering code	B39212B9869P810
Marking and package	C61157-A8-A56
Packaging	F61074-V8255-Z000
Date codes	L_1126
S-parameters	B9869_NB.s3p, B9869_WB.s3p See file header for port/pin assignment table.
Soldering profile	S_6001
RoHS compatible	RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8 th , 2011, on the restriction of the use of certain hazardous substances in electrical and electronic equipment ("Directive") with due regard to the application of exemptions as per Annex III of the Directive in certain cases.
Moldability	Before using in overmolding environment, please contact your EPCOS sales office.
Matching coils	See Inductor pdf-catalog http://www.tdk.co.jp/tefe02/coil.htm#aname1 and Data Library for circuit simulation http://www.tdk.co.jp/etvcl/index.htm

For further information please contact your local EPCOS sales office or visit our webpage at www.epcos.com.

Published by EPCOS AG
Systems, Acoustics, Waves Business Group
P.O. Box 80 17 09, 81617 Munich, GERMANY

© EPCOS AG 2013. This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.

Please read *cautions and warnings* and *important notes* at the end of this document.

7 January 15, 2013



Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CeraLink, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FilterCap, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.