





P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECO-10-025607	21DEC10	HMR	MW
	E1	REVISED PER ECO-16-017354	10MAR2017	RK	AS




2.00-3.00	20.20	22.20
1.25-2.00	19.60	22.20
0.75-1.25	19.40	22.20
PANEL THICKNESS	X	Y



PRODUCT MARKING
DETAIL A




PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36


6 1634200-2 SHOWN ON-OFF

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712 2-4-07	TE Connectivity	
DIMENSIONS: mm		CHK —		
		APVD —	NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED	
		PRODUCT SPEC —		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC —	SIZE A2	CAGE CODE 00779
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -		WEIGHT —	DRAWING NO C-1634200	RESTRICTED TO —
MATERIAL —		CUSTOMER DRAWING	SCALE 3:1	SHEET 1 of 7
			REV E1	




2.00–3.00	20.20	22.20
1.25–2.00	19.60	22.20
0.75–1.25	19.40	22.20
PANEL THICKNESS	X	Y

CIRCUIT DIAGRAM



PRODUCT MARKING
DETAIL A



PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36


7 OBSOLETE 1634200-8 SHOWN ON-OFF ILLUMINATED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712 2-4-07	TE Connectivity			
DIMENSIONS: mm		CHK -	NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED			
		APVD -				
		PRODUCT SPEC -				
		APPLICATION SPEC -				
MATERIAL -		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-1634200	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 3:1	SHEET 2 of 7	REV E1




2.00–3.00	20.20	22.20
1.25–2.00	19.60	22.20
0.75–1.25	19.40	22.20
PANEL THICKNESS	X	Y

CIRCUIT DIAGRAM



PRODUCT MARKING
DETAIL A



PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36


8 1-1634200-2 SHOWN ON-ON

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712 CHK —	2—4—07		 TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME		
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± ± — FINISH		PRODUCT SPEC —	POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON—ILLUMINATED		
				APPLICATION SPEC —			
MATERIAL —		WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO 1634200	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 3:1	SHEET 3 of 7	REV F1	




2.00–3.00	20.20	22.20
1.25–2.00	19.60	22.20
0.75–1.25	19.40	22.20
PANEL THICKNESS	X	Y

CIRCUIT DIAGRAM



PRODUCT MARKING
DETAIL A


PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36


9 1-1634200-7 SHOWN ON-OFF-ON

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712 2-4-07	TE Connectivity			
DIMENSIONS: mm		CHK -	NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	SIZE A2			
0 PLC ± -		PRODUCT SPEC -	CAGE CODE 00779			
1 PLC ± -		APPLICATION SPEC -	DRAWING NO 1634200			
2 PLC ± -		WEIGHT -	RESTRICTED TO -			
3 PLC ± -		CUSTOMER DRAWING	SCALE 3:1			
4 PLC ± -			SHEET 4 of 7			
ANGLES ± -			REV E1			
FINISH -						




PANEL CUT OUT

2.00–3.00	20.20	22.20
1.25–2.00	19.60	22.20
0.75–1.25	19.40	22.20
PANEL THICKNESS	X	Y



PRODUCT MARKING
DETAIL A




PRE
10A 125VAC, 6A 250VAC





TYCO ELECTRONICS LOGO
PER TEC-202-36

10 2-1634200-3 SHOWN ON-OFF-(ON)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712		2-4-07		 TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK —		NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED							
		0 PLC ± —		APVD —									
		1 PLC ± —		PRODUCT SPEC —									
		2 PLC ± —		APPLICATION SPEC —									
3 PLC ± —		4 PLC ± —		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
MATERIAL —		FINISH —		WEIGHT —		A2		00779		C=1634200		—	
CUSTOMER DRAWING						SCALE 3:1		SHEET 5 of 7		REV E1			




2.00-3.00	20.20	22.20
1.25-2.00	19.60	22.20
0.75-1.25	19.40	22.20
PANEL THICKNESS	X	Y



PRODUCT MARKING
DETAIL A

PRE
10A 125VAC, 6A 250VAC



TYCO ELECTRONICS LOGO
PER TEC-202-36

11 2-1634200-6 SHOWN (ON)-OFF-(ON)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712 2-4-07	TE Connectivity			
DIMENSIONS: mm		CHK -				
		APVD -	NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED			
		PRODUCT SPEC -	SIZE A2			
MATERIAL -		APPLICATION SPEC -	CAGE CODE 00779			
		WEIGHT -	DRAWING NO C-1634200			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING	SCALE 3:1	SHEET 6 of 7	REV E1	RESTRICTED TO -

D

 COMPONENT RECOGNIZED TO EUROPEAN STANDARDS (ENEC, PENDING VDE). MARKS LICENSE No. 40006757

ROCKER COLOR: X11 = B — BLACK
G — GREEN
R — RED
W — WHITE

G — GREEN
R — RED
B — BLACK
W — WHITE

1634200

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SA008712 2-4-07 CHK — APVD — PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		 TE Connectivity NAME POWER ROCKER SWITCH 19,4MM X 22,2mm PANEL SIZE DPST, NON-ILLUMINATED	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH —		SIZE A2 CAGE CODE 00779 DRAWING NO C=1634200 RESTRICTED TO —	
MATERIAL —		CUSTOMER DRAWING		SCALE 3:1 SHEET 7 of 7 REV E1	