





*3/16 HEX FEMALE SCREW LOCKS (inch)



STYLE 1



STYLE 2



ORDERING CODE	XX MATERIAL	XXXX BASIC PART NUMBER	XX FINISH
---------------	----------------	---------------------------	--------------

MATERIAL	CODE
*STEEL	ST
STAINLESS STEEL	SS
BRASS	BR

STYLE 1

BASIC PART NUMBERS			A (REF.) LENGTH	B LENGTH	C LENGTH	D FEMALE THREAD	E MALE THREAD
SCREW-LOCK ONLY	KIT	BULK					
9410	9420	9430	.375	.187	.187	4-40 UNC-2B	4-40 UNC-2A
9411	9421	9431	.437		.250		
9412	9422	9432	.500		.312		
9413	9423	9433	.562		.375		
9414	9424	9434	.625		.437		
9415	9425	9435	.688		.500		
9416	9426	9436	.750		.562		
9417	9427	9437	.812		.625		
9418	9428	9438	.875		.688		
9419	9429	9439	.937		.750		
9440	9441	9442	.550	.191 ± .002	.365	2-56	2-56
9443	9444	9445	.500		.312		
9446	9447	9448	.500	.187	.312	4-40	4-40
9449	9450	9451	.500	.185 Max.	.312	4-40	4-40
9452	9453	9454	.442	.130	.312	4-40	4-40
9455	9456	9457	.735	.305	.430	4-40	4-40
9390	9391	9392	.720	.210	.510	4-40	4-40

STYLE 2

9411	9393	9394	.437	.187	.250	4-40	4-40
------	------	------	------	------	------	------	------

CODE	FINISH	CODE	FINISH
00	Plain — None	35	Zinc ASTMB633, Type I, Fe/Zn 8 — No Chromate
01	Passivate MIL-F-140720-E300	36	Zinc ASTMB633, Type II, Fe/Zn 8 — Yellow Chromate
02	Caustic Etch	43	Bright Tin — MIL-T-10727
03	Bright Dip — Brass	50	Black Oxide MIL-C-13924 — Steel
31	Cadmium QQ-P-416, CL 2 — Clear Chromate	51	Black Oxide MIL-F-495 — Brass
32	Cadmium QQ-P-416, CL 2, Type II — Yellow Chromate	52	Black Oxide MIL-C-13924 — Stainless Steel
33	Zinc, ASTMB633, Type II, CL 3 — Black Chromate	61	Nickel QQ-N-290 CL 1, Type VI KC
34	Zinc ASTMB633, Type III, Fe/Zn 8 — Clear Chromate	63	Ductile, Nickel — QQ-N-290

*Also manufactured in 5 millimeter Hex Steel. Please call the sales department for pricing and availability.

STYLE 1



STYLE 2



NOTES:

- Two assemblies are required per connector.
- Each kit contains 2 female screw locks, 4 flat washers, 2 split lock washers, 2 hex nuts.
- Bulk quantities — each type part is separately packaged.
- All parts are shipped unassembled.
- Other combinations of body lengths (B) and male lengths (C) are available.
- Partially threaded male lengths are available.
- All above parts are available with 3/16" round body.
- *Most common material is steel with optional finish.
- A 6" lb. (female) and a 4" lb. (male) maximum assembly torque is recommended for steel screw locks.
- All dimensions are for reference only. Tolerances are to manufacturer's standards.

G6

