







Amphenol  
FCi

© 2016 AFci


|               |  |                                       |  |                                       |  |                 |  |            |  |                                                                                       |  |                                                                                       |  |                                                                   |  |         |  |           |  |          |  |     |  |
|---------------|--|---------------------------------------|--|---------------------------------------|--|-----------------|--|------------|--|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|--|-------------------------------------------------------------------|--|---------|--|-----------|--|----------|--|-----|--|
| spec ref      |  | -                                     |  | dr                                    |  | Chris Gieski    |  | 2015/01/31 |  | projection                                                                            |  |  |  | mm                                                                |  | size    |  | A2        |  | scale    |  | 4:1 |  |
| tolerance std |  | TOLERANCES UNLESS OTHERWISE SPECIFIED |  | eng                                   |  | Vicking Liu     |  | 2018/01/23 |  |  |  | title                                                                                 |  | RA ORTHO RECEPTACLE ASSEMBLY 2DC<br>PWRMAX ORTHO CONNECTOR SYSTEM |  | dwg no  |  | 10132644  |  | rev      |  | A   |  |
| ISO 406       |  |                                       |  | chr                                   |  | Feng Zheng      |  | 2018/01/23 |  |                                                                                       |  |                                                                                       |  |                                                                   |  |         |  |           |  |          |  |     |  |
| ISO 1101      |  |                                       |  | appr                                  |  | Pei-Ming Zheng  |  | 2018/01/23 |  |                                                                                       |  |                                                                                       |  |                                                                   |  |         |  |           |  |          |  |     |  |
|               |  |                                       |  |                                       |  |                 |  |            |  | product family                                                                        |  | --                                                                                    |  | ecn no                                                            |  | -       |  | rel level |  | Released |  |     |  |
| surface       |  | linear                                |  | 0.X ±0.5<br>0.XX ±0.25<br>0.XXX ±0.10 |  | Amphenol<br>FCI |  | cat. no.   |  | -                                                                                     |  | Product - Customer Drw                                                                |  | sheet 1 of 6                                                      |  |         |  |           |  |          |  |     |  |
| ISO 1302      |  |                                       |  |                                       |  |                 |  |            |  |                                                                                       |  |                                                                                       |  |                                                                   |  | angular |  | 0° ±2°    |  |          |  |     |  |
|               |  |                                       |  |                                       |  |                 |  |            |  |                                                                                       |  |                                                                                       |  |                                                                   |  |         |  |           |  |          |  |     |  |




| PART NO        | DESCRIPTION                  |
|----------------|------------------------------|
| 10132644-003LF | PCB RA RECEPTACLE STB OPTION |



SEE NOTE 4-



SECTION RIGHT-RIGHT  
SCALE 4:1




|               |  |                                       |  |       |  |                |  |                 |  |                                                                                       |  |                                                                                       |  |              |  |              |  |          |  |          |  |     |  |   |  |
|---------------|--|---------------------------------------|--|-------|--|----------------|--|-----------------|--|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|--|--------------|--|--------------|--|----------|--|----------|--|-----|--|---|--|
| spec ref      |  | -                                     |  | dr    |  | Chris Gieski   |  | 2015/01/31      |  | projection                                                                            |  |  |  | mm           |  | size         |  | A2       |  | scale    |  | 1:1 |  |   |  |
| tolerance std |  | TOLERANCES UNLESS OTHERWISE SPECIFIED |  | eng   |  | Vickling Liu   |  | 2018/01/23      |  |  |  | ecn no                                                                                |  | -            |  | rel level    |  | Released |  |          |  |     |  |   |  |
| ISO 406       |  |                                       |  | chr   |  | Feng Zheng     |  | 2018/01/23      |  |                                                                                       |  | product family                                                                        |  | --           |  |              |  |          |  |          |  |     |  |   |  |
| ISO 1101      |  |                                       |  | appr  |  | Pei-Ming Zheng |  | 2018/01/23      |  |                                                                                       |  |                                                                                       |  |              |  |              |  |          |  |          |  |     |  |   |  |
| surface       |  | linear                                |  | 0.X   |  | ±0.5           |  | Amphenol<br>FCi |  | title                                                                                 |  | RA ORTHO RECEPTACLE ASSEMBLY 2DC<br>PWRMAX ORTHO CONNECTOR SYSTEM                     |  |              |  |              |  | dwg no   |  | 10132644 |  | rev |  | A |  |
|               |  |                                       |  | 0.XX  |  | ±0.25          |  |                 |  |                                                                                       |  |                                                                                       |  |              |  |              |  |          |  |          |  |     |  |   |  |
|               |  |                                       |  | 0.XXX |  | ±0.10          |  |                 |  |                                                                                       |  |                                                                                       |  |              |  |              |  |          |  |          |  |     |  |   |  |
| ISO 1302      |  | angular                               |  | 0°    |  | ±2°            |  | cat. no.        |  | -                                                                                     |  | Product-                                                                              |  | Customer Drw |  | sheet 3 of 6 |  |          |  |          |  |     |  |   |  |




|                          |                                                      |                        |                       |                     |                   |                    |                     |                           |               |
|--------------------------|------------------------------------------------------|------------------------|-----------------------|---------------------|-------------------|--------------------|---------------------|---------------------------|---------------|
| 1                        | 2                                                    | 3                      | 4                     | 5                   | 6                 | 7                  | 8                   |                           |               |
| TOP LAYER<br>DESCRIPTION | TABLE 1 (PWRMAX)<br>PLATED THROUGH-HOLE REQUIREMENTS |                        |                       |                     |                   |                    |                     |                           |               |
|                          | DRILLED HOLE<br>DIAMETER                             | COPPER<br>THICKNESS    | TIN-LEAD<br>THICKNESS | NICKEL<br>THICKNESS | GOLD<br>THICKNESS | TIN<br>THICKNESS   | SILVER<br>THICKNESS | FINISHED<br>HOLE DIAMETER |               |
|                          | IMMERSION TIN                                        | 1.68-1.73 (1.72 DRILL) | 0.025 - 0.050         | --                  | --                | --                 | 0.9 - 1.5um         | --                        | 1.500 - 1.650 |
|                          | IMMERSION SILVER                                     | 1.68-1.73 (1.72 DRILL) | 0.025 - 0.050         | --                  | --                | --                 | 0.15 - 0.65um       | --                        | 1.500 - 1.650 |
|                          | COPPER (SEE NOTE 8)                                  | 1.68-1.73 (1.72 DRILL) | 0.025 - 0.050         | --                  | --                | --                 | --                  | --                        | 1.500 - 1.650 |
|                          | GOLD                                                 | 1.68-1.73 (1.72 DRILL) | 0.025 - 0.050         | --                  | 0.003 - 0.007     | FLASH UP TO 0.0002 | --                  | --                        | 1.500 - 1.650 |

| TABLE 2 (PWRMAX OTHOGONAL PLUG)<br>BUSBAR HOLE REQUIREMENTS |                           |
|-------------------------------------------------------------|---------------------------|
| DESCRIPTION                                                 | FINISHED<br>HOLE DIAMETER |
| BUSBAR                                                      | 1.600 ± 0.050             |




|               |  |                                       |  |       |  |                |  |                 |  |                                                                   |  |                                                                                       |  |              |  |          |  |       |  |     |  |
|---------------|--|---------------------------------------|--|-------|--|----------------|--|-----------------|--|-------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|--|--------------|--|----------|--|-------|--|-----|--|
| spec ref      |  | -                                     |  | dr    |  | Chris Gieski   |  | 2015/01/31      |  | projection                                                        |  |  |  | size         |  | A2       |  | scale |  | 2:1 |  |
| tolerance std |  | TOLERANCES UNLESS OTHERWISE SPECIFIED |  | eng   |  | Vicking Liu    |  | 2018/01/23      |  | mm                                                                |  |  |  | ecn no       |  | -        |  |       |  |     |  |
| ISO 406       |  |                                       |  | chr   |  | Feng Zheng     |  | 2018/01/23      |  |                                                                   |  |                                                                                       |  |              |  |          |  |       |  |     |  |
| ISO 1101      |  |                                       |  | appr  |  | Pei-Ming Zheng |  | 2018/01/23      |  | product family                                                    |  | -                                                                                     |  | rel level    |  | Released |  |       |  |     |  |
| surface       |  | linear                                |  | 0.X   |  | ±0.5           |  | Amphenol<br>FCI |  | RA ORTHO RECEPTACLE ASSEMBLY 2DC<br>PWRMAX ORTHO CONNECTOR SYSTEM |  | dwg no                                                                                |  | 10132644     |  | rev      |  | A     |  |     |  |
|               |  | 0.XX                                  |  | ±0.25 |  |                |  |                 |  |                                                                   |  |                                                                                       |  |              |  |          |  |       |  |     |  |
|               |  | 0.XXX                                 |  | ±0.10 |  |                |  |                 |  |                                                                   |  |                                                                                       |  |              |  |          |  |       |  |     |  |
| ISO 1302      |  | angular                               |  | 0°    |  | ±2°            |  | cat. no.        |  | -                                                                 |  | Product - Customer Drw                                                                |  | sheet 4 of 6 |  |          |  |       |  |     |  |




| RA ORTHO RECEPTACLE ASSEMBLY 2DC |              |        |                                       |
|----------------------------------|--------------|--------|---------------------------------------|
| PRODUCT NUMBER                   | PLATING TYPE | TOOLED | DESCRIPTION                           |
| 10132644-001LF                   | GCS          | NO     | BUSBAR RA RECEPTACLE PRESS FIT OPTION |
| 10132644-002LF                   | GCS          | YES    | PCB RA RECEPTACLE PRESS FIT OPTION    |
| 10132644-003LF                   | GCS          | YES    | PCB RA RECEPTACLE STB OPTION          |

NOTES:


1. CONNECTOR MATERIALS:  
HOUSING: HIGH TEMP THERMOPLASTIC, BLACK  
UL94 V-0 COMPLIANT  
CONTACTS: COPPER ALLOY
2. CONTACT FINISH: (REF. GS-12-1342 SECTION 5.2).
3. PRODUCT SPECIFICATION: GS-12-1342.  
APPLICATION SPECIFICATION: GS-20-0452.  
PACKAGING SPECIFICATION: GS-14-2479
4. PRODUCT MARKING (MANUFACTURER'S NAME, PRODUCT NUMBER AND DATE CODE) ON HOUSING IN AREA SHOWN.
5. MINIMAL NOMINAL BUSBAR & PCB THICKNESS: 1.60 mm
6. COPPER PLATING THICKNESS IN CENTER OF VIA-HOLE CAN BE NO MORE THAN 0.003 LESS THAN OTHER AREAS.
7. ALL HOLE SIZES ARE FINISHED HOLE SIZES UNLESS OTHERWISE NOTED.
8. PLASTIC PEG MOUNTING HOLES ARE UNPLATED.  
Ø 2.85 ± 0.10 FOR PRESS-FIT TAILS  
Ø 2.55 ± 0.10 FOR SOLDER TAILS
9. CONNOCTER KEEP OUT ZONE.



10132644-001  
SCALE 4:1



10132644-002  
SCALE 4:1



10132644-003  
SCALE 4:1

|               |  |              |  |                                  |            |                                                 |                        |           |              |     |
|---------------|--|--------------|--|----------------------------------|------------|-------------------------------------------------|------------------------|-----------|--------------|-----|
| spec ref -    |  | dr           |  | Chris Gieski                     | 2015/01/31 | <div>projection</div> <div></div> <div>mm</div> | size                   | A2        | scale        | 4:1 |
| tolerance std |  | eng          |  | Vicking Liu                      | 2018/01/23 |                                                 | ecn no -               | rel level | Released     |     |
| ISO 406       |  | chr          |  | Feng Zheng                       | 2018/01/23 |                                                 |                        |           |              |     |
| ISO 1101      |  | appr         |  | Pei-Ming Zheng                   | 2018/01/23 |                                                 |                        |           |              |     |
| surface       |  | Amphenol FCI |  | title                            |            | dwg no                                          |                        | rev       |              |     |
| ISO 1302      |  |              |  | RA ORTHO RECEPTACLE ASSEMBLY 2DC |            | 10132644                                        |                        |           |              |     |
|               |  |              |  | PWRMAX ORTHO CONNECTOR SYSTEM    |            |                                                 |                        | A         |              |     |
|               |  |              |  | cat. no.                         |            | -                                               | Product - Customer Drw |           | sheet 6 of 6 |     |