



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G9	REVISED PER ECR-16-012572	04OCT2016	BW	RS


2pol.
8-927 742-2




2pol.
0-927 742-2
5-927 742-5
9-927 742-2




3pol.
0-927 742-3
1-927 742-3
5-927 742-3
9-927 742-3




4pol.
0-927 742-4
9-927 742-4




5pol.
0-927 742-5






6pol.
0-927 742-6
1-927 742-6
5-927 742-6
6-927 742-6
7-927 742-6
8-927 742-6



7pol.
0-927 742-7
2-927 742-7



8pol.
0-927 742-8



SCALE 1:1

1) TYPICAL CAVITY SUITABLE FOR:
FASTIN-FASTON TAB CONTACTS 6.3 mm SRS:
P/N: 60294, 0.3-0.8 mm2 WIRE RANGE
160691, 0.3-0.8 mm2 WIRE RANGE
AMPLIVAR CONTACTS:
P/N: 141051, 0.1-0.5 mm2 WIRE RANGE
142411, 0.3-1.6 mm2 WIRE RANGE
MAX. INSULATION DIA. 2.8 mm,
MAX. INSULATION CRIMP WIDTH 3.3 mm.

2) SEE TABLE FOR SUITABLE COUNTERPART.

3) CIRCUIT IDENTIFICATION No. ACCORDING TO DIN 1451.

4) POLARIZATION KEYS DIMENSIONS AND POSITIONS
ARE ACCORDING TO "RAST 5" NORM

5) TE TRADEMARK "LOGO" AND
TYCO ELECTRONICS "PART NUMBER"
OPTIONAL POSITION.


6) PACKAGING ACCORDING TO TE SPEC. 107-20248.

7) PRODUCT ACCORDING TO IEC 60335-1 NORM.


8) NOT TOOLED YET.

9) SPECIAL VERSION WITH LARGER GAP "A"


SECTION A-A



SECTION B-B



PANEL CUT DIMENSIONS
SCALE 1:1



0.8-1.0 THICKNESS

12	-	-	-	-	-	-	-	-	-
11	-	-	-	-	-	-	-	-	-
10	-	-	-	-	-	-	-	-	-
9	-	-	-	-	-	-	-	-	-
8	-	-	-	-	-	-	-	-	-
7	44	30	35	2-927 742-7	0-927 740-7	UL94V-2	black	-	-
7	44	30	35	0-927 742-7	0-927 740-7	UL94V-2	natur	-	-
6	39	25	30	8-927 742-6	0-927 740-6	UL94-V0	natur	-	7
6	39	25	30	7-927 742-6	0-927 740-6	UL94V-2	natur	-	7
6	39	25	30	6-927 742-6	0-927 740-6	UL94V-0	black	-	-
6	39	25	30	5-927 742-6	0-927 740-6	UL94V-0	natur	-	-
6	39	25	30	1-927742-6	927740-6	UL94-V2	natur	-	7 9
6	39	25	30	0-927 742-6	0-927 740-6	UL94V-2	natur	-	-
5	34	20	25	0-927 742-5	0-927 740-5	UL94V-2	natur	-	9
4	29	15	20	9-927 742-4	0-927 740-4	UL94V-2	natur	-	7
4	29	15	20	0-927 742-4	0-927 740-4	UL94V-2	natur	-	-
3	24	10	15	9-927 742-3	0-927 740-3	UL94V-2	natur	-	7
3	24	10	15	5-927 742-3	0-927 740-3	UL94V-0	natur	-	-
3	24	10	15	2-927 742-3	0-927 740-3	UL94V-2	grey	-	-
3	24	10	15	1-927742-3	927740-3	UL94V-2	natur	-	7 9
OBSOLETE	3	24	10	0-927 742-3	0-927 740-3	UL94V-2	natur	-	-
2	19	5	10	9-927 742-2	4-927 740-2	UL94V-2	natur	-	7
2	19	5	10	8-927 742-2	-	UL94V-2	natur	-	7
2	19	5	10	5-927 742-2	4-927 740-2	UL94V-0	natur	-	-
2	19	5	10	0-927 742-2	4-927 740-2	UL94V-2	natur	-	9
POS.	W	X	Y	PART-NO.	STANDARD TIMER	MATERIAL	COLOUR	REV.	NOTE
PARTS LIST									

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. YAALI	Z2MAR2005	TE Connectivity	
DIMENSIONS: mm		CHK G. TURCO	-		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	-	NAME 2-12 POS. FASTIN-FASTON CONNECTOR TAB HOUSING RAST 5, PANEL MOUNT VERSION	
		PRODUCT SPEC	-		
		APPLICATION SPEC	-		
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT	-	SIZE A100779	RESTRICTED TO
CUSTOMER DRAWING		DRAWING NO C=927742		SHEET 1 OF 1	REV G9