SKKT 162, SKKH 162

THYRISTOR BRIDGE,SCR,BRIDGE

SEMIPACK® 2

Thyristor / Diode Modules

SKKT 162

SKKH 162

Features

- Heat transfer through aluminium oxide ceramic isolated metal baseplate
- Hard soldered joints for high reliability
- UL recognized, file no. E 63 532

Typical Applications

- DC motor control (e. g. for machine tools)
- Temperature control (e. g. for ovens, chemical processes)
- Professional light dimming (studios, theaters)

1) See the assembly instructions

V_{RSM} V	V_{RRM}, V_{DRM} V	I_{TRMS} = 250 A (maximum value for continuous operation) I_{TAV} = 160 A (sin.180; T_c = 83 °C)	
900	800	SKKT 162/08E	SKKH 162/08E
1300	1200	SKKT 162/12E	SKKH 162/12E
1500	1400	SKKT 162/14E	SKKH 162/14E
1700	1600	SKKT 162/16E	SKKH 162/16E
1900	1800	SKKT 162/18E	SKKH 162/18E

Symbol	Conditions	Values	Units
I_{TAV}	sin. 180; T_c = 85 (100) °C;	156 (110)	A
I_D	P3/180F; T_a = 35 °C; B2 / B6	190 / 230	A
I_{RMS}	P3/180F; T_a = 35 °C; W1 / W3	265 / 3 * 185	A
I_{TSM}	T_{vj} = 25 °C; 10 ms	5400	A
	T_{vj} = 125 °C; 10 ms	5000	A
i^2t	T_{vj} = 25 °C; 8,3 ... 10 ms	145000	A^2s
	T_{vj} = 125 °C; 8,3 ... 10 ms	125000	A^2s
V_T	T_{vj} = 25 °C; I_T = 500 A	max. 1,6	V
$V_{T(TO)}$	T_{vj} = 125 °C	max. 0,85	V
r_T	T_{vj} = 125 °C	max. 1,5	mΩ
I_{DD}; I_{RD}	T_{vj} = 125 °C; V_{RD} = V_{RRM}; V_{DD} = V_{DRM}	max. 40	mA
t_{gd}	T_{vj} = 25 °C; I_G = 1 A; di_G/dt = 1 A/µs	1	µs
t_{gr}	V_D = 0,67 * V_{DRM}	2	µs
$(di/dt)_{cr}$	T_{vj} = 125 °C	max. 200	A/µs
$(dv/dt)_{cr}$	T_{vj} = 125 °C	max. 1000	V/µs
t_q	T_{vj} = 125 °C ,	50 ... 150	µs
I_H	T_{vj} = 25 °C; typ. / max.	150 / 400	mA
I_L	T_{vj} = 25 °C; R_G = 33 Ω; typ. / max.	300 / 1000	mA
V_{GT}	T_{vj} = 25 °C; d.c.	min. 2	V
I_{GT}	T_{vj} = 25 °C; d.c.	min. 150	mA
V_{GD}	T_{vj} = 125 °C; d.c.	max. 0,25	V
I_{GD}	T_{vj} = 125 °C; d.c.	max. 10	mA
$R_{th(j-c)}$	cont.; per thyristor / per module	0,17 / 0,085	K/W
$R_{th(j-c)}$	sin. 180; per thyristor / per module	0,18 / 0,09	K/W
$R_{th(j-c)}$	rec. 120; per thyristor / per module	0,2 / 0,1	K/W
$R_{th(c-s)}$	per thyristor / per module	0,1 / 0,05	K/W
T_{vj}		- 40 ... + 125	°C
T_{stg}		- 40 ... + 125	°C
V_{isol}	a. c. 50 Hz; r.m.s.; 1 s / 1 min.	3600 / 3000	V~
M_s	to heatsink	5 ± 15 %[1)]	Nm
M_t	to terminal	5 ± 15 %	Nm
a		5 * 9,81	m/s^2
m	approx.	165	g
Case	SKKT	A 21	
	SKKH	A 22	



SKKT SKKH

 © by SEMIKRON



Fig. 1L Power dissipation per thyristor vs. on-state current



Fig. 1R Power dissipation per thyristor vs. ambient temp.



Fig. 2L Power dissipation per module vs. rms current



Fig. 2R Power dissipation per module vs. case temp.



Fig. 3L Power dissipation of two modules vs. direct current



Fig. 3R Power dissipation of two modules vs. case temp.

 © by SEMIKRON



Fig. 4L Power dissipation of three modules vs. direct and rms current



Fig. 4R Power dissipation of three modules vs. case temp.



Fig. 5 Recovered charge vs. current decrease



Fig. 6 Transient thermal impedance vs. time



Fig. 7 On-state characteristics



Fig. 8 Surge overload current vs. time

 © by SEMIKRON



Fig. 9 Gate trigger characteristics

Dimensions in mm



Case A 21 (SKKT)


Case A 22 SKKH

This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.

 © by SEMIKRON