

Change Language 

- English
- 日本語
- 한국어
- 简体中文
- Deutsch
- Español
- Русский

Register  Login 

- Products
- Industries
- Capabilities
- CAREERS
- Resources
- Find Distributor
- Contact Molex

Menu 

Enter Part No. or Keyw 

Search

 Product Name Index

 Cross Reference

Status:

 Obsolete

 Add to My Parts



Email this page

Part Number: 791080073

Image not available

• **Series:** 79108
• **Replacement:** NO
• **Category:** PCB Receptacles
• **Overview:** Milli-Grid Connector System

 Check Distributor Inventory

 Engineering Documents  Environmental  Part Details

Engineering Documents



Product Environmental Compliance



Compliance:

EU ELV: Product not active

EU RoHS: Product not active

EU RoHS Phthalates: Product not active

China RoHS: 

REACH SVHC: Product not active

Low-Halogen Status: Product not active

Documents:

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

*IEC-62474

*chemSHERPA (xml)

Request Molex's CMRT from conflictminerals@molex.com

Part Details



Expand All

General

Status	Obsolete
Replacement Part Number	NO
Category	PCB Receptacles
Series	79108
Application	Board-to-Board, Signal
Overview	Milli-Grid Connector System
Product Name	Milli-Grid
UPC	800754350099
Physical	
Circuits (Loaded)	48
Circuits (maximum)	48
Color - Resin	TOP
Durability (mating cycles max)	50
Glow-Wire Capable	No
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Number of Rows	2
Orientation	Right Angle
PC Tail Length	1.27mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole
Electrical	

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Do you have any questions?

[Contact Us](#)

California Proposition 65 Information

This product contains Prop 65 substances, the following warning may be required based on application and use:

 **WARNING:** This product can expose you to , known to the State of California to cause .

For more information go to www.P65Warnings.ca.gov

Products+

- [Product Categories](#)
- [Product Index](#)
- [Industries](#)

Quick Links+

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Investor Relations](#)
- [Literature](#)
- [Press Room / Press Releases](#)
- [Sitemap](#)
- [Terms & Conditions](#)

Resources+

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Help](#)
- [Jobs](#)
- [Legal | Trademarks](#)
- [Supplier Portal](#)
- [Privacy Policy](#)
- [Tradeshows](#)
- [Molex News](#)

Stay Connected



