





	5	4	3	2	1					
	Mating face according to MIL-C-24308 / DIN 41 652 / CECC 75301-802									
D										
	No. 1 contact		Printed board layout(1,6±0,2 thick) View component side (PCB plating = Tin)							
C	Grounding pins 0,2x0,6									
										
B			No. 1 contact							
	Mounting force on Printed board : 25 - 80 N									
A	09 66 162 6815	M3	2							
	09 66 162 7815	M3	3							
	09 66 162 5815	M3	0,76 µm Au							
	09 66 162 6816	4-40 UNC	2							
	09 66 162 7816	4-40 UNC	3	29749	14-FEB-02	JB				
	09 66 162 5816	4-40 UNC	0,76 µm Au	29733	23-NOV-01	JB				
	Part number	nut thread	Performance level	Mod.	Dat.	Name			D-Sub male low profile 9 poles with solder pins, nuts,board lock and grounding pins	
							HARTING EURL F-95972 Paris		TB 09 66 162 X81x	
							Sub.		Maßstab/ Scale 1,5:1	
									Blatt/ Page 4	