




- 1 NYLON, UL 94-VO RATED, RED.
- 2 PHOSPHOR BRONZE.
- 3 3.81µm [.000150] MIN TIN-LEAD OVER 1.27µm [.000050] MIN NICKEL.
- 4 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5 3.81µm [.000150] MIN TIN OVER 1.27µm [.000050] MIN NICKEL.
- 6 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 7 PRELIMINARY PART NUMBER.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECO-16-004940	06AUG2016	NK	MZ
	P	REVISED PER ECO-17-011181	04AUG2017	RS	MZ
	R	REVISED PER ECO-18-000437	17JAN2018	RS	MZ

OBSOLETE	3.50[.137]	6	YES	1-207530-1
OBSOLETE	4.60[.181]	6	NO	1-207530-0
		6	YES	207530-9
		5	NO	207530-8
		5	YES	207530-7
OBSOLETE		4	NO	207530-4
OBSOLETE		4	YES	207530-3
OBSOLETE		3	NO	207530-2
OBSOLETE		3	YES	207530-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03/19/92		TE Connectivity												
		L	SIPE														
		CHK	3-25-92														
		R	STONE		NAME												
		APVD	3-25-92														
		A TRAVIS															
		PRODUCT SPEC															
		108-10033															
		APPLICATION SPEC		SOCKET HEADER ASSEMBLY, 18 POSITION, METRIMATE													
		-															
		WEIGHT								SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		-								A2		00779		C=207530		-	
		CUSTOMER DRAWING										SCALE		4:1		SHEET	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:															
		0 PLC ± -															
		1 PLC ± -															
		2 PLC ± 0.25 [.010]															
		3 PLC ± -															
		4 PLC ± -															
MATERIAL		FINISH															
HOUSING: 		CONTACT: SEE TABLE															