

## 74VHC573

### Octal D-Type Latch with 3-STATE Outputs

#### General Description

The VHC573 is an advanced high speed CMOS octal latch with 3-STATE output fabricated with silicon gate CMOS technology. It achieves the high speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation. This 8-bit D-type latch is controlled by a latch enable input (LE) and an Output Enable input (OE). When the OE input is HIGH, the eight outputs are in a high impedance state.

An input protection circuit ensures that 0V to 7V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5V to 3V systems and two supply systems such as battery back up. This circuit prevents device destruction due to mismatched supply and input voltages.

#### Features


- High Speed:  $t_{PD} = 5.0$  ns (typ) at  $V_{CC} = 5V$
- High Noise Immunity:  $V_{NIH} = V_{NIL} = 28\% V_{CC}$  (Min)
- Power Down Protection is provided on all inputs
- Low Noise:  $V_{OLP} = 0.6V$  (typ)
- Low Power Dissipation:  $I_{CC} = 4 \mu A$  (Max) @  $T_A = 25^\circ C$
- Pin and function compatible with 74HC573

#### Ordering Code:


| Order Number | Package Number | Package Description                                                         |
|--------------|----------------|-----------------------------------------------------------------------------|
| 74VHC573M    | M20B           | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  |
| 74VHC573SJ   | M20D           | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide               |
| 74VHC573MTC  | MTC20          | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| 74VHC573N    | N20A           | 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide      |

Surface mount packages are also available on Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

#### Logic Symbol



#### Connection Diagram



#### Pin Descriptions

| Pin Names       | Description                 |
|-----------------|-----------------------------|
| $D_0-D_7$       | Data Inputs                 |
| LE              | Latch Enable Input          |
| $\overline{OE}$ | 3-STATE Output Enable Input |
| $O_0-O_7$       | 3-STATE Outputs             |

## Functional Description


The VHC573 contains eight D-type latches with 3-STATE output buffers. When the Latch Enable (LE) input is HIGH, data on the  $D_n$  inputs enters the latches. In this condition the latches are transparent, i.e., a latch output will change state each time its D input changes. When LE is LOW the latches store the information that was present on the D inputs, a setup time preceding the HIGH-to-LOW transition of LE. The 3-STATE buffers are controlled by the Output Enable ( $\overline{OE}$ ) input. When  $\overline{OE}$  is LOW, the buffers are enabled. When  $\overline{OE}$  is HIGH the buffers are in the high impedance mode, but, this does not interfere with entering new data into the latches.

## Truth Table

| Inputs          |    |   | Outputs |
|-----------------|----|---|---------|
| $\overline{OE}$ | LE | D | $O_n$   |
| L               | H  | H | H       |
| L               | H  | L | L       |
| L               | L  | X | $O_0$   |
| H               | X  | X | Z       |

H = HIGH Voltage Level  
 L = LOW Voltage Level  
 X = Immaterial  
 Z = High Impedance

## Logic Diagram



Please note that this diagram is provided only for the understanding of logic operations and should not be used to estimate propagation delays.

**Absolute Maximum Ratings**(Note 1)

|                                                       |                          |
|-------------------------------------------------------|--------------------------|
| Supply Voltage ( $V_{CC}$ )                           | -0.5V to +7.0V           |
| DC Input Voltage ( $V_{IN}$ )                         | -0.5V to +7.0V           |
| DC Output Voltage ( $V_{OUT}$ )                       | -0.5V to $V_{CC} + 0.5V$ |
| Input Diode Current ( $I_{IK}$ )                      | -20 mA                   |
| Output Diode Current                                  | ±20 mA                   |
| DC Output Current ( $I_{OUT}$ )                       | ±25 mA                   |
| DC $V_{CC}$ /GND Current ( $I_{CC}$ )                 | ±75 mA                   |
| Storage Temperature ( $T_{STG}$ )                     | -65°C to +150°C          |
| Lead Temperature ( $T_L$ )<br>(Soldering, 10 seconds) | 260°C                    |

**Recommended Operating Conditions** (Note 2)

|                                         |                |
|-----------------------------------------|----------------|
| Supply Voltage ( $V_{CC}$ )             | 2.0V to +5.5V  |
| Input Voltage ( $V_{IN}$ )              | 0V to +5.5V    |
| Output Voltage ( $V_{OUT}$ )            | 0V to $V_{CC}$ |
| Operating Temperature ( $T_{OPR}$ )     | -40°C to +85°C |
| Input Rise and Fall Time ( $t_r, t_f$ ) |                |
| $V_{CC} = 3.3V \pm 0.3V$                | 0 ~ 100 ns/V   |
| $V_{CC} = 5.0V \pm 0.5V$                | 0 ~ 20 ns/V    |

**Note 1:** Absolute Maximum Ratings are values beyond which the device may be damaged or have its useful life impaired. The databook specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. Fairchild does not recommend operation outside databook specifications.

**Note 2:** Unused inputs must be held HIGH or LOW. They may not float.

**DC Electrical Characteristics**

| Symbol   | Parameter                        | $V_{CC}$<br>(V)  | $T_A = 25^\circ\text{C}$ |     |                      | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |                      | Units | Conditions                                                     |
|----------|----------------------------------|------------------|--------------------------|-----|----------------------|-------------------------------------------------|----------------------|-------|----------------------------------------------------------------|
|          |                                  |                  | Min                      | Typ | Max                  | Min                                             | Max                  |       |                                                                |
| $V_{IH}$ | HIGH Level Input Voltage         | 2.0<br>3.0 – 5.5 | 1.50<br>0.7 $V_{CC}$     |     |                      | 1.50<br>0.7 $V_{CC}$                            |                      | V     |                                                                |
| $V_{IL}$ | LOW Level Input Voltage          | 2.0<br>3.0 – 5.5 |                          |     | 0.50<br>0.3 $V_{CC}$ |                                                 | 0.50<br>0.3 $V_{CC}$ | V     |                                                                |
| $V_{OH}$ | HIGH Level Output Voltage        | 2.0              | 1.9                      | 2.0 |                      | 1.9                                             |                      | V     | $V_{IN} = V_{IH}$<br>or $V_{IL}$<br>$I_{OH} = -50 \mu\text{A}$ |
|          |                                  | 3.0              | 2.9                      | 3.0 |                      | 2.9                                             |                      |       |                                                                |
|          |                                  | 4.5              | 4.4                      | 4.5 |                      | 4.4                                             |                      | V     | $I_{OH} = -4 \text{ mA}$<br>$I_{OH} = -8 \text{ mA}$           |
|          |                                  | 3.0<br>4.5       | 2.58<br>3.94             |     |                      | 2.48<br>3.80                                    |                      |       |                                                                |
| $V_{OL}$ | LOW Level Output Voltage         | 2.0              |                          | 0.0 | 0.1                  |                                                 | 0.1                  | V     | $V_{IN} = V_{IH}$<br>or $V_{IL}$<br>$I_{OL} = 50 \mu\text{A}$  |
|          |                                  | 3.0              |                          | 0.0 | 0.1                  |                                                 | 0.1                  |       |                                                                |
|          |                                  | 4.5              |                          | 0.0 | 0.1                  |                                                 | 0.1                  | V     | $I_{OL} = 4 \text{ mA}$<br>$I_{OL} = 8 \text{ mA}$             |
|          |                                  | 3.0<br>4.5       |                          |     | 0.36<br>0.36         |                                                 | 0.44<br>0.44         |       |                                                                |
| $I_{OZ}$ | 3-STATE Output Off-State Current | 5.5              |                          |     | ±0.25                |                                                 | ±2.5                 | μA    | $V_{IN} = V_{IH}$ or $V_{IL}$<br>$V_{OUT} = V_{CC}$ or GND     |
| $I_{IN}$ | Input Leakage Current            | 0 – 5.5          |                          |     | ±0.1                 |                                                 | ±1.0                 | μA    | $V_{IN} = 5.5V$ or GND                                         |
| $I_{CC}$ | Quiescent Supply Current         | 5.5              |                          |     | 4.0                  |                                                 | 40.0                 | μA    | $V_{IN} = V_{CC}$ or GND                                       |

**Noise Characteristics**

| Symbol                | Parameter                                | $V_{CC}$<br>(V) | $T_A = 25^\circ\text{C}$ |        | Units | Conditions            |
|-----------------------|------------------------------------------|-----------------|--------------------------|--------|-------|-----------------------|
|                       |                                          |                 | Typ                      | Limits |       |                       |
| $V_{OLP}$<br>(Note 3) | Quiet Output Maximum Dynamic $V_{OL}$    | 5.0             | 0.9                      | 1.2    | V     | $C_L = 50 \text{ pF}$ |
| $V_{OLV}$<br>(Note 3) | Quiet Output Minimum Dynamic $V_{OL}$    | 5.0             | -0.8                     | -1.0   | V     | $C_L = 50 \text{ pF}$ |
| $V_{IHD}$<br>(Note 3) | Minimum HIGH Level Dynamic Input Voltage | 5.0             |                          | 3.5    | V     | $C_L = 50 \text{ pF}$ |
| $V_{ILD}$<br>(Note 3) | Maximum LOW Level Dynamic Input Voltage  | 5.0             |                          | 1.5    | V     | $C_L = 50 \text{ pF}$ |

**Note 3:** Parameter guaranteed by design.

## AC Electrical Characteristics



| Symbol            | Parameter                                         | V <sub>CC</sub><br>(V) | T <sub>A</sub> = 25°C |      |      | T <sub>A</sub> = -40°C to +85°C |      | Units | Conditions             |                        |
|-------------------|---------------------------------------------------|------------------------|-----------------------|------|------|---------------------------------|------|-------|------------------------|------------------------|
|                   |                                                   |                        | Min                   | Typ  | Max  | Min                             | Max  |       |                        |                        |
| t <sub>PLH</sub>  | Propagation Delay<br>Time (LE to O <sub>n</sub> ) | 3.3 ± 0.3              |                       | 7.6  | 11.9 | 1.0                             | 14.0 | ns    |                        | C <sub>L</sub> = 15 pF |
| t <sub>PHL</sub>  |                                                   |                        |                       | 10.1 | 15.4 | 1.0                             | 17.5 |       |                        | C <sub>L</sub> = 50 pF |
|                   |                                                   | 5.0 ± 0.5              |                       | 5.0  | 7.7  | 1.0                             | 9.0  | ns    |                        | C <sub>L</sub> = 15 pF |
|                   |                                                   |                        |                       | 6.5  | 9.7  | 1.0                             | 11.0 |       |                        | C <sub>L</sub> = 50 pF |
| t <sub>PLH</sub>  | Propagation Delay<br>Time (D–O <sub>n</sub> )     | 3.3 ± 0.3              |                       | 7.0  | 11.0 | 1.0                             | 13.0 | ns    |                        | C <sub>L</sub> = 15 pF |
| t <sub>PHL</sub>  |                                                   |                        |                       | 9.5  | 14.5 | 1.0                             | 16.5 |       |                        | C <sub>L</sub> = 50 pF |
|                   |                                                   | 5.0 ± 0.5              |                       | 4.5  | 6.8  | 1.0                             | 8.0  |       |                        | C <sub>L</sub> = 15 pF |
|                   |                                                   |                        |                       | 6.0  | 8.8  | 1.0                             | 10.0 |       |                        | C <sub>L</sub> = 50 pF |
| t <sub>PZL</sub>  | 3-STATE Output<br>Enable Time                     | 3.3 ± 0.3              |                       | 7.3  | 11.5 | 1.0                             | 13.5 | ns    | R <sub>L</sub> = 1 kΩ  | C <sub>L</sub> = 15 pF |
| t <sub>PZH</sub>  |                                                   |                        |                       | 9.8  | 15.0 | 1.0                             | 17.0 |       |                        | C <sub>L</sub> = 50 pF |
|                   |                                                   | 5.0 ± 0.5              |                       | 5.2  | 7.7  | 1.0                             | 9.0  | ns    |                        | C <sub>L</sub> = 15 pF |
|                   |                                                   |                        |                       | 6.7  | 9.7  | 1.0                             | 11.0 |       |                        | C <sub>L</sub> = 50 pF |
| t <sub>PLZ</sub>  | 3-STATE Output<br>Disable Time                    | 3.3 ± 0.3              |                       | 10.7 | 14.5 | 1.0                             | 16.5 | ns    | R <sub>L</sub> = 1 kΩ  | C <sub>L</sub> = 50 pF |
| t <sub>PHZ</sub>  |                                                   | 5.0 ± 0.5              |                       | 6.7  | 9.7  | 1.0                             | 11.0 |       |                        | C <sub>L</sub> = 50 pF |
| t <sub>OSLH</sub> | Output to Output Skew                             | 3.3 ± 0.3              |                       |      | 1.5  |                                 | 1.5  | ns    | (Note 4)               | C <sub>L</sub> = 50 pF |
| t <sub>OSHL</sub> |                                                   | 5.0 ± 0.5              |                       |      | 1.0  |                                 | 1.0  |       |                        | C <sub>L</sub> = 50 pF |
| C <sub>IN</sub>   | Input Capacitance                                 |                        |                       | 4    | 10   |                                 | 10   | pF    | V <sub>CC</sub> = Open |                        |
| C <sub>OUT</sub>  | Output Capacitance                                |                        |                       | 6    |      |                                 |      | pF    | V <sub>CC</sub> = 5.0V |                        |
| C <sub>PD</sub>   | Power Dissipation<br>Capacitance                  |                        |                       | 29   |      |                                 |      | pF    | (Note 5)               |                        |

**Note 4:** Parameter guaranteed by design. t<sub>OSLH</sub> = |t<sub>PLH max</sub> – t<sub>PLH min</sub>|; t<sub>OSHL</sub> = |t<sub>PHL max</sub> – t<sub>PHL min</sub>|


**Note 5:** C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I<sub>CC (opr.)</sub> = C<sub>PD</sub> \* V<sub>CC</sub> \* f<sub>IN</sub> + I<sub>CC</sub>/8 (per Latch). The total C<sub>PD</sub> when n pcs. of the Latch operates can be calculated by the equation: C<sub>PD(total)</sub> = 21 + 8n.

## AC Operating Requirements



| Symbol            | Parameter          | V <sub>CC</sub><br>(V) | T <sub>A</sub> = 25°C |     |     | T <sub>A</sub> = -40°C to +85°C |     | Units |
|-------------------|--------------------|------------------------|-----------------------|-----|-----|---------------------------------|-----|-------|
|                   |                    |                        | Min                   | Typ | Max | Min                             | Max |       |
| t <sub>w(H)</sub> | Minimum Pulse      | 3.3 ± 0.3              | 5.0                   |     |     | 5.0                             |     | ns    |
| t <sub>w(L)</sub> | Width (LE)         | 5.0 ± 0.5              | 5.0                   |     |     | 5.0                             |     |       |
| t <sub>S</sub>    | Minimum Setup Time | 3.3 ± 0.3              | 3.5                   |     |     | 3.5                             |     | ns    |
|                   |                    | 5.0 ± 0.5              | 3.5                   |     |     | 3.5                             |     |       |
| t <sub>H</sub>    | Minimum Hold Time  | 3.3 ± 0.3              | 1.5                   |     |     | 1.5                             |     | ns    |
|                   |                    | 5.0 ± 0.5              | 1.5                   |     |     | 1.5                             |     |       |



# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)




LAND PATTERN RECOMMENDATION



DIMENSIONS ARE IN MILLIMETERS

## NOTES:


- CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION AC, REF NOTE 6, DATE 7/93.
- DIMENSIONS ARE IN MILLIMETERS.
- DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLDS FLASH, AND TIE BAR EXTRUSIONS.
- DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.



DETAIL A

**20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide  
Package Number MTC20**

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide  
Package Number N20A

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)