






CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



P.C. LAYOUT



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: GOLD FLASHING OVER SILVER PLATE OVER
COPPER ALLOY
5. CONTACT RATING: 0.3A @125VAC
6. OPERATING FORCE: 800±200 GRAMS
7. OPERATING TEMP: -30°C TO 85°C
- ▲ 8. CIRCUIT SP: 12 POSITION 30° INDEX.
9. DIELECTRIC STRENGTH: 500VAC- 60 SEC.
- ▲ 10. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT
11. ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH®

A	15064	RELEASED FOR PRODUCTION	7/8/05	JB
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE KC52A9.501NPF

SCALE 1.5:1

DATE 7/8/2005

DR JB

DWG G511002

REV A