



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—						

REFERENCE P.C.BOARD PATTERN LAYOUT
(CONNECTOR MOUNTING SIDE)



REAL SIZE (SCALE 1:1)



1.8V	17.55	2.4	2.7
2.5V	18.45	1.5	1.8
POWER SUPPLY	D5	D4	D3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH ±

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME

DDR1 & DDR2 SODIMM SOCKET
0.6mm PITCH 200POS
STANDARD PROFILE REVERSE TYPE (NEW LATCH TYPE)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO


A300779C-1612508

SCALE 2:1

SHEET 2 OF 4

REV D

2		1				
LOC	DIST	REVISIONS				
J	—	P	LTR	DESCRIPTION	DATE	APVD
		—	—	SEE SHEET 1	—	—



TIN PLATING	16EA/TRAY	912109-1	1612508-3
TIN LEAD PLATING			1612508-1
REMARK (PEG)	QTY	TRAY P/N	P/N

1. THE DIRECTION OF EACH CONNECTOR ON A TRAY IS REFERRED TO THIS DRAWING.

2. GENERAL TOLERANCE:±0.5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME

DDR1 & DDR2 SODIMM SOCKET
0.6mm PITCH 200POS
STANDARD PROFILE REVERSE TYPE (NEW LATCH TYPE)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3 00779 C-1612508

SCALE 1:2

SHEET 4 OF 4

REV D