

2/1 FABRIC

- Shrink Temperature
275°F (135°C)
- Highly Flexible
- Halogen Free
- Excellent Chemical Resistance
- Superior Abrasion Resistance Over A Wide Temp. Range
- Cuts Easily With Scissors



Cut Cleanly
Scissor

Material

Polyolefin/Polyester

Grade

H2F

Put-Ups

Nominal Size	Part #	Unshrunk Diameter /mm	Shrunk Diameter /mm	Put-Ups		Available Colors	Lbs/100'
				Bulk Spool	Shop Spool		
1/2"	H2F0.48BK	12	6	100'	25'	Black (BK)	1.15
3/4"	H2F0.79BK	20	10	100'	25'	Black (BK)	1.61
1 3/16"	H2F1.18BK	30	15	100'	25'	Black (BK)	2.13
1 1/2"	H2F1.58BK	40	20	100'	25'	Black (BK)	2.66
2"	H2F1.97BK	50	25	100'	25'	Black (BK)	3.44
2 3/8"	H2F2.36BK	60	30	100'	25'	Black (BK)	4.11
2 3/4"	H2F2.75BK	70	35	100'	25'	Black (BK)	4.69

Fabric 2/1 Heatshrink Tubing Shrinks To 1/2 its original diameter!

2/1 Fabric Heatshrink tubing, a unique mixture of Polyolefin and Polyester yarns which shrinks to 1/2 its original diameter, is the ideal way to form the only shrinkable fabric of its kind.

The woven construction makes this product extremely flexible and resistant to trapping water, heat and humidity. Provides outstanding abrasion, chafing and cutting protection, even at high temperatures.

Shrinkflex Fabric tubing, designed primarily to provide mechanical abrasion protection for components such as rubber hoses, plastic pipes, and harness wiring bundles. Also suitable for other applications, such as noise and rattle suppression.

Colors Available:
BK (Black)

Applications: mechanical abrasion protection, severe environment protection, noise and rattle protection, and flexing application.



HEATSHRINK TUBING

Technical Data Sheet



2/1 FABRIC



Flammability Rating ____ Non-Flame-Retardant



Chemical Resistance

Lubricating Oil, Antifreeze (50% Ethylene Glycol),
Brake Fluid, Engine Oil, Unleaded Gasoline, Die-
sel Fluid, Hydraulic Fluid, Mineral Hydraulic Fluid,
Battery Acid, Water.

PHYSICAL PROPERTIES

Recommended Cutting _____ Scissors

Colors _____ 1

Wall Type _____ Single


Pliancy _____ Very Flexible

Abrasion Resistance _____ High

Shrinks
275°F (135°C)

Maximum Continuous
Mil-DTL-23053
257°F (125°C)

Minimum Continuous
Mil-DTL-23053
-40°F (-40°C)



Measure the Shrinkflex® tubing
to length and cut with a scissor.

The thickness of your bundle, as well as the desired final appearance, will determine the length of the tubing you cut. Generally, a piece 1 1/2" - 2" long will accommodate almost any need. Single wires, or smaller bundles, require shorter pieces.



Slip the Shrinkflex® tubing over the bundle and position it so that both the sleeved and unsleeved portions are sufficiently covered. Notice the small pieces of tubing installed on single wires as part of a color coding system. If your project requires multiple operations, always work up from the smallest to the largest bundle.



Gently apply heat to Shrinkflex® tubing from a heat gun, hair dryer or torch with an appropriate attachment. Keep the heat source far enough away so that hot metal or direct flame does not come in contact with the tubing, wires or sleeving. Move the heat around the bundle to prevent damaging the sleeving and to ensure that all areas of the tubing have been shrunk. Once cooled, your installation is complete.