

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

---

— , — , \*

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

|     |
|-----|
| LOC |
|-----|

|  |      |
|--|------|
|  | DIST |
|--|------|

REVISIONS

FI

25

|  |   |
|--|---|
|  | F |
|--|---|

|     |
|-----|
| LTR |
|-----|

DESCRIPTION

DATE \_\_\_\_\_

|     |
|-----|
| DWN |
|-----|

|      |
|------|
| APVD |
|------|

G2


REVISÉD PER ECO-13-004228

|         |
|---------|
| 08JUN13 |
|---------|


KH

|    |
|----|
| DR |
|----|

1. PACKAGED IN A HEAT SEALED 3 MIL POLYBAG WITH LABEL PER DWG 404707.
2. MAXIMUM BUNDLE DIAMETER: 50.8 [2.0].
3. MINIMUM TENSILE STRENGTH: 8.165 KG [18 LBS].
4. MIL NO. MS3367-4
5. MOSITURIZED 1 TO 2.5% WATER



|          |              |       |         |             |
|----------|--------------|-------|---------|-------------|
| OBSOLETE | 1 000        | TY2MB | BLACK   | 2-608687-0  |
|          | 1 000        | TY2M  | NATURAL | 2-608687-9  |
|          | 100          | TY2CB | BLACK   | 1-608687-0  |
|          | 100          | TY2C  | NATURAL | 1-608687-9  |
|          | QUANTITY/BAG | REF   | COLOR   | PART NUMBER |

|                                                                                       |  |                                                                                       |  |                                                                                                       |                    |
|---------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN 12MAR10<br>JR RUTH<br>CHK 12MAR10<br>T MICHELUTTI<br>APVD 12MAR10<br>T MICHELUTTI |  |  TE Connectivity |                    |
| DIMENSIONS:<br>mm [INCHES]                                                            |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                             |  | NAME<br>CABLE TIE,<br>RELEASABLE, 8 INCHES<br>—                                                       |                    |
|  |  | PRODUCT SPEC<br>—                                                                     |  |                                                                                                       |                    |
| MATERIAL<br>NYLON 6/6                                                                 |  | FINISH<br>—                                                                           |  |                                                                                                       |                    |
|                                                                                       |  | APPLICATION SPEC<br>—                                                                 |  | SIZE<br>A3                                                                                            | CAGE CODE<br>00779 |
|                                                                                       |  | WEIGHT<br>—                                                                           |  | DRAWING NO<br>C-608687                                                                                |                    |
|                                                                                       |  | CUSTOMER DRAWING                                                                      |  | SCALE<br>NONE                                                                                         | SHEET<br>1 OF 1    |
|                                                                                       |  |                                                                                       |  | REV<br>G2                                                                                             |                    |