

TYPICAL INDICATOR ORDERING EXAMPLE

LB 01 G W01 — 5C 12 — JC

Shapes

01	Square
02	Round
03	Rectangular

Housing

K	Black
G	Gray

Terminals

W01	Silver Solder Lug/ Quick Connect Terminals
-----	--

Lamps

Incandescent Lamp Used with Solid Cap

05	5-volt
12	12-volt

Incandescent or Neon Used with Insert Cap

01	110-volt Neon
05	5-volt Incandescent
12	12-volt Incandescent

Bright LED Used with LED Cap

Colors	Resistor
5C Red	No Code No Resistor
5D Amber	05 5-volt
	12 12-volt
5F Green	24 24-volt

Super Bright LED Used with LED Cap

6B	White
6F	Green
6G	Blue

Cap Types & Colors

Solid Cap: Lens/Filter Colors

BJ	White/Clear
CJ	Red/Clear
EJ	Yellow/Clear
FJ	Green/Clear
GJ	Blue/Clear

Insert Cap: Lens/Filter Colors

JB	Clear/White
JC	Clear/Red
JE	Clear/Yellow
*JF	Clear/Green
*JG	Clear/Blue

*JF & JG not suitable with neon.

LED Cap: Lens/Diffuser Colors

JB	Clear/White
JC	Clear/Red
JD	Clear/Amber
JF	Clear/Green

LED Cap: Lens/Diffuser Colors

JB	Clear/White
----	-------------

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE



LB01GW01-5C12-JC



SHAPES & PANEL CUTOUTS


01

.622" (15.8mm)
Square





02

.854" (21.7mm)
Round



03

.622" x .866" (15.8mm x 22.0mm)
Rectangular



Panel Thickness: .039" ~ .157" (1.0 ~ 4.0mm)

HOUSING

Housing Colors Available:

K

Black


G

Gray

TERMINALS

W01

Silver Solder Lug/.110" (2.8mm) Quick Connect



LAMP CODES & SPECIFICATIONS

Incandescent Lamp for Solid Colored and Colored Insert Caps

AT607  T-1 Bi-pin		05	12	
	Voltage	V	5V AC	12V AC
	Current	I	115mA	60mA
	Endurance	Hours	10,000 average	
	Ambient Temp. Range		-25°C ~ +50°C	

Neon Lamp for Colored Insert Cap






AT607N  T-1 Bi-pin		01	
	Voltage	V	110V AC
	Current	I	1.5mA
	Endurance	Hours	10,000 average
	Ambient Temp. Range		-25°C ~ +50°C
	Recommended Resistors: 33K ohms for 110V AC; 100K ohms for 220V AC		

The electrical specifications shown are determined at a basic temperature of 25°C.

CAP TYPES & COLOR COMBINATIONS

Color Codes: B White C Red D Amber E Yellow F Green G Blue J Clear






Solid Cap for Incandescent Lamp

Lens/Filter
Colors Available:**AT476**
Square**AT4012**
Round**AT4026**
Rectangular

Material: Polycarbonate Finish: Glossy

Lamp AT607





Insert Cap for Incandescent or Neon Lamp

Lens/Filter
Colors Available:**AT477**
Square**AT4013**
Round**AT4027**
RectangularJF and JG not suitable
with neon lamp.

Material: Polycarbonate Finish: Glossy

Lamp AT607 or 607N





Cap for Bright LED without Resistor

Lens/Diffuser
Colors Available:**AT4176**
Square**AT4178**
Round**AT4177**
Rectangular

Material: Polycarbonate Finish: Glossy

Bright LED
AT635

Cap for Bright LED with Resistor

Lens/Diffuser
Colors Available:**AT4162**
Square**AT4164**
Round**AT4163**
Rectangular

Material: Polycarbonate Finish: Glossy

Bright LED
AT627

CAP TYPES & COLOR COMBINATIONS

Cap for Super Bright LEDs




**Clear Lens
White Diffuser**

**AT4129
Square**





**AT4128
Round**

**AT4130
Rectangular**



**Transparent
Clear Lens**

Material:
Polycarbonate
Finish: Glossy






**Translucent
White Diffuser**



**LEDs AT625
AT631 AT632**




TYPICAL INDICATOR DIMENSIONS

Square






LB01KW01-12-CJ

Round



LB02KW01-12-CJ

Rectangular



LB03KW01-12-CJ