





| REVISIONS |         |                 |           |     |
|-----------|---------|-----------------|-----------|-----|
| REV.      | ECO. NO | DESCRIPTION     | DATE      | BY  |
| A         | 1255    | INITIAL RELEASE | 1/24/2007 | MNH |



CONTACT ID  
SCALE 2:1


- NOTES:
1. INSULATOR MATERIAL: SEE PART NUMBER CODING
  2. CONTACT MATERIAL: SEE PART NUMBER CODING
  3. PLATING: SEE PART NUMBER CODING
  4. OPERATING TEMPERATURE: SEE PART NUMBER CODING
  5. PROCESSING TEMP: SEE PART NUMBER CODING
  6. UL FLAMMABILITY RATING: 94V-0
  7. VOLTAGE RATING: 600 VDC MINIMUM AT SEA LEVEL.
  8. CURRENT RATING: 3 AMP PER CONTACT PAIR
  9. VOLTAGE DROP: 30 MILLI VOLT AT RATED CURRENT
  10. INSULATION RESISTANCE: 5000 MEGA OHM
  11. CONNECTOR IDENTIFICATION: THE PART SHALL BE MARKED WITH A PART NUMBER AND BARCODE
  12. BOARD THICKNESS ACCOMMODATED: .062 ± .008"
  13. BOARD INSERTION FORCE: 16 OZ MAX PER CONTACT PAIR WHEN USING A .062" TEST BLADE. INTERNAL INSPECTION TO BE PER SULLIN'S WORK INSTRUCTION W17.3-01.
  14. BOARD WITHDRAWAL FORCE: 1 OUNCE MINIMUM PER CONTACT PAIR USING .062" PCB





RoHS COMPLIANT

## CUSTOMER COPY


| UNLESS OTHERWISE SPECIFIED:<br>DIMENSIONS ARE IN INCHES[MM]                                                                                          |  | DATE                                                                                                                                                                                                                                       | NAME | SULLINS ELECTRONICS                  |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|--------------------------------------|--|
| TOLERANCES:<br>ANGULAR: ± 1°<br>.XX= ± .02 [508]<br>.XXX= ± .005 [1270]<br>.XXXX= ± .0005 [0127]<br>PARENTHEetical INFORMATION IS FOR REFERENCE ONLY |  | DRAWN                                                                                                                                                                                                                                      | MNH  | DESCRIPTION<br>EDGE CARD, .100 CC LP |  |
| INTERPRET DIMENSIONS AND GEOMETRIC TOLERANCING PER: ANSI Y14.5-1984                                                                                  |  | THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS. |      | PART NUMBER<br>C DRY                 |  |
| SIZE<br>C                                                                                                                                            |  | DWG. NO.<br>C10879                                                                                                                                                                                                                         |      | REV<br>A                             |  |
| SCALE: 2:1                                                                                                                                           |  | SHEET 1 OF 3                                                                                                                                                                                                                               |      |                                      |  |



-- C -- DRYN




-- C -- DRYE



-- C -- DRY

2X FLOATING BOBBIN  
Ø .116 [2.95]  
CLEARANCE FOR  
# 4 SCREW



-- C -- DRYF

## CUSTOMER COPY



RoHS COMPLIANT

|                                                                                       |  |                                                                                                                                                                                                                                                                 |  |                       |  |
|---------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------|--|
| UNLESS OTHERWISE SPECIFIED:<br>DIMENSIONS ARE IN INCHES[MM]                           |  | DATE                                                                                                                                                                                                                                                            |  | NAME                  |  |
| TOLERANCES:                                                                           |  | DRAWN                                                                                                                                                                                                                                                           |  | MNH                   |  |
| ANGULAR: ± 1°                                                                         |  | THE INFORMATION HEREIN CONTAINS<br>PROPRIETARY INFORMATION OF<br>SULLINS ELECTRONICS AND IS NOT<br>TO BE REPRODUCED, USED OR<br>DISCLOSED TO OTHERS FOR ANY<br>PURPOSE EXCEPT AS SPECIFICALLY<br>AUTHORIZED IN WRITING BY AN<br>OFFICER OF SULLINS ELECTRONICS. |  |                       |  |
| .XX= ± .02 [ .508]                                                                    |  |                                                                                                                                                                                                                                                                 |  |                       |  |
| .XXX= ± .005 [ .1270]                                                                 |  |                                                                                                                                                                                                                                                                 |  |                       |  |
| .XXXX= ± .0005 [ .0127]                                                               |  |                                                                                                                                                                                                                                                                 |  |                       |  |
| PARENTHEICAL INFORMATION IS FOR<br>REFERENCE ONLY                                     |  |                                                                                                                                                                                                                                                                 |  |                       |  |
| INTERPRET DIMENSIONS AND GEOMETRIC<br>TOLERANCING<br>PER: ANSI Y14.5-1984             |  | DESCRIPTION<br><b>SULLINS<br/>ELECTRONICS</b>                                                                                                                                                                                                                   |  |                       |  |
|  |  | PART NUMBER                                                                                                                                                                                                                                                     |  | EDGE CARD, .100 CC LP |  |
|                                                                                       |  | C_DRY                                                                                                                                                                                                                                                           |  |                       |  |
|                                                                                       |  | SIZE                                                                                                                                                                                                                                                            |  | DWG. NO.              |  |
|                                                                                       |  | C10879                                                                                                                                                                                                                                                          |  | REV                   |  |
|                                                                                       |  | SCALE: 2:1                                                                                                                                                                                                                                                      |  | SHEET 2 OF 3          |  |

| PART<br>NUMBER | NO. OF<br>POS. | A□.008[0.20] |        | B□.008[0.20] |        | C□.015[0.38] |        | D□.010[0.25] |        | E□.020[0.51] |        | F±.005[0.13] |       |
|----------------|----------------|--------------|--------|--------------|--------|--------------|--------|--------------|--------|--------------|--------|--------------|-------|
|                |                | IN           | MM     | IN           | MM     | IN           | MM     | IN           | MM     | IN           | MM     | IN           | MM    |
| C04DRY *       | 4              | 0.300        | 7.62   | 0.500        | 12.70  | 0.675        | 17.15  | 0.975        | 24.77  | 1.275        | 32.39  | 0.330        | 8.38  |
| C05DRY         | 5              | 0.400        | 10.16  | 0.600        | 15.24  | 0.775        | 19.69  | 1.075        | 27.31  | 1.375        | 34.93  |              |       |
| C06DRY         | 6              | 0.500        | 12.70  | 0.700        | 17.78  | 0.875        | 22.23  | 1.175        | 29.85  | 1.475        | 37.47  |              |       |
| C07DRY         | 7              | 0.600        | 15.24  | 0.800        | 20.32  | 0.975        | 24.77  | 1.275        | 32.39  | 1.575        | 40.01  |              |       |
| C08DRY         | 8              | 0.700        | 17.78  | 0.900        | 22.86  | 1.075        | 27.31  | 1.375        | 34.93  | 1.675        | 42.55  |              |       |
| C10DRY         | 10             | 0.900        | 22.86  | 1.100        | 27.94  | 1.275        | 32.39  | 1.575        | 40.01  | 1.875        | 47.63  |              |       |
| C12DRY         | 12             | 1.100        | 27.94  | 1.300        | 33.02  | 1.475        | 37.47  | 1.775        | 45.09  | 2.075        | 52.71  |              |       |
| C13DRY         | 13             | 1.200        | 30.48  | 1.400        | 35.56  | 1.575        | 40.01  | 1.875        | 47.63  | 2.175        | 55.25  |              |       |
| C15DRY         | 15             | 1.400        | 35.56  | 1.600        | 40.64  | 1.775        | 45.09  | 2.075        | 52.71  | 2.375        | 60.33  |              |       |
| C17DRY         | 17             | 1.600        | 40.64  | 1.800        | 45.72  | 1.975        | 50.17  | 2.275        | 57.79  | 2.575        | 65.41  |              |       |
| C18DRY         | 18             | 1.700        | 43.18  | 1.900        | 48.26  | 2.075        | 52.71  | 2.375        | 60.33  | 2.675        | 67.95  |              |       |
| C19DRY         | 19             | 1.800        | 45.72  | 2.000        | 50.80  | 2.175        | 55.25  | 2.475        | 62.87  | 2.775        | 70.49  |              |       |
| C20DRY         | 20             | 1.900        | 48.26  | 2.100        | 53.34  | 2.275        | 57.79  | 2.575        | 65.41  | 2.875        | 73.03  |              |       |
| C22DRY         | 22             | 2.100        | 53.34  | 2.300        | 58.42  | 2.475        | 62.87  | 2.775        | 70.49  | 3.075        | 78.11  |              |       |
| C23DRY *       | 23             | 2.200        | 55.88  | 2.400        | 60.96  | 2.575        | 65.41  | 2.875        | 73.03  | 3.175        | 80.65  |              |       |
| C25DRY         | 25             | 2.400        | 60.96  | 2.600        | 66.04  | 2.775        | 70.49  | 3.075        | 78.11  | 3.375        | 85.73  |              |       |
| C26DRY         | 26             | 2.500        | 63.50  | 2.700        | 68.58  | 2.875        | 73.03  | 3.175        | 80.65  | 3.475        | 88.27  |              |       |
| C28DRY         | 28             | 2.700        | 68.58  | 2.900        | 73.66  | 3.075        | 78.11  | 3.375        | 85.73  | 3.675        | 93.35  |              |       |
| C30DRY         | 30             | 2.900        | 73.66  | 3.100        | 78.74  | 3.275        | 83.19  | 3.575        | 90.81  | 3.875        | 98.43  |              |       |
| C31DRY         | 31             | 3.000        | 76.20  | 3.200        | 81.28  | 3.375        | 85.73  | 3.675        | 93.35  | 3.975        | 100.97 |              |       |
| C35DRY         | 35             | 3.400        | 86.36  | 3.600        | 91.44  | 3.775        | 95.89  | 4.075        | 103.51 | 4.375        | 111.13 | 0.400        | 10.16 |
| C36DRY         | 36             | 3.500        | 88.90  | 3.700        | 93.98  | 3.875        | 98.43  | 4.175        | 106.05 | 4.475        | 113.67 |              |       |
| C40DRY         | 40             | 3.900        | 99.06  | 4.100        | 104.14 | 4.275        | 108.59 | 4.575        | 116.21 | 4.875        | 123.83 |              |       |
| C43DRY         | 43             | 4.200        | 106.68 | 4.400        | 111.76 | 4.575        | 116.21 | 4.875        | 123.83 | 5.175        | 131.45 |              |       |
| C44DRY         | 44             | 4.300        | 109.22 | 4.500        | 114.30 | 4.675        | 118.75 | 4.975        | 126.37 | 5.275        | 133.99 |              |       |
| C49DRY         | 49             | 4.800        | 121.92 | 5.000        | 127.00 | 5.175        | 131.45 | 5.475        | 139.07 | 5.775        | 146.69 |              |       |
| C50DRY         | 50             | 4.900        | 124.46 | 5.100        | 129.54 | 5.275        | 133.99 | 5.575        | 141.61 | 5.875        | 149.23 |              |       |
| C52DRY *       | 52             | 5.100        | 129.54 | 5.300        | 134.62 | 5.475        | 139.07 | 5.775        | 146.69 | 6.075        | 154.31 |              |       |
| C60DRY         | 60             | 5.900        | 149.86 | 6.100        | 154.94 | 6.275        | 159.39 | 6.575        | 167.01 | 6.875        | 174.63 |              |       |
| C65DRY         | 65             | 6.400        | 162.56 | 6.600        | 167.64 | 6.775        | 172.09 | 7.075        | 179.71 | 7.375        | 187.33 |              |       |

\* CONSULT FACTORY FOR AVAILABILITY

PART NUMBER CODING

MATERIAL (INSULATOR/CONTACT)

E=PBT/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 10 SECS MAX

R=PPS/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

G=PA9T/PHOSPHOR BRONZE

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

H=PBT/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +125°C

PROCESSING TEMP: 260°C FOR 10 SECS MAX

A=PPS/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +150°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

J=PA9T/BERYLLIUM COPPER

OPERATING TEMP: -65°C TO +150°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

F=PPS/SPINODAL (CONSULT FACTORY)

OPERATING TEMP: -65°C TO +200°C

C=PPS/BERYLLIUM NICKEL (CONSULT FACTORY)

OPERATING TEMP: -65°C TO +200°C

PROCESSING TEMP: 260°C FOR 120 SECS MAX

W=PEEK/BERYLLIUM NICKEL (CONSULT FACTORY)

OPERATING TEMP: -65°C TO +250°C

C DRY

NUMBER OF POSITIONS

PLATING

ALL PLATINGS HAVE .000050" NICKEL UNDERPLATE

CONTACT SURFACE

G = .000010" GOLD

Y = .000030" GOLD

B = .000010" GOLD

C = .000030" GOLD

\*\*E = .000100" PURE TIN, MATTE

S = .000010" GOLD OVERALL

M = .000030" GOLD

LEAD FREE

\*\*ONLY AVAILABLE ON MATERIAL CODES E, R AND G

MOUNTING STYLE

H = .125" DIA. CLEARANCE HOLES (PAGE 1)

I = #4-40 THREADED INSERT (PAGE 2)

S = .125" DIA. SIDE MOUNTING (PAGE 2)

N = NO MOUNTING EARS (PAGE 2)

F = FLOATING BOBBIN (PAGE 2)

TERMINATION

.000005" GOLD


.000005" GOLD

.000100" PURE TIN, MATTE

.000100" PURE TIN, MATTE

OVERALL

.000010" GOLD OVERALL



CUSTOMER COPY



RoHS COMPLIANT

|                                                                                                                                                                                                                                                                 |  |                                      |      |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------|------|
| UNLESS OTHERWISE SPECIFIED:<br>DIMENSIONS ARE IN INCHES[MM]                                                                                                                                                                                                     |  | DATE                                 | NAME |
| TOLERANCES:<br>ANGULAR: ± 1°<br>.XX= ± .02 [ .508]<br>.XXX= ± .005 [ .1270]<br>.XXXX= ± .0005 [ .0127]<br>PARENTHEICAL INFORMATION IS FOR<br>REFERENCE ONLY                                                                                                     |  | DRAWN                                | MNH  |
| THE INFORMATION HEREIN CONTAINS<br>PROPRIETARY INFORMATION OF<br>SULLINS ELECTRONICS AND IS NOT<br>TO BE REPRODUCED, USED OR<br>DISCLOSED TO OTHERS FOR ANY<br>PURPOSE EXCEPT AS SPECIFICALLY<br>AUTHORIZED IN WRITING BY AN<br>OFFICER OF SULLINS ELECTRONICS. |  | DESCRIPTION<br>EDGE CARD, .100 CC LP |      |
| PART NUMBER<br>C DRY                                                                                                                                                                                                                                            |  | PART NUMBER<br>C10879                |      |
| SIZE<br>C                                                                                                                                                                                                                                                       |  | DWG. NO.<br>C10879                   |      |
| INTERPRET DIMENSIONS AND GEOMETRIC<br>TOLERANCING<br>PER: ANSI Y14.5-1984                                                                                                                                                                                       |  | REV<br>A                             |      |
| SCALE: 2:1                                                                                                                                                                                                                                                      |  | SHEET 3 OF 3                         |      |