


By accepting this proprietary Huck drawing, recipient agrees not to reproduce or disclose any part thereof to any others without the written permission of Huck International, Inc.

REV	DESCRIPTION	DATE
A	RELEASE	11-11-93
B	FILE OBSOLETE. SS 99-1826-2	04-11-96

NOTES:

- 1 FOR -06 PRODUCT WITH 1.000 INCH LONG PINTAIL ONLY, (GP AND ALUMINUM LGP)
- 2 ANVIL ASSEMBLY 123072 CONSISTS OF:
ANVIL 123071 AND
RETAINER 120738,
NOT AVAILABLE SEPARATELY.



MATERIAL:	-	SPEC: -	TOLERANCES UNLESS OTHERWISE SPECIFIED		HUCK INTERNATIONAL, INC., I.S.D. 85 GRAND STREET, P.O. BOX 2270 KINGSTON, NEW YORK 12401			
HARDNESS:	-				NOSE ASSEMBLY			
HEAT TREAT:	-	SPEC: -	XX, .XXX ±		-06 PULL-IN 			
SURF. TREAT:	-	SPEC: -	INT. COR. RADII					
SURFACE FINISH NOT TO EXCEED			Ra	BREAK EDGES	DET: T.L. CK:	DATE: 11-11-93	SCALE: 2/1	
IDENTIFICATION PER SPEC 42-311: ★ CHEMICAL ETCH			ANGLES ±		FOC.			
SURFACES TO BE ☉, //, ⊕, ⊥, & ▽ WITHIN			T.I.R.	FINAL ASSY: -	FAC.	B	99-1826-2A	

FORM: KE104 REV B