






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: CURRENT: .01mA-250mA
VOLTAGE: 20mV-50 VDC
5. OPERATING LIFE: 30,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 1000VDC, 1000M OHM. MIN.
- ▲ 7. OPERATING FORCE: 250gf ± 100 GRAMS
8. OPERATING TEMP.: -30°C to 85°C ^B
- ▲ 9. TRAVEL: MOMENTARY
FULL TRAVEL 5.1 ± 0.5mm
10. CONTACT RESISTANCE: 50 m OHM. MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT
- ▲ 13. LED COLOR: RED

▲ LED SPECS	UNITS	RED
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	2.3 TYP-2.6 MAX
LUMINOUS INTENSITY @ 20mA	MCD	13



B	19585	CHANGED DIMS & TEMP.	1/14/11	BGL
A	18803	New Release	1/19/10	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP370ACGR

SCALE 2=1

DATE 1/20/2010

DR rc

DWG T010000

REV B