





NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. OPERATING FORCE: 425 ± 100 CM/STANDARD
6. OPERATING TEMP: -30° to 85° C
7. CIRCUIT DP: 6 POSITIONS, 30° INDEX.
8. DIELECTRIC STRENGTH: 1000V RMS min.@Sea Level
9. DESIGNATE MAJOR DIMENSIONS
10. HARDWARE SUPPLIED ON SWITCH- SEE BELOW
STOPRING, LOCKWASHER, & HEXNUT



CONTACT CONFIGURATION

Timing: Non-Shorting (BBM)



E-SWITCH®				TITLE			
A	12821	REVISE NOTE 10	CJB	8/29/02	SCALE	1.5:1	DATE
A	12392	RELEASED FOR PRODUCTION	CJB	8/29/02	KC-26-A (10.0mm) 02-N-L-S		
REV.	ECN No.	DESCRIPTION	DATE	CHKD	DR	CJB	DWG
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				G510405			REV
				B			